



Recommended P.C.B Layout

MATERIAL

Insulator : 30% Glass fiber PBT
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 5000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : AC 500V for one minute
Operation Temperature : -40°C to + 105°C

210-7 2- 02 G B 01
1 2 3 4 5 6

- 1. 5: Normal Parts
- 7: Green Product
- 9: Green Product High Temp (NYLON 6T or 9T)
- 2. 1: Single row
- 2: Dual rows
- 3. No. of contacts per row
- 4. G: Gold flash
- S: Selective
- T: Tin plated
- 5. B: Black Insulator
- 6. Pinrex internal code.

				<p>TOLERANCE</p> <p>.0 =±.30</p> <p>.00 =±.20</p> <p>.000 =±.XXX</p> <p>.0000=±.</p> <p>ANG.=±3'</p>		<p>UNITS : mm</p>		<p>OLD PART NO.</p> <p>PH1S-202GB1160</p>		<p>TITLE</p> <p>PIN HEADER 2.54*2.54mm</p> <p>STRAIGHT TYPE, DUAL ROWS</p>		<p>頻銳科技股份有限公司</p> <p>PINREX TECHNOLOGY CORP.</p>	
B	ADD DIM	2005/07/08		DRAWER		CHECK		SHEET		REV.		APP'D	
A	RELEASE	2004/01/15		Kent				1 OF 1		B			
REV.	DESCRIPTION	DATE		SCALE	SIZE			NEW PART NO.		DRAW NO.			
				NONE	A4			210-72-02GB01		210-72-02GB01(B版)			