

AP55N03**N-Channel Power MOSFET****Description**

The AP55N03 uses advanced trench technology and design to provide excellent $R_{DS(ON)}$ with low gate charge. It can be used in a wide variety of applications.




General Features

- $V_{DS} = 30V, I_D = 30A$
- $R_{DS(ON)} < 12m\Omega @ V_{GS}=10V$
- $R_{DS(ON)} < 15m\Omega @ V_{GS}=4.5V$

- High density cell design for ultra low $R_{DS(on)}$
- Fully characterized Avalanche voltage and current
- Good stability and uniformity with high E_{AS}
- Excellent package for good heat dissipation
- Special process technology for high ESD capability

Application

- Power switching application
- Hard switched and high frequency circuits
- Uninterruptible Power Supply

**Schematic diagram****Marking and pin assignment****TO-252-2L top view****Package Marking and Ordering Information**

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
AP55N03	AP55N03	TO-252-2L	-	-	-

Absolute Maximum Ratings ($T_c=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 12	V
Drain Current-Continuous	I_D	30	A
Drain Current-Continuous($T_c=100^\circ C$)	$I_D (100^\circ C)$	22	A
Pulsed Drain Current	I_{DM}	90	A
Maximum Power Dissipation	P_D	40	W
Derating factor		0.4	W/ $^\circ C$
Single pulse avalanche energy (Note 5)	E_{AS}	60	mJ
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 To 175	$^\circ C$

AP55N03**N-Channel Power MOSFET****Thermal Characteristic**

Thermal Resistance, Junction-to-Case ^(Note 2)	R _{θJC}	2.5	°C/W
--	------------------	-----	------

Electrical Characteristics (T_C=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Off Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	30	33	-	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±12V, V _{DS} =0V	-	-	±100	nA
On Characteristics ^(Note 3)						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	1	1.3	2	V
Drain-Source On-State Resistance	R _{DSON}	V _{GS} =10V, I _D =20A	-	9.6	12	mΩ
		V _{GS} =4.5V, I _D =15A	-	12	15	
Forward Transconductance	g _{FS}	V _{DS} =5V, I _D =10A	15	-	-	S
Dynamic Characteristics ^(Note 4)						
Input Capacitance	C _{iss}	V _{DS} =15V, V _{GS} =0V, F=1.0MHz	-	1000	-	PF
Output Capacitance	C _{oss}		-	150	-	PF
Reverse Transfer Capacitance	C _{rss}		-	100	-	PF
Switching Characteristics ^(Note 4)						
Turn-on Delay Time	t _{d(on)}	V _{DD} =15V, I _D =20A V _{GS} =10V, R _{GEN} =1.8Ω	-	5	-	nS
Turn-on Rise Time	t _r		-	8	-	nS
Turn-Off Delay Time	t _{d(off)}		-	19	-	nS
Turn-Off Fall Time	t _f		-	5	-	nS
Total Gate Charge	Q _g	V _{DS} =10V, I _D =25A, V _{GS} =10V	-	20	-	nC
Gate-Source Charge	Q _{gs}		-	7	-	nC
Gate-Drain Charge	Q _{gd}		-	4.1	-	nC
Drain-Source Diode Characteristics						
Diode Forward Voltage ^(Note 3)	V _{SD}	V _{GS} =0V, I _s =25A	-	0.75	1.2	V
Diode Forward Current ^(Note 2)	I _s		-	-	30	A
Reverse Recovery Time	t _{rr}	T _J = 25°C, IF = 30A di/dt = 100A/μs ^(Note 3)	-	22	35	nS
Reverse Recovery Charge	Q _{rr}		-	11	18	nC
Forward Turn-On Time	t _{on}	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)				

Notes:


1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board, t ≤ 10 sec.
3. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.
4. Guaranteed by design, not subject to production
5. EAS condition: T_j=25°C, V_{DD}=15V, V_G=10V, L=1mH, R_g=25Ω

AP55N03


N-Channel Power MOSFET

Test circuit


1) E_{AS} test Circuits



2) Gate charge test Circuit:



3) Switch Time Test Circuit:



AP55N03

N-Channel Power MOSFET




Figure 7 Capacitance vs Vds



Figure 9 BV_{dss} vs Junction Temperature

Figure 8 Safe Operation Area









Figure 10 $V_{gs(th)}$ vs Junction Temperature


Figure 11 Normalized Maximum Transient Thermal Impedance

AP55N03**N-Channel Power MOSFET****Typical Electrical and Thermal Characteristics (Curves)****Figure 1 Output Characteristics****Figure 4 Rdson-Junction Temperature****Figure 2 Transfer Characteristics****Figure 5 Gate Charge****Figure 3 Rdson- Drain Current****Figure 6 Source- Drain Diode Forward**

AP55N03

N-Channel Power MOSFET

TO-252 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	