



30V,100A N-channel MOSFET

Features

- 30V,100A
- $R_{DS(ON)}=3.1\text{m}\Omega$ (Typ.) @ $V_{GS}=10\text{V}$
- $R_{DS(ON)}=4.5\text{m}\Omega$ (Typ.) @ $V_{GS}=4.5\text{V}$
- Advanced Trench Technology
- Provide Excellent $R_{DS(ON)}$ and Low Gate Charge

Application

- Load Switch
- PWM Application

Package**Absolute Maximum Ratings** ($T_c=25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter		Max.	Units
V_{DSS}	Drain-Source Voltage		30	V
V_{GSS}	Gate-Source Voltage		± 20	V
I_D	Continuous Drain Current	$T_c = 25^\circ\text{C}$	100	A
		$T_c = 100^\circ\text{C}$	65	A
I_{DM}	Pulsed Drain Current ^{note1}		400	A
E_{AS}	Single Pulsed Avalanche Energy ^{note2}		180	mJ
P_D	Power Dissipation	$T_c = 25^\circ\text{C}$	88	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case		1.7	$^\circ\text{C}/\text{W}$
T_J, T_{STG}	Operating and Storage Temperature Range		-55 to +175	$^\circ\text{C}$

Electrical Characteristics ($T_C=25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
Off Characteristic						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu\text{A}$	30	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=30V, V_{GS}=0V,$	-	-	1.0	μA
I_{GSS}	Gate to Body Leakage Current	$V_{DS}=0V, V_{GS}=\pm 20V$	-	-	± 100	nA
On Characteristics						
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	1.0	1.6	2.5	V
$R_{DS(\text{on})}$ note3	Static Drain-Source on-Resistance	$V_{GS}=10V, I_D=24A$	-	3.1	4	$\text{m}\Omega$
		$V_{GS}=4.5V, I_D=12A$	-	4.5	6	
g_{FS}	Forward Transconductance	$V_{DS}=10V, I_D=10A$	-	15.5	-	S
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=25V, V_{GS}=0V,$ $f=1.0\text{MHz}$	-	2200	-	pF
C_{oss}	Output Capacitance		-	280	-	pF
C_{rss}	Reverse Transfer Capacitance		-	177	-	pF
Q_g	Total Gate Charge	$V_{DS}=15V, I_D=24A,$ $V_{GS}=10V$	-	42	-	nC
Q_{gs}	Gate-Source Charge		-	4	-	nC
Q_{gd}	Gate-Drain("Miller") Charge		-	13	-	nC
Switching Characteristics						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD}=15V,$ $I_D=15A, R_{GEN}=3.3\Omega,$ $V_{GS}=10V$	-	12.6	-	ns
t_r	Turn-on Rise Time		-	19.5	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	42.8	-	ns
t_f	Turn-off Fall Time		-	13.2	-	ns
Drain-Source Diode Characteristics and Maximum Ratings						
I_s	Maximum Continuous Drain to Source Diode Forward Current	-	-	100	-	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current	-	-	400	-	A
V_{SD}	Drain to Source Diode Forward Voltage	$V_{GS}=0V, I_s=30A$	-	-	1.2	V
t_{rr}	Body Diode Reverse Recovery Time	$I_F=30A, dI/dt=100A/\mu\text{s}$	-	19	-	ns
Q_{rr}	Body Diode Reverse Recovery Charge		-	11	-	nC

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. EAS condition: $T_J=25^\circ\text{C}, V_{DD}=25V, V_G=10V, R_G=25\Omega$

3. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 2\%$

Typical Performance Characteristics




Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveforms







Figure 3: Unclamped Inductive Switching Test Circuit & Waveforms



* V_{GS} = 5V for Logic Level Devices

Figure 4:Peak Diode Recovery dv/dt Test Circuit & Waveforms (For N-channel)


Package Mechanical Data



TO-252

Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.10		2.50	0.083		0.098
A2	0		0.10	0		0.004
B	0.66		0.86	0.026		0.034
B2	5.18		5.48	0.202		0.216
C	0.40		0.60	0.016		0.024
C2	0.44		0.58	0.017		0.023
D	5.90		6.30	0.232		0.248
D1	5.30REF			0.209REF		
E	6.40		6.80	0.252		0.268
E1	4.63			0.182		
G	4.47		4.67	0.176		0.184
H	9.50		10.70	0.374		0.421
L	1.09		1.21	0.043		0.048
L2	1.35		1.65	0.053		0.065
V1		7°			7°	
V2	0°		6°	0°		6°

Reel Specification-TO-252



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
W	15.90	16.00	16.10	0.626	0.630	0.634
E	1.65	1.75	1.85	0.065	0.069	0.073
F	7.40	7.50	7.60	0.291	0.295	0.299
D0	1.40	1.50	1.60	0.055	0.059	0.063
D1	1.40	1.50	1.60	0.055	0.059	0.063
P0	3.90	4.00	4.10	0.154	0.157	0.161
P1	7.90	8.00	8.10	0.311	0.315	0.319
P2	1.90	2.00	2.10	0.075	0.079	0.083
A0	6.85	6.90	7.00	0.270	0.271	0.276
B0	10.45	10.50	10.60	0.411	0.413	0.417
K0	2.68	2.78	2.88	0.105	0.109	0.113
T	0.24		0.27	0.009		0.011
t1	0.10			0.004		
10P0	39.80	40.00	40.20	1.567	1.575	1.583

OUTLINE	REEL (PCS)	PER CARTON (PCS)	TAPE & REEL
TAPING	2,500	25,000	13inch