

**30V,5.8A  
N-Channel Mosfet**

## FEATURES

$RDS(ON) \leq 33m\Omega$  @  $VGS=10V$

$RDS(ON) \leq 39m\Omega$  @  $VGS=4.5V$

$RDS(ON) \leq 60m\Omega$  @  $VGS=2.5V$

## SOT-23




## APPLICATIONS


Load/Power Switching

Interfacing Switching

## MARKING



## N-CHANNEL MOSFET



## Maximum ratings ( $T_a=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	$\pm 12$	
Continuous Drain Current	$I_D$	5.8	A
Pulsed Drain Current	$I_{DM}$	30	
Maximum Power Dissipation	$P_D$	0.35	W
Thermal Resistance from Junction to Ambient( $t \leq 5s$ )	$R_{\theta JA}$	357	$^\circ C/W$
Junction Temperature	$T_J$	150	$^\circ C$
Storage Temperature	$T_{stg}$	-55 ~ +150	

MOSFET ELECTRICAL CHARACTERISTICS  $T_a=25\text{ }^{\circ}\text{C}$  unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
<b>Static</b>						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	30	31.5		V
Gate-source threshold voltage	$V_{GS(\text{th})}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	0.7	1	1.4	
Gate-source leakage	$I_{GSS}$	$V_{DS} = 0V, V_{GS} = \pm 12V$			$\pm 100$	nA
Zero gate voltage drain current	$I_{DSS}$	$V_{DS} = 30V, V_{GS} = 0V$			1	$\mu A$
Drain-source on-state resistance <sup>a</sup>	$R_{DS(\text{on})}$	$V_{GS} = 10V, I_D = 5A$		21	33	$m\Omega$
		$V_{GS} = 4.5V, I_D = 4A$		25	39	
		$V_{GS} = 2.5V, I_D = 3A$		36	60	
Body diode voltage	$V_{SD}$	$I_S = 1A$		0.8	1	V
<b>Dynamic<sup>b</sup></b>						
Input capacitance	$C_{iss}$	$V_{DS} = 15V, V_{GS} = 0V, f = 1MHz$			1155	pF
Output capacitance	$C_{oss}$			108		
Reverse transfer capacitance	$C_{rss}$			84		
Total gate charge	$Q_g$	$V_{DS} = 15V, V_{GS} = 4.5V, I_D = 5.8A$		10		nC
Gate-source charge	$Q_{gs}$			1.6		
Gate-drain charge	$Q_{gd}$			3.1		
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 15V, R_L = 2.7\Omega, V_{GS} = 10V, R_{GEN} = 3\Omega$			5	nS
Rise time	$t_r$				7	
Turn-off delay time	$t_{d(off)}$				40	
Fall time	$t_f$				6	

**Notes :**

- a. Pulse Test : Pulse Width < 300 $\mu s$ , Duty Cycle  $\leq 2\%$ .
- b. Guaranteed by design, not subject to production testing.

## N-Channel 30V (D-S) MOSFET Typical Characteristics




Figure 1:Switching Test Circuit




Figure 2:Switching Waveforms


 $T_J$ -Junction Temperature(°C)

Figure 3 Power Dissipation



 $T_J$ -Junction Temperature(°C)

Figure 4 Drain Current



Vds Drain-Source Voltage (V)

Figure 5 Output Characteristics










I<sub>D</sub>- Drain Current (A)

Figure 6 Drain-Source On-Resistance


**Figure 7 Transfer Characteristics****Figure 8 Drain-Source On-Resistance****Figure 9 Rdson vs Vgs****Figure 10 Capacitance vs Vds****Figure 11 Gate Charge****Figure 12 Source-Drain Diode Forward**

## SOT-23 package



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

## SOT-23 Suggested Pad Layout



Note:  
 1. Controlling dimension:in millimeters.  
 2.General tolerance: $\pm 0.05\text{mm}$ .  
 3.The pad layout is for reference purposes only.