


Dual N Channel Enhancement Mode MOSFET
0.65A

DESCRIPTION


DMG1012T is the N-Channel enhancement mode power field effect transistors are produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance and provide superior switching performance. These devices are particularly suited for low voltage applications such as notebook computer power management and other battery powered circuits where high-side switching, low in-line power loss, and resistance to transients are needed.

PIN CONFIGURATION SOT-523 / SC-89



FEATURE

- 20V/0.65A, $R_{DS(ON)} = 380\text{ohm}$ @ $V_{GS} = 4.5\text{V}$
- 20V/0.55A, $R_{DS(ON)} = 450\text{ohm}$ @ $V_{GS} = 2.5\text{V}$
- 20V/0.45A, $R_{DS(ON)} = 800\text{ohm}$ @ $V_{GS} = 1.8\text{V}$
- Super high density cell design for extremely low $R_{DS(ON)}$
- Exceptional low on-resistance and maximum DC current capability
- SOT-523 / SC89 package design



Dual N Channel Enhancement Mode MOSFET
0.65A

ABSOULTE MAXIMUM RATINGS (Ta = 25°C Unless otherwise noted)

Parameter		Symbol	Typical	Unit
Drain-Source Voltage		V _{DSS}	20	V
Gate-Source Voltage		V _{GSS}	+/-12	V
Continuous Drain Current (T _J =150°C)	T _A =25°C	I _D	0.65	A
	T _A =80°C		0.45	
Pulsed Drain Current		I _{DM}	1.0	A
Continuous Source Current (Diode Conduction)		I _S	0.3	A
Power Dissipation	T _A =25°C	P _D	0.27	W
	T _A =70°C		0.16	
Operation Junction Temperature		T _J	-55/150	°C
Storage Temperature Range		T _{STG}	-55/150	°C







Dual N Channel Enhancement Mode MOSFET
0.65A






ELECTRICAL CHARACTERISTICS (Ta = 25°C Unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} =0V, I _D =250uA	20			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	0.35		1.0	V
Gate Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =+/-12V			100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =20V, V _{GS} =0V			1	uA
		V _{DS} =20V, V _{GS} =0V T _J =55°C			5	
On-State Drain Current	I _{D(on)}	V _{DS} ≤4.5V, V _{GS} =5V	0.7			A
Drain-source On-Resistance	R _{DS(on)}	V _{GS} =4.5V, I _D =0.65A		260	380	mΩ
		V _{GS} =2.5V, I _D =0.55A		320	450	
		V _{GS} =1.8V, I _D =0.55A		420	800	
Forward Transconductance	g _{fs}	V _{DS} =10V, I _D =0.4A		1.0		S
Diode Forward Voltage	V _{SD}	I _s =0.15A, V _{GS} =0V		0.8	1.2	V


DYNAMIC

Total Gate Charge	Q _g	V _{DS} =10V, V _{GS} =4.5V, V _{DS} =0.6A		1.2	1.5	nC
Gate-Source Charge	Q _{gs}			0.2		
Gate-Drain Charge	Q _{gd}			0.3		
Turn-On Time	T _{d(on)}	V _{DD} =10V, RL=10Ω, I _D =0.5A, V _{GEN} =4.5V, RG=6Ω		5	10	nS
	t _r			8	15	
Turn-Off Time	T _{d(off)}			10	18	
	t _f			1.2	2.8	

TYPICAL CHARACTERISTICS


TYPICAL CHARACTERISTICS


Dual N Channel Enhancement Mode MOSFET
 0.65A

SOT523 (SC-89) PACKAGE OUTLINE


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.700	0.900	0.028	0.035
A1	0.000	0.100	0.000	0.004
A2	0.700	0.800	0.028	0.031
b1	0.150	0.250	0.006	0.010
b2	0.250	0.325	0.010	0.013
c	0.100	0.200	0.004	0.008
D	1.500	1.700	0.059	0.067
E	0.750	0.850	0.030	0.033
E1	1.450	1.750	0.057	0.069
e	0.500 TYP		0.020 TYP	
e1	0.900	1.100	0.035	0.043
L	0.550 REF		0.022 REF	
L1	0.280	0.440	0.011	0.017
θ	0°	4°	0°	4°