

**MM3Z2V0~MM3Z120**  
**Silicon Planar Zener Diodes**

Revision:A


**General Description**

Silicon planar zener diode in a small plastic SMD SOD-323 package.


**Features**

- Total power dissipation: max. 500mW
- Small plastic package suitable for surface mounted design
- Wide variety of voltage ranges: nom. 2.0 to 120V
- Tolerance approximately  $\pm 5\%$

**Functional diagram**



SOD-323



Note: 1-Cathode;2-Anode

**Absolute Maximum Ratings ( $T_a=25^\circ\text{C}$ )**

Symbol	Parameter	Value	Unit
	Zener Current see Table "Characteristics"		
$P_{tot}$	Power Dissipation	500	mW
$T_j$	Junction Temperature	175	$^\circ\text{C}$
$T_s$	Storage Temperature Range	-55 to +175	$^\circ\text{C}$

**Characteristics at  $T_{amb}=25^\circ\text{C}$**

	Symbol	Min.	Typ.	Max.	Unit
Thermal Resistance Junction to Ambient Air	$R_{thA}$	---	---	0.3	K/mW
Forward Voltage at $I_F=100\text{mA}$	$V_F$	---	---	1	V

# MM3Z2V0~MM3Z120

## Electrical Characteristics

Type	Zener Voltage Range			Dynamic Impedance		Revers Leakage Current		Temp. coefficient of Zener Voltage
	V <sub>znom</sub> V	I <sub>ZT</sub> mA	for V <sub>ZT</sub> V	Z <sub>Z</sub> (Max) at I <sub>Z</sub>		I <sub>R</sub> (Max) μA	at V <sub>R</sub> V	TK <sub>vz</sub> %/K
				Ω	mA			
MM3Z2V0	2.0	5	1.80...2.15	100	5	120	0.5	-0.09...-0.06
MM3Z2V2	2.2	5	2.08...2.33	100	5	120	0.7	-0.09...-0.06
MM3Z2V4	2.4	5	2.28...2.56	100	5	120	1.0	-0.09...-0.06
MM3Z2V7	2.7	5	2.5...2.9	110	5	120	1.0	-0.09...-0.06
MM3Z3V0	3.0	5	2.8...3.2	120	5	50	1.0	-0.08...-0.05
MM3Z3V3	3.3	5	3.1...3.5	130	5	20	1.0	-0.08...-0.05
MM3Z3V6	3.6	5	3.4...3.8	130	5	10	1.0	-0.08...-0.05
MM3Z3V9	3.9	5	3.7...4.1	130	5	10	1.0	-0.08...-0.05
MM3Z4V3	4.3	5	4.0...4.6	130	5	10	1.0	-0.06...-0.03
MM3Z4V7	4.7	5	4.4...5.0	130	5	10	1.0	-0.05...+0.02
MM3Z5V1	5.1	5	4.8...5.4	130	5	5	1.5	-0.02...+0.02
MM3Z5V6	5.6	5	5.2...6.0	80	5	5	2.5	-0.05...+0.05
MM3Z6V2	6.2	5	5.8...6.6	50	5	2	3.0	0.03...0.06
MM3Z6V8	6.8	5	6.4...7.2	30	5	2	3.5	0.03...0.07
MM3Z7V5	7.5	5	7.0...7.9	30	5	2	4.0	0.03...0.07
MM3Z8V2	8.2	5	7.7...8.7	30	5	2	5.0	0.03...0.08
MM3Z9V1	9.1	5	8.5...9.6	30	5	2	6.0	0.03...0.09
MM3Z10	10	5	9.4...10.6	30	5	2	7.0	0.03...0.1
MM3Z11	11	5	10.4...11.6	30	5	2	8.0	0.03...0.11
MM3Z12	12	5	11.4...12.7	35	5	2	9.0	0.03...0.11
MM3Z13	13	5	12.4...14.1	35	5	2	10	0.03...0.11
MM3Z15	15	5	13.8...15.6	40	5	2	11	0.03...0.11
MM3Z16	16	5	15.3...17.1	40	5	2	12	0.03...0.11
MM3Z18	18	5	16.8...19.1	45	5	2	13	0.03...0.11
MM3Z20	20	5	18.8...21.2	50	5	2	15	0.03...0.11
MM3Z22	22	5	20.8...23.3	55	5	2	17	0.04...0.12
MM3Z24	24	5	22.8...25.6	60	5	2	19	0.04...0.12
MM3Z27	27	55	25.1...28.9	70	2	2	21	0.04...0.12
MM3Z30	30	5	28...32	80	2	2	23	0.04...0.12
MM3Z33	33	5	31...35	80	2	2	25	0.04...0.12
MM3Z36	36	5	34...38	90	2	2	27	0.04...0.12
MM3Z39	39	2.5	37...41	100	2	2	30	0.04...0.12
MM3Z43	43	2.5	40...46	130	2	2	33	0.04...0.12
MM3Z47	47	2.5	44...50	150	2	2	36	0.04...0.12
MM3Z51	51	2.5	48...54	180	2	1	39	0.04...0.12
MM3Z56	56	2.5	52...60	180	2	1	43	0.04...0.12
MM3Z62	62	2.5	58...66	200	2	0.2	47	0.04...0.12

# MM3Z2V0~MM3Z120

Type	Zener Voltage Range			Dynamic Impedance		Revers Leakage Current		Temp. coefficient of Zener Voltage
	$V_{znom}$	$I_{zT}$ for	$V_{zT}$	$Z_z(Max)$ at $I_z$		$I_R(Max)$ at $V_R$		TK <sub>vz</sub> %/K
	V	mA	V	$\Omega$	mA	$\mu A$	V	
MM3Z68	68	2.5	64...72	250	2	0.2	52	0.04...0.12
MM3Z75	75	2.5	70...79	300	2	0.2	57	0.04...0.12
MM3Z82	82	2.5	77...87	300	2	0.2	63	0.05...0.12
MM3Z91	91	1	85...96	700	1	0.2	69	0.05...0.12
MM3Z100	100	1	94...106	700	1	0.2	76	0.05...0.12
MM3Z110	110	1	104...116	800	1	0.2	84	0.05...0.12
MM3Z120	120	1	114...127	900	1	0.2	91	0.05...0.12

- 1)  $V_z$  is tested with pulses (20 ms).
- 2)  $Z_z$  is measured at  $I_z$  by given a very small A.C. current signal.

## Breakdown Characteristics $T_J=constant$ (pulse)




Fig 1







Fig 2

## SOD-323 Mechanical Data



Dimensions				
Dim	Inches		Mil	
	Min	Max	Min	Max
A	0.060	0.071	1.5	1.8
B	0.045	0.054	1.2	1.4
C	0.060	0.107	2.3	2.7
D	-	0.043	-	1.1
E	0.012	0.016	0.3	0.4
F	0.004	0.010	0.10	0.25
H	-	0.004	-	0.10

**CONTROLLING DIMENSION: MILLIMETERS**

The SINO-IC logo is a registered trademark of ShangHai Sino-IC Microelectronics Co., Ltd.

© 2005 SINO-IC – Printed in China – All rights reserved.

**SHANGHAI SINO-IC MICROELECTRONICS CO., LTD**

Add: No.55-302, 200 SongTao Road, ZhangJiang Hi-Tech Park, Pudong, Shanghai 201203, China

Phone: +86-21-50275099 50805407 50805408

Fax: +86-21-50275077

Email: [webmaster@sino-ic.com](mailto:webmaster@sino-ic.com)

Website: <http://www.sino-ic.com>