



SBU8A~SBU8M

SILICON SINGLE-PHASE BRIDGE RECTIFIER

VOLTAGE 50 to 1000 Volts **CURRENT** 8.0 Amperes


SBU Unit: inch (mm)

FEATURES

- Plastic material has Underwriters Laboratory Flammability Classification 94V-O
- Ideal for printed circuit board
- Reliable low cost construction utilizing molded plastic technique.
- High temperature soldering guaranteed:
260°C/10 seconds/.375"(9.5mm) lead length at 5 lbs. (2.3kg) tension
- Pb free product : 99% Sn above can meet RoHS environment substance request

MECHANICAL DATA

- Case: Reliable low cost construction utilizing
- molded plastic technique
- Terminals: Leads solderable per MIL-STD-750, Method 2026
- Mounting position: Any
- Mounting torque: 5 in. lb. Max.
- Weight: 0.2 ounce, 5.6 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified. Resistive or inductive load, 60Hz.
For Capacitive load derate current by 20%.

PARAMETER	SYMBOL	SBU8A	SBU8B	SBU8D	SBU8G	SBU8J	SBU8K	SBU8M	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Bridge Input Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward $T_C=100^\circ\text{C}$ Rectified Output Current at $T_A=40^\circ\text{C}$	$I_{F(AV)}$					8.0			A
						6.0			
I ² t Rating for fusing ($t < 8.3\text{ms}$)	I ² t					259			A ² sec
Peak Forward Surge Current single sine-wave superimposed on rated load (JEDEC method)	I_{FSM}					250			Apk
Maximum Forward Voltage Drop per Bridge Element at 8.0A	V_F					0.98			Vpk
Maximum Reverse Leakage Current at Rated @ $T_A=25^\circ\text{C}$ Dc Blocking Voltage @ $T_A=100^\circ\text{C}$	I_R					3.0			uA
						1000			
Typical Thermal Resistance per leg (Note 2)	$R_{\theta JA}$					16.0			°C/W
Typical Thermal Resistance per leg (Note 3)	$R_{\theta JC}$					2.8			
Operating Junction and Storage Temperature Range	T_J, T_{STG}					-55 to + 150			°C

NOTES:

1. Recommended mounting position is to bolt down on heatsink with silicone thermal compound for maximum heat transfer with #6 screw.
2. Units Mounted in free air, no heatsink, P.C.B at 0.375"(9.5mm) lead length with 0.5 x 0.5"(12 x 12mm)copper pads.
3. Units Mounted on a 2.0 x 1.6" x 0.3" thick (5 x 4 x 0.8cm) AL plate.



SBU8A~SBU8M

RATING AND CHARACTERISTIC CURVES




Fig.1 - DERATING CURVE FOR OUTPUT RECTIFIED CURRENT




Fig.2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




Fig.3 - TYPICAL REVERSE CHARACTERISTICS




Fig.4 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER ELEMENT




Fig.5 - TYPICAL JUNCTION CAPACITANCE