



Shear Patterns - Dual Grid

Transducer-Class® Strain Gages

| | | | | | | |
|---------------------|---|---|---------------------------------------|---------------------|----------------------------|---------------------------------------|
| GAGE PATTERN | Actual size shown. Enlarged when necessary for definition. | | GAGE DESIGNATION See Note 1 | RES. IN OHMS | STANDARD CREEP CODE | ENCAPSULATION OPTION AVAILABLE |
| | DIMENSIONS | <input type="checkbox"/> inch <input checked="" type="checkbox"/> millimeter | | | | |

| | | | | | | |
|---|-----------------------|-------------------|----------------------|------------------------------------|------------|---|
|  | | | | Three-tab version of S034 pattern. | | |
| GAGE LENGTH | OVERALL LENGTH | GRID WIDTH | OVERALL WIDTH | J2A-XX-S111K-350 | 350 ± 0.4% | K |
| 0.125 | 0.33 | 0.100 | 0.275 | | | |
| 3.18 | 8.4 | 2.54 | 6.99 | | | |
| MATRIX SIZE | 0.40 L x 0.34 W | | 10.1 L x 8.5 W | | | |

| | | | | | | |
|---|-----------------------|-------------------|----------------------|--|------------|---|
|  | | | | Encapsulated dual-shear pattern with tabs at both ends of pattern. | | |
| GAGE LENGTH | OVERALL LENGTH | GRID WIDTH | OVERALL WIDTH | J2A-XX-S245K-350 | 350 ± 0.4% | K |
| 0.125 | 0.360 | 0.201 | 0.252 | | | |
| 3.18 | 9.14 | 5.10 | 6.40 | | | |
| MATRIX SIZE | 0.39 L x 0.29 W | | 9.9 L x 7.4 W | | | |

Note 1: All products are RoHS compliant.



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.


Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.

Advanced Sensors


N2A SERIES

N2A gages are constantan-alloy patterns constructed on a thin, laminated, polyimide-film backing. This series is capable of low and repeatable creep performance. Construction is very rugged, which will help prevent gage handling damage. Advanced Sensors N2A gages are offered with epoxy encapsulation as standard. An open-faced version can be supplied upon request.




J2A SERIES

J2A gages are encapsulated constantan-alloy patterns. Both the encapsulation and backing are thin, laminated polyimide film. Gage soldering tabs are exposed for simplified lead connections. Creep performance is equal to the N2A Series, although the presence of an encapsulating layer will require a change in creep code selection to maintain the same performance.



N2K SERIES

N2K gages are modified-Karma-alloy patterns constructed on a thin, laminated, polyimide-film backing. All N2K gages are supplied with gold soldering pads (DG) for ease of leadwire attachment. Copper soldering pads are also available. Most gages in the N2K Series can also be modulus compensated. Advanced Sensors N2K gages are offered with epoxy encapsulation as standard. An open-faced version can be supplied upon request.




N5K SERIES

N5K gages are modified-Karma-alloy patterns constructed on a thin, laminated, polyimide-film backing constructed to improve gage performance at elevated temperatures. All N5K gages are supplied with gold soldering pads (DG) for ease of leadwire attachment. Copper soldering pads are also available. Most gages in the N5K Series can also be modulus compensated. Advanced Sensors N5K gages are offered with epoxy encapsulation as standard.

J5K SERIES

J5K gages are encapsulated, modified-Karma-alloy patterns specially constructed to improve gage performance at elevated temperatures. Because of the laminated polyimide-film backing and encapsulation, all J5K patterns are fully flexible without being brittle. Gold soldering pads (DG) as well as copper soldering pads (DP) are exposed for simplified lead connections. Some J5K gages can be supplied with modulus-compensation (EMC) options. For best high-temperature performance, J5K-Series gages should be installed with M-Bond 450 high-temperature adhesive.



| GAGE SERIES | TEMPERATURE RANGE | | GAGE FACTOR (SEE NOTE) | FATIGUE LIFE | |
|-------------|-------------------------------------|--------------------------------------|-------------------------|-------------------------------|---------------------------------|
| | STATIC | DYNAMIC | | STRAIN LEVEL IN $\mu\epsilon$ | NUMBER OF CYCLES |
| N2A | -100° to +200°F (-75° to +95°C) | Same as Static | 2.05 nom. | ± 1500 1500 | 10^7 10^8 ⁽²⁾ |
| J2A | -100° to +200°F (-75° to +95°C) | Same as Static | 2.05 nom. | ± 1700 1700 | 10^6 10^7 ⁽²⁾ |
| N2K | -100° to +200°F (-75° to +95°C) | Same as Static | 2.1 nom. ⁽¹⁾ | ± 1800 | 10^7 |
| N5K | -100° to +400°F (-75° to +205°C) | -320° to +500°F (-195° to +260°C) | 2.1 nom. ⁽¹⁾ | ± 1800 | 10^7 |
| J5K | -100° to +400°F (-75° to +205°C) | -320° to +500°F (-195° to +260°C) | 2.1 nom. ⁽¹⁾ | ± 2000 1800 | 10^7 10^8 ⁽²⁾ |

Notes:

Advanced Sensors gages are supplied with nominal gage factor values that will vary slightly with pattern. They are not suitable for strain measurement in stress analysis applications. Request our Precision Strain Gages databook, or contact our Applications Engineering Department, for a complete listing of gages for precision strain measurement applications.

⁽¹⁾ Nominal gage factor is 2.2 for EMC options.


⁽²⁾ Unidirectional strain.

Advanced Sensors

CREEP COMPENSATION

Commercial transducers regularly achieve a creep specification of less than $\pm 0.02\%$ of full scale (FS) for a 20-minute test. To attain this level on a high production basis, it is usually necessary to match the strain gage's creep characteristic to the spring element creep.

Most *Transducer-Class* gages can be adjusted in design to exhibit either a positive or negative creep under load. Spring element materials exhibit only positive creep under load. (See figure below.)



Since transducer creep depends on several variables such as spring element material, heat treatment, strain field, adhesive type and test temperature, it is not possible to predict the proper gage compensation necessary to achieve the best creep result.

Most of the gages in this catalog list one available creep compensation code. Since it is not possible to predetermine the creep characteristics of a particular transducer, it is suggested that the standard creep code be ordered in quantities sufficient to evaluate three or four transducers. Where creep levels are high enough to warrant correction, a different creep compensation, either more negative or more positive, depending on test results, can often be recommended.

A complicating factor in creep code selection is that while different gage patterns may list the same creep code, they do not necessarily exhibit the same creep behavior. This is because the gage backing selection, gridline width and gage length also influence creep characteristics.

It should also be noted that this type of creep correction is generally limited to transducers exhibiting less than $\pm 0.1\%$ FS creep. Higher creep levels in the positive direction are often the result of poor spring element material selection. Negative creep values in excess of 0.1% FS generally are the result of a faulty gage installation.

MODULUS COMPENSATION (EMC) OPTION

Many of the K-alloy gages in this catalog are available in a special form which permits the gage factor change with temperature to be adjusted over a wide range during gage manufacture.

Properly matched to the transducer spring element, these EMC (Effective Modulus Compensation) gages can provide very good self-correction of changes in transducer span versus temperature. A compensation better than $\pm 0.0008\%/^{\circ}\text{F}$ ($\pm 0.0014\%/^{\circ}\text{C}$) can readily be achieved in many cases.

While this may at first appear to be the "ideal" strain gage for transducers, there are certain factors that should be considered prior to selecting EMC gages for a given application:

1. EMC gages cost more than other gages. In most cases the difference is great enough to offset the additional cost of span/temperature resistors.
2. EMC gages must be "matched" to the transducer spring material. Depending on the degree of compensation accuracy desired, the standard EMC options may not yield the "best fit" compensation on the spring material in use. In these cases, a special foil lot which possesses the desired compensation would be required. There is normally a minimum order requirement and set-up charge for special foil lots.
3. Transducer spring materials may not have batch-to-batch repeatability sufficient to maintain specifications when using the same EMC gages. New material lot testing is therefore necessary for high precision units.

Despite these limitations, EMC gages can often be advantageous for transducer manufacturers.

The following standard EMC options are available:

OPTION M1

Gage factor slope is -1.50% per 100°F (-2.70% per 100°C). Provides span-versus-temperature compensation for many stainless steels.

OPTION M2

Gage factor slope is -2.35% per 100°F (-4.23% per 100°C). Provides span-versus-temperature compensation for most aluminum alloys.

OPTION M3

Gage factor slope is -1.25% per 100°F (-2.25% per 100°C). Provides span-versus-temperature compensation for many tool steels.

OPTION M4

Gage factor slope is -1.35% per 100°F (-2.43% per 100°C). Provides "mid-range" compensation between M1 and M3.

Advanced Sensors

