


General Description

These N-Channel enhancement mode power field effect transistors are using trench DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switching applications.

| | | |
|-------|---------------------|----------------|
| BVDSS | R _{DS(ON)} | I _D |
| 60V | 75mΩ | 5A |

SOT89 Pin Configuration



Features

- 60V,5A, R_{DS(ON)} =75mΩ@V_{GS} = 10V
- Improved dv/dt capability
- Fast switching
- 100% EAS Guaranteed
- Green Device Available

Applications

- Motor Drive
- Power Tools
- LED Lighting

Absolute Maximum Ratings T_C=25°C unless otherwise noted

| Symbol | Parameter | Rating | Units |
|------------------|--|------------|-------|
| V _{DS} | Drain-Source Voltage | 60 | V |
| V _{GS} | Gate-Source Voltage | ±20 | V |
| I _D | Drain Current – Continuous (T _C =25°C) | 5 | A |
| | Drain Current – Continuous (T _C =100°C) | 3.2 | A |
| I _{DM} | Drain Current – Pulsed ¹ | 20 | A |
| EAS | Single Pulse Avalanche Energy ² | 25 | mJ |
| IAS | Single Pulse Avalanche Current ² | 7 | A |
| P _D | Power Dissipation (T _C =25°C) | 1.79 | W |
| | Power Dissipation – Derate above 25°C | 0.014 | W/°C |
| T _{STG} | Storage Temperature Range | -50 to 150 | °C |
| T _J | Operating Junction Temperature Range | -50 to 150 | °C |

Thermal Characteristics

| Symbol | Parameter | Typ. | Max. | Unit |
|------------------|--|------|------|------|
| R _{θJA} | Thermal Resistance Junction to ambient | --- | 70 | °C/W |
| R _{θJC} | Thermal Resistance Junction to Case | --- | 30 | °C/W |

Electrical Characteristics (T_J=25 °C, unless otherwise noted)
Off Characteristics

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|-------------------------------------|---|--|------|------|------|------|
| BV _{DSS} | Drain-Source Breakdown Voltage | V _{GS} =0V, I _D =250uA | 60 | --- | --- | V |
| ΔBV _{DSS} /ΔT _J | BV _{DSS} Temperature Coefficient | Reference to 25°C, I _D =1mA | --- | 0.05 | --- | V/°C |
| I _{DSS} | Drain-Source Leakage Current | V _{DS} =60V, V _{GS} =0V, T _J =25°C | --- | --- | 1 | uA |
| | | V _{DS} =48V, V _{GS} =0V, T _J =125°C | --- | --- | 10 | uA |
| I _{GSS} | Gate-Source Leakage Current | V _{GS} =±20V, V _{DS} =0V | --- | --- | ±100 | nA |

On Characteristics

| | | | | | | |
|----------------------|---|--|-----|-----|-----|-------|
| R _{DS(ON)} | Static Drain-Source On-Resistance | V _{GS} =10V, I _D =5A | --- | 60 | 75 | mΩ |
| | | V _{GS} =4.5V, I _D =3A | --- | 70 | 90 | mΩ |
| V _{GS(th)} | Gate Threshold Voltage | V _{GS} =V _{DS} , I _D =250uA | 1.2 | 1.8 | 2.5 | V |
| ΔV _{GS(th)} | V _{GS(th)} Temperature Coefficient | | --- | -5 | --- | mV/°C |
| g _{fs} | Forward Transconductance | V _{DS} =10V, I _D =3A | --- | 7 | --- | S |

Dynamic and switching Characteristics

| | | | | | | |
|---------------------|-------------------------------------|--|-----|------|-----|----|
| Q _g | Total Gate Charge ^{2, 3} | V _{DS} =48V, V _{GS} =10V, I _D =5A | --- | 9.3 | 14 | nC |
| Q _{gs} | Gate-Source Charge ^{2, 3} | | --- | 2.1 | 4 | |
| Q _{gd} | Gate-Drain Charge ^{2, 3} | | --- | 1.8 | 4 | |
| T _{d(on)} | Turn-On Delay Time ^{2, 3} | V _{DD} =30V, V _{GS} =10V, R _G =3.3Ω I _D =1A | --- | 2.9 | 6 | ns |
| T _r | Rise Time ^{2, 3} | | --- | 9.5 | 18 | |
| T _{d(off)} | Turn-Off Delay Time ^{2, 3} | | --- | 18.4 | 35 | |
| T _f | Fall Time ^{2, 3} | | --- | 5.3 | 10 | |
| C _{iss} | Input Capacitance | V _{DS} =15V, V _{GS} =0V, F=1MHz | --- | 500 | 725 | pF |
| C _{oss} | Output Capacitance | | --- | 45 | 65 | |
| C _{rss} | Reverse Transfer Capacitance | | --- | 16 | 30 | |
| R _g | Gate resistance | V _{GS} =0V, V _{DS} =0V, F=1MHz | --- | 2 | 4 | Ω |

Drain-Source Diode Characteristics and Maximum Ratings

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|-----------------|--------------------------------------|---|------|------|------|------|
| I _S | Continuous Source Current | V _G =V _D =0V, Force Current | --- | --- | 5 | A |
| I _{SM} | Pulsed Source Current | | --- | --- | 20 | A |
| V _{SD} | Diode Forward Voltage | V _{GS} =0V, I _S =1A, T _J =25°C | --- | --- | 1 | V |
| t _{rr} | Reverse Recovery Time ² | V _{GS} =30V, I _S =1A, dI/dt=100A/μs T _J =25°C | --- | 23.2 | --- | ns |
| Q _{rr} | Reverse Recovery Charge ² | | --- | 14.3 | --- | nC |

Note :

1. Repetitive Rating : Pulsed width limited by maximum junction temperature.
2. V_{DD}=25V, V_{GS}=10V, L=1mH, I_{AS}=7A., R_G=25Ω, Starting T_J=25°C
3. The data tested by pulsed, pulse width ≤ 300us, duty cycle ≤ 2%.
4. Essentially independent of operating temperature.




Fig.1 Typical Output Characteristics




Fig.2 $R_{DS(on)}$ vs. Gate Voltage




Fig.3 Continuous Drain Current vs. T_C




Fig.4 Normalized $R_{DS(on)}$ vs. T_C




Fig.5 Normalized V_{th} vs. T_J




Fig.6 Gate Charge Waveform




Fig.7 Normalized Transient Response




Fig.8 Maximum Safe Operation Area




Fig.9 Switching Time Waveform





Fig.10 EAS Waveform

SOT89 PACKAGE INFORMATION



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 1.400 | 1.600 | 0.055 | 0.063 |
| b | 0.320 | 0.520 | 0.013 | 0.020 |
| b1 | 0.400 | 0.580 | 0.016 | 0.023 |
| c | 0.350 | 0.440 | 0.014 | 0.017 |
| D | 4.400 | 4.600 | 0.173 | 0.181 |
| D1 | 1.550 REF | | 0.061 REF | |
| E | 2.300 | 2.600 | 0.091 | 0.102 |
| E1 | 3.940 | 4.250 | 0.155 | 0.167 |
| e | 1.500 TYP. | | 0.060 TYP. | |
| e1 | 3.000 TYP | | 0.118 TYP | |
| L | 0.900 | 1.200 | 0.035 | 0.047 |