

**Specification**


**MATERIAL:** IL 94V-0, Insulator: High Temperature Thermoplastic, Gaskets: Copper Alloy

**PLATING:**



Contact: Plated 99% Ni Overall Contact Au 10  
Sull: Plated 50% Ni Overall, PVD Au 10

**Electrical:**

Current Rating : 0.5A AC/DC max.  
Voltage Rating : 120V AC/DC  
Ambient Temperature Range : -20° C~+60° C  
Storage Temperature Range : -40° C~+70° C  
Moisture Humidity Range : 5% R.H. Max.  
Contact Resistance: 10mΩ max. Ω  
Insulation Resistance: 1000M ΩV/500VDC  
Testing Cycle: 300~600 Insertions  
产品耐插温度: 200度



SIM pin assignment	Pin#	Name
C1	VCC	供电电压
C2	RST	重置
C3	CLK	时钟
C5	GND	接地
C6	VPP	程序电压
C7	I/O	输入输出



PCB AREA  
RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

REVISION NO.	REV. NO.	DESCRIPTION	DATE	DESIGNER
1	1			



台湾汉博电子科技有限公司  
Taiwan Han Bo Electronic Technology Co., Ltd.

PRODUCT NAME:	BOBo	DATE:	2014.9
PRODUCT NO.:	SNO-1350	DATE:	
SCALE:	1:1	DATE:	
REV.:	A	DATE:	
FIG. NO.:	1 of 1	DATE:	

DIMENSIONS UNIT: mm	TOLERANCE
UNLESS OTHERWISE SPECIFIED	±0.15
1.X: ±	±0.10
2.XXX: ±	±0.05
ANGULAR: ±	1°