


NPN Transistors

KST9013

■ Features

- Excellent h_{FE} linearity
- Collector Current : $I_C=0.5A$

■ Absolute Maximum Ratings $T_a = 25^\circ C$

Parameter	Symbol	Rating	Unit
Collector - Base Voltage	V_{CB0}	40	V
Collector - Emitter Voltage	V_{CEO}	25	V
Emitter - Base Voltage	V_{EBO}	5	V
Collector Current - Continuous	I_C	500	mA
Collector Power Dissipation	P_C	300	mW
Junction Temperature	T_j	150	$^\circ C$
Storage Temperature	T_{stg}	-55 to 150	$^\circ C$

■ Electrical Characteristics $T_a = 25^\circ C$

Parameter	Symbol	Testconditions	Min	Typ	Max	Unit
Collector - base breakdown voltage	V_{CB0}	$I_C = 100 \mu A, I_E = 0$	40			V
Collector - emitter breakdown voltage	V_{CEO}	$I_C = 0.1 mA, I_B = 0$	25			V
Emitter - base breakdown voltage	V_{EBO}	$I_E = 100 \mu A, I_C = 0$	5			V
Collector cut - off current	I_{CBO}	$V_{CB} = 40 V, I_E = 0$			0.1	μA
Collector cut -off current	I_{CEO}	$V_{CE} = 20 V, I_B = 0$			1	μA
Emitter cut - off current	I_{EBO}	$V_{EB} = 5 V, I_C = 0$			0.1	μA
DC current gain	h_{FE}	$V_{CE} = 1 V, I_C = 50 mA$	120		400	
		$V_{CE} = 1 V, I_C = 500 mA$	40			
Collector - emitter saturation voltage	$V_{CE(sat)}$	$I_C = 500 mA, I_B = 50 mA$			0.6	V
Base - emitter saturation voltage	$V_{BE(sat)}$	$I_C = 500 mA, I_B = 50 mA$			1.2	V
Transition frequency	f_T	$V_{CE} = 6 V, I_C = 20 mA, f = 30 MHz$	150			MHz

■ Classification of $h_{FE}(1)$

Type	KST9013	KST9013-L	KST9013-H	KST9013-J
Range	200-350	120-200	144-202	300-400
Marking	J3			

KST9013

Typical Characteristics

