


FEATURES

- Epitaxial planar die construction.
- Complementary PNP type available (MMBT3906).
- Collector Current Capability $I_{CM} = 200\text{mA}$.
- Collector-emitter Voltage $V_{CEO}=40\text{V}$.



SOT-23		
Dim	Min	Max
A	2.70	3.10
B	1.10	1.50
C	1.0 Typical	
D	0.4 Typical	
E	0.35	0.48
G	1.80	2.00
H	0.02	0.1
J	0.1 Typical	
K	2.20	2.60

All Dimensions in mm

APPLICATIONS

- General switching and amplification

ORDERING INFORMATION

Type No.	Marking	Package Code
MMBT3904LT1	1AM	SOT-23

MAXIMUM RATING @ $T_a=25^\circ\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	Value	UNIT
V_{CBO}	collector-base voltage	open emitter	60	V
V_{CEO}	collector-emitter voltage	open base	40	V
V_{EBO}	emitter-base voltage	open collector	6	V
I_C	collector current (DC)		100	mA
I_{CM}	peak collector current		200	mA
I_{BM}	peak base current		100	mA
P_{tot}	total power dissipation	$T_{amb} \leq 25^\circ\text{C}$	250	mW
T_{stg}	storage temperature		-65 to +150	°C
T_j	junction temperature		150	°C
T_{amb}	operating ambient temperature		-65 to +150	°C

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
I_{CBO}	collector cut-off current	$I_E = 0$; $V_{CB} = 30$ V	-	50	nA
I_{EBO}	emitter cut-off current	$I_C = 0$; $V_{EB} = 6$ V	-	50	nA
h_{FE}	DC current gain	$V_{CE} = 1$ V; $I_C = 0.1$ mA $I_C = 1$ mA $I_C = 10$ mA $I_C = 50$ mA $I_C = 100$ mA	60 80 100 60 30	- - 300 - -	
$V_{CE(sat)}$	collector-emitter saturation voltage	$I_C = 10$ mA; $I_B = 1$ mA	-	200	mV
		$I_C = 50$ mA; $I_B = 5$ mA	-	300	mV
$V_{BE(sat)}$	base-emitter saturation voltage	$I_C = 10$ mA; $I_B = 1$ mA	650	850	mV
		$I_C = 50$ mA; $I_B = 5$ mA	-	950	mV
C_{obo}	Output Capacitance	$I_E = I_e = 0$; $V_{CB} = 5$ V; $f = 1$ MHz	-	4	pF
C_{ibo}	Input Capacitance	$I_C = I_c = 0$; $V_{BE} = 500$ mV; $f = 1$ MHz	-	8	pF
f_T	transition frequency	$I_C = 10$ mA; $V_{CE} = 20$ V; $f = 100$ MHz	300	-	MHz
F	noise figure	$I_C = 100$ mA; $V_{CE} = 5$ V; $R_S = 1$ kΩ; $f = 10$ Hz to 15.7 kHz	-	5	dB
Switching times (between 10% and 90% levels);					
t_d	delay time	$I_{Con} = 10$ mA; $I_{Bon} = 1$ mA; $I_{Boff} = -1$ mA	-	35	ns
t_r	rise time		-	35	ns
t_s	storage time		-	200	ns
t_f	fall time		-	50	ns

Note Pulse test: $tp \leq 300$ ms; $d \leq 0.02$.

TYPICAL CHARACTERISTICS @ $T_a=25^\circ\text{C}$ unless otherwise specified




Fig. 1, Max Power Dissipation vs
Ambient Temperature




Fig. 2, Input and Output Capacitance vs.
Collector-Base Voltage




Fig. 3, Typical DC Current Gain vs
Collector Current




Fig. 4, Typical Collector-Emitter
Saturation Voltage vs. Collector Current




Fig. 5, Typical Base-Emitter
Saturation Voltage vs. Collector Current

Device	Package	Shipping
MMBT3904LT1	SOT-23	3000/Tape&Reel