


## GF Series Low Impedance

### Features

- Used in mother board, computer peripheral, etc.
- Endurance 3000 ~ 5000 Hrs at 105 °C
- Safety vent construction design.
- RoHS Compliant




### Specifications

Item	Performance Characteristics														
Operating Temperature Range	-55 to +105°C														
Rated Voltage Range	6.3 to 100 VDC														
Capacitance Range	4.7 to 6800 μF														
Capacitance Tolerance	±20% (120Hz, +20°C)														
Leakage Current (+20°C,max.)	I≤0.01 CV or 3 (μA) After 2 minutes whichever is greater measured with rated working voltage applied.														
Dissipation Factor (tan δ , at 20°C , 120Hz)	Working Voltage (VDC)	6.3	10	16	25	35	50	63							
	D.F. (%)max	16	14	12	10	9	8	8							
	For capacitance >1000 μF, add 2% per another 1000 μF.														
Low Temperature Characteristics (at 120Hz)	Impedance ratio max														
	Working Voltage	6.3	10	16	25	35	50	63							
	Z(-25°C) / Z(20°C)	4	3	3	3	3	3	2							
	Z(-40°C) / Z(20°C)	8	6	4	3	3	3	3							
Endurance	For Capacitance > 1000 μF, add 0.5 per another 1000 μF for -25°C/+20°C add 1 per another 1000 μF for -40°C/+20°C														
	Test conditions														
	Duration time	:as right													
	Ambient temperature	:+105°C													
Shelf Life	Applied voltage	:Rated DC working voltage													
	After test requirement at +20°C														
	Capacitance change	:≤ ±20% of the initial measured value													
	Dissipation factor	:≤ 200% of the initial specified value													
	Leakage current	:≤ The initial specified value													
	Test conditions														
	Duration time	:1000Hrs													
	Ambient temperature	:+105°C													
	Applied voltage	:None													
	After test requirement at +20°C:Same limits as Endurance.														
	Pre-treatment for measurements shall be conducted after application of DC working voltage for 30 minutes.														

### Multiplier for Ripple Current vs. Frequency

CAP(μF)\Frequency(Hz)	50(60)	120	400	1K	10K	50K-100K
CAP≤10	0.47	0.59	0.76	0.85	0.97	1.0
10<CAP≤100	0.52	0.62	0.80	0.89	0.97	1.0
100<CAP≤1000	0.58	0.72	0.84	0.90	0.98	1.0
1000<CAP	0.63	0.78	0.87	0.91	0.98	1.0

### Diagram of Dimensions:(unit:mm)



D φ	5	6.3	8	10	13	16	18
F	2.0	2.5	3.5	5.0	5.0	7.5	7.5
d φ	0.5		L<20 0.5	L≥20 0.6		0.6	0.8
a	D<18		D=18		D>18		
	L<35.5	L≥35.5					
	1.5	1.5	2.0	2.0			

## Case Size

WV Cap( $\mu$ F)	6.3				10				$\phi$ DxL(mm)	
	Size	Ripple	Impedance		Size	Ripple	Impedance			
			+20°C	-10°C			+20°C	-10°C		
68					5x11	190	0.70	2.065		
82					5x11	210	0.50	1.475		
100	5x11	200	0.40	1.240	5x11	242	0.31	0.915		
120	5x11	210	0.38	1.178	5x11	261	0.28	0.826		
150	5x11	225	0.35	1.085	6.3x11	300	0.26	0.767		
180	6.3x11	300	0.32	0.992	6.3x11	350	0.22	0.649		
220	6.3x11	360	0.25	0.775	6.3x11	390	0.18	0.531		
270	6.3x11	377	0.24	0.744	6.3x15	460	0.16	0.472		
330	6.3x11	395	0.20	0.465	8x11.5	540	0.11	0.325		
390	8x11.5	576	0.14	0.434	8x11.5	620	0.095	0.280		
470	8x11.5	600	0.095	0.294	8x11.5	750	0.075	0.221		
560	8x16	720	0.087	0.270	8x16	870	0.072	0.212		
680	8x16	800	0.080	0.248	8x20	1010	0.068	0.201		
	10x16	814	0.084	0.260						
820	8x20	970	0.070	0.217	8x20	1030	0.065	0.192		
1000	10x12.5	1000	0.055	0.168	8x20	1220	0.050	0.148		
					10x16	1400	0.042	0.124		
1200	8x20	1150	0.048	0.146	10x20	1560	0.035	0.095		
	10x16	1180	0.050	0.152						
1500	10x20	1400	0.045	0.137	10x20	1670	0.032	0.086		
	10x25	1560	0.043	0.131						
1800	10x20	1500	0.041	0.125	10x25	2000	0.028	0.076		
2200	10x25	1720	0.037	0.113	13x20	2370	0.025	0.065		
	13x20	1890	0.039	0.119						
2700	13x20	2080	0.034	0.095	13x20	2400	0.023	0.060		
3300	13x20	2290	0.026	0.073	13x25	2720	0.021	0.055		
3900	10x30	2450	0.024	0.067	13x30	3000	0.020	0.052		
	13x25	2670	0.022	0.062						
4700	13x30	3200	0.021	0.059	13x35	3450	0.019	0.049		
5600	13x35	3270	0.020	0.056	16x31.5	3460	0.018	0.047		
6800	16x31.5	3490	0.018	0.050	16x31.5	3630	0.016	0.042		

Ripple Current ( mA, rms ) at 105°C 100KHz

Max Impedance (  $\Omega$  ) at 20°C 100KHz

WV Cap( $\mu$ F)	16					25					$\phi$ pDxL(mm)	
	Size	Ripple	Impedance		Size	Ripple	Impedance		+20°C	-10°C		
			+20°C	-10°C			+20°C	-10°C				
39					5x11	210	0.42	1.218				
47	5x11	200	0.40	1.16	5x11	240	0.35	1.015				
56	5x11	220	0.38	1.10	5x11	256	0.31	0.899				
68	5x11	230	0.35	1.02	6.3x11	300	0.28	0.812				
82	5x11	260	0.31	0.90	6.3x11	350	0.24	0.696				
100	6.3x11	360	0.25	0.73	6.3x11	410	0.15	0.435				
120	6.3x11	365	0.23	0.67	6.3x15	490	0.13	0.377				
150	6.3x11	385	0.21	0.61	8x11.5	540	0.11	0.319				
180	8x11.5	520	0.19	0.55	8x11.5	620	0.098	0.2842				
220	8x11.5	575	0.14	0.41	8x11.5	750	0.075	0.218				
270	8x11.5	600	0.12	0.35	8x16	850	0.063	0.183				
330	8x11.5	740	0.08	0.23	8x16	990	0.056	0.1624				
					10x12.5	1010	0.054	0.1566				
390	8x16	790	0.075	0.22	10x12.5	1050	0.051	0.1479				
470	8x16	990	0.062	0.18	8x20	1260	0.045	0.1305				
	10x12.5	1000	0.058	0.17	10x16	1415	0.042	0.1218				
560	8x20	1070	0.057	0.17	10x20	1450	0.040	0.116				
680	8x20	1120	0.055	0.16	10x20	1570	0.035	0.1015				
	10x16	1280	0.052	0.15								
820	10x20	1400	0.048	0.14	10x25	1910	0.032	0.093				
1000	10x20	1840	0.035	0.09	13x20	2340	0.025	0.055				
1200	10x25	1920	0.032	0.08	13x20	2390	0.025	0.055				
1500	10x25	2050	0.030	0.08	13x25	2710	0.023	0.0506				
	13x20	2200	0.029	0.07								
1800	13x20	2380	0.026	0.07	13x30	3150	0.021	0.0462				
2200	13x25	2750	0.022	0.06	13x35	3420	0.018	0.0396				
2700	13x25	3000	0.022	0.06	16x31.5	3480	0.018	0.0396				
3300	13x35	3490	0.018	0.05	16x31.5	3600	0.018	0.0396				
3900	16x25	3520	0.018	0.05								
4700	16x31.5	3770	0.017	0.04								

Ripple Current ( mA, rms ) at 105°C 100KHz

Max Impedance (  $\Omega$  ) at 20°C 100KHz

WV Cap( $\mu$ F)	35					50					$\phi$ DxL(mm)	
	Size	Ripple	Impedance		Size	Ripple	Impedance		+20°C	-10°C		
			+20°C	-10°C			+20°C	-10°C				
22					5x11	220	0.35	1.015				
27					6.3x11	265	0.34	0.986				
33	5x11	230	0.32	0.934	6.3x11	280	0.32	0.928				
39	6.3x11	277	0.31	0.905	6.3x11	300	0.28	0.812				
47	6.3x11	340	0.20	0.584	8x11.5	360	0.20	0.580				
56	6.3x11	375	0.20	0.584	8x11.5	385	0.19	0.551				
68	6.3x11	400	0.19	0.555	8x11.5	400	0.17	0.493				
82	8x11.5	480	0.17	0.496	8x11.5	550	0.12	0.348				
100	8x11.5	560	0.15	0.438	8x11.5	730	0.075	0.2175				
120	8x11.5	585	0.13	0.38	8x16	770	0.073	0.2117				
					10x12.5	790	0.072	0.2088				
150	8x11.5	680	0.11	0.321	10x12.5	870	0.068	0.1972				
180	8x16	810	0.098	0.286	8x20	1060	0.055	0.1595				
					10x16	1090	0.055	0.1595				
220	8x16	1000	0.056	0.164	10x16	1385	0.045	0.1305				
	10x12.5	1060	0.052	0.152								
270	10x16	1190	0.050	0.146	10x20	1500	0.043	0.1247				
330	8x20	1210	0.041	0.12	10x25	1850	0.032	0.0928				
	10x16	1400	0.038	0.111								
390	10x20	1550	0.035	0.102	13x20	1910	0.031	0.0899				
470	10x20	1850	0.034	0.064	13x20	2000	0.030	0.0870				
560	10x25	2040	0.031	0.064	13x20	2150	0.028	0.0812				
680	13x20	2260	0.029	0.061	13x25	2490	0.026	0.0754				
820	13x25	2630	0.021	0.053	13x30	2770	0.025	0.0725				
					16x25	2960	0.024	0.0696				
1000	13x25	2780	0.019	0.048	16x25	3000	0.020	0.0580				
1200	13x30	2950	0.019	0.048								
	16x25	3150	0.018	0.045								
1500	13x35	3350	0.018	0.045								
1800	16x31.5	3600	0.017	0.043								
2200	16x31.5	3670	0.016	0.04								
2700	16x35.5	3750	0.015	0.038								
	18x31.5	3850	0.014	0.035								

Ripple Current ( mA, rms ) at 105°C 100KHz

Max Impedance (  $\Omega$  ) at 20°C 100KHz

Φ DxL(mm)

WV Cap(μF)	63				100			
	Size	Ripple	Impedance		Size	Ripple	Impedance	
			+20°C	-10°C			+20°C	-10°C
4.7					5x11	105	1.60	4.64
5.6					5x11	116	1.49	4.321
6.8					5x11	120	1.45	4.205
10	5x11	135	0.95	2.755	6.3x11	170	0.70	2.03
15	6.3x11	168	0.85	2.465	8x11.5	255	0.61	1.769
18	6.3x11	170	0.82	2.378	8x11.5	270	0.56	1.624
22	6.3x11	250	0.75	2.175	8x11.5	320	0.48	1.392
27	6.3x11	260	0.55	1.595	8x11.5	340	0.39	1.131
33	6.3x11	270	0.38	1.102	8x16	400	0.31	0.899
39	8x11.5	320	0.35	1.015	8x16	425	0.29	0.841
					10x12.5	440	0.27	0.783
47	8x11.5	400	0.22	0.638	10x12.5	450	0.25	0.725
56	8x11.5	420	0.22	0.638	10x16	540	0.21	0.609
68	10x12.5	500	0.20	0.58	10x20	630	0.18	0.522
82	8x16	540	0.17	0.493	10x20	720	0.15	0.435
	10x12.5	570	0.16	0.464				
100	10x12.5	720	0.14	0.406	10x25	890	0.12	0.348
120	8x20	790	0.14	0.406	10x25	900	0.12	0.348
	10x16	835	0.13	0.377	13x20	980	0.11	0.319
150	10x16	900	0.11	0.319	13x20	1100	0.095	0.276
180	10x20	1200	0.095	0.276	13x25	1250	0.078	0.226
220	10x25	1315	0.075	0.218	13x30	1420	0.065	0.189
					16x21	1270	0.075	0.218
270	13x20	1400	0.071	0.206	13x35	1630	0.057	0.165
					16x25	1570	0.058	0.168
330	10x30	1750	0.047	0.136	13x40	1650	0.045	0.131
	13x25	1870	0.045	0.131				
390	13x25	1920	0.044	0.128	16x31.5	1850	0.043	0.125
470	13x30	2225	0.041	0.119	16x35.5	1900	0.032	0.093
	16x21	1970	0.043	0.125	18x31.5	1700	0.038	0.095
560	16x25	2350	0.039	0.098	16x41	2170	0.032	0.08
					18x31.5	2100	0.031	0.078
680	16x31.5	2600	0.035	0.088	18x35.5	2400	0.029	0.073
820	16x31.5	2650	0.031	0.078				
1000	16x35.5	2780	0.026	0.065				
	18x31.5	3230	0.028	0.070				

Ripple Current ( mA, rms ) at 105°C 100KHz

Max Impedance ( Ω ) at 20°C 100KHz