

## Features

- N-Channel, 5V Logic Level Control
- Enhancement mode
- Very low on-resistance  $R_{DS(on)}$  @  $V_{GS}=4.5$  V
- 100% Avalanche test
- Pb-free lead plating; RoHS compliant


$V_{DS}$	40	V
$R_{DS(on),TYP} @ V_{GS}=10$ V	2.7	$m\Omega$
$R_{DS(on),TYP} @ V_{GS}=4.5$ V	3.7	$m\Omega$
$I_D$	125	A

**PDFN5x6**



Halogen-Free

Part ID	Package Type	Marking	Tape and reel information
VS4604AP	PDFN5x6	4604AP	3000PCS/Reel



## Maximum ratings, at $T_A=25^\circ C$ , unless otherwise specified

Symbol	Parameter	Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage	40	V
$V_{GS}$	Gate-Source voltage	$\pm 20$	V
$I_S$	Diode continuous forward current	$T_C=25^\circ C$	A
$I_D$	Continuous drain current @ $V_{GS}=10V$	$T_C=25^\circ C$	A
		$T_C=100^\circ C$	A
$I_{DSM}$	Continuous drain current @ $V_{GS}=10V$	$T_A=25^\circ C$	A
		$T_A=70^\circ C$	A
$I_{DM}$	Pulse drain current tested ①	$T_c=25^\circ C$	A
$EAS$	Avalanche energy, single pulsed ②	72	$mJ$
$P_D$	Maximum power dissipation	$T_c=25^\circ C$	W
$P_{DSM}$	Maximum power dissipation ③	$T_A=25^\circ C$	W
MSL		Level 1	
$T_{STG}, T_J$	Storage and Junction Temperature Range	-55 to 150	$^\circ C$

## Thermal Characteristics

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	2	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	30	$^\circ C/W$



Vanguard  
Semiconductor

VS4604AP

40V/125A N-Channel Advanced Power MOSFET

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
<b>Static Electrical Characteristics @ <math>T_j=25^\circ\text{C}</math> (unless otherwise stated)</b>						
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$	40	--	--	V
$I_{\text{DSS}}$	Zero Gate Voltage Drain Current	$V_{\text{DS}}=40\text{V}, V_{\text{GS}}=0\text{V}$	--	--	1	$\mu\text{A}$
	Zero Gate Voltage Drain Current( $T_j=125^\circ\text{C}$ )	$V_{\text{DS}}=40\text{V}, V_{\text{GS}}=0\text{V}$	--	--	100	$\mu\text{A}$
$I_{\text{GSS}}$	Gate-Body Leakage Current	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$	--	--	$\pm 100$	nA
$V_{\text{GS}(\text{TH})}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$	1.3	1.6	2.4	V
$R_{\text{DS}(\text{ON})}$	Drain-Source On-State Resistance④	$V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}$	--	2.7	4	$\text{m}\Omega$
$R_{\text{DS}(\text{ON})}$	Drain-Source On-State Resistance④	$V_{\text{GS}}=4.5\text{V}, I_{\text{D}}=15\text{A}$	--	3.7	5	$\text{m}\Omega$
<b>Dynamic Electrical Characteristics @ <math>T_j = 25^\circ\text{C}</math> (unless otherwise stated)</b>						
$C_{\text{iss}}$	Input Capacitance	$V_{\text{DS}}=20\text{V}, V_{\text{GS}}=0\text{V}, f=1\text{MHz}$	4500	5015	5500	pF
$C_{\text{oss}}$	Output Capacitance		350	440	550	pF
$C_{\text{rss}}$	Reverse Transfer Capacitance		300	380	450	pF
$R_g$	Gate Resistance	$f=1\text{MHz}$	--	2.3	--	$\Omega$
$Q_g$	Total Gate Charge	$V_{\text{DS}}=20\text{V}, I_{\text{D}}=20\text{A}, V_{\text{GS}}=10\text{V}$	--	83	--	nC
$Q_{\text{gs}}$	Gate-Source Charge		--	16	--	nC
$Q_{\text{gd}}$	Gate-Drain Charge		--	17	--	nC
<b>Switching Characteristics</b>						
$t_{\text{d(on)}}$	Turn-on Delay Time	$V_{\text{DD}}=20\text{V}, I_{\text{D}}=20\text{A}, R_{\text{G}}=3\Omega, V_{\text{GS}}=10\text{V}$	--	15.7	--	nS
$t_r$	Turn-on Rise Time		--	6.5	--	nS
$t_{\text{d(off)}}$	Turn-Off Delay Time		--	56	--	nS
$t_f$	Turn-Off Fall Time		--	12	--	nS
<b>Source- Drain Diode Characteristics@ <math>T_j = 25^\circ\text{C}</math> (unless otherwise stated)</b>						
$V_{\text{SD}}$	Forward on voltage	$I_{\text{SD}}=20\text{A}, V_{\text{GS}}=0\text{V}$	--	0.8	1.2	V
$t_{\text{rr}}$	Reverse Recovery Time	$T_j=25^\circ\text{C}, I_{\text{SD}}=20\text{A}, V_{\text{GS}}=0\text{V}$ $dI/dt=500\text{A}/\mu\text{s}$	--	18	--	nS
$Q_{\text{rr}}$	Reverse Recovery Charge		--	40	--	nC

NOTE:

- ① Repetitive rating; pulse width limited by max junction temperature.
- ② Limited by  $T_{\text{Jmax}}$ , starting  $T_j = 25^\circ\text{C}$ ,  $L = 0.5\text{mH}$ ,  $R_g = 25\Omega$ ,  $I_{\text{AS}} = 17\text{A}$ ,  $V_{\text{GS}} = 10\text{V}$ . Part not recommended for use above this value
- ③ The power dissipation  $P_{\text{DSM}}$  is based on  $R_{\theta\text{JA}}$  and the maximum allowed junction temperature of  $150^\circ\text{C}$ .
- ④ Pulse width  $\leq 300\mu\text{s}$ ; duty cycle  $\leq 2\%$ .



Vanguard  
Semiconductor

VS4604AP

40V/125A N-Channel Advanced Power MOSFET

## Typical Characteristics




Fig1. Typical Output Characteristics




Fig2.  $V_{GS(TH)}$  Gate -Source Voltage Vs. $T_j$




Fig3. Typical Transfer Characteristics




Fig4. Normalized On-Resistance Vs.  $T_j$




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area




Vanguard  
Semiconductor


**VS4604AP**

**40V/125A N-Channel Advanced Power MOSFET**


## Typical Characteristics




**Fig7.** Typical Capacitance Vs.Drain-Source Voltage




**Fig8.** Typical Gate Charge Vs.Gate-Source Voltage



**Fig9.** Normalized Maximum Transient Thermal Impedance



**Fig10.** Unclamped Inductive Test Circuit and waveforms



**Fig11.** Switching Time Test Circuit and waveforms




Vanguard  
Semiconductor

**VS4604AP**

**40V/125A N-Channel Advanced Power MOSFET**

### Marking Information



1st line: Vanguard Code (Vs), Vanguard Logo

2nd line: Part Number (4604AP)

3rd line: Date code (LOTYWW)

LOT: Wafer Lot Number

Y: Year Code, e.g. E means 2017

WW: Week Code




Vanguard  
Semiconductor

VS4604AP

40V/125A N-Channel Advanced Power MOSFET

## PDFN5×6 Package Outline Data



DIMENSIONS ( unit : mm )

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	0.90	1.02	1.10	D	4.90	4.98	5.10
D <sub>1</sub>	4.80	4.89	5.00	E	6.00	6.11	6.20
E <sub>1</sub>	5.65	5.74	5.85	e	3.72	3.80	3.92
e <sub>1</sub>	--	0.54	--	e <sub>2</sub>	--	1.27	--
f	--	3.82	--	f <sub>1</sub>	0.31	0.37	0.51
f <sub>2</sub>	--	0.64	--	H	--	3.15	--
H <sub>1</sub>	0.59	0.63	0.79	H <sub>2</sub>	0.26	0.28	0.32
L	3.38	3.45	3.58	L <sub>1</sub>	--	1.39	--
v	--	0.13	--	w	0.64	0.68	0.84
y	--	0.34	--		--		--

## Customer Service

### Sales and Service:

[sales@vgsemi.com](mailto:sales@vgsemi.com)

**Vanguard Semiconductor CO., LTD**

**TEL:** (86-755) -26902410

**FAX:** (86-755) -26907027

**WEB:** [www.vgsemi.com](http://www.vgsemi.com)