Noise Suppression Products/EMI Suppression Filters > Common Mode Choke Coil > Wire Wound Type for Large Current

Data Sheet

Common Mode Choke Coil Wire Wound Type for Large Current DLW5AT/DLW5BT Series (2014/2020 Size) Dimensions DLW5BT Series DLW5BT Series



Impedance-Frequency Characteristics (Main Items) DLW5AT_SQ2 Series



Equivalent Circuit



isions			
	DLW5BT	Series	
<u>1.7±0.3</u> 0.5±0.3	(Top)	0.5 min. 0.7 mi	
1.3±0.3	(1) (2) (Bot (4) (3) 1.3±0.3 0.9±0.3		

Impedance-Frequency Characteristics (Main Items) DLW5BT_SQ2 Series



Packaging

Code	Packaging	Minimum Quantity		
L	180mm Embossed Tape	700		
к	330mm Embossed Tape	2500		
В	Bulk(Bag)	100		

Continued on the following page.

• This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.

▲Note:

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Data Sheet

Continued from the preceding page.

■ Rated Value (□: packaging code)

Part Number	Common Mode Impedance (at 100MHz/20°C)	Rated Current	Rated Voltage	Insulation Resistance (min.)	Withstand Voltage	DC Resistance	Operating Temperature Range
DLW5ATN111SQ2	110ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.020ohm max.	-40 to +85°C
DLW5ATN401SQ2	400ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.034ohm max.	-40 to +85°C
DLW5ATN501SQ2	500ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.056ohm max.	-40 to +85°C
DLW5ATN851SQ2	850ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.073ohm max.	-40 to +85°C
DLW5ATN272SQ2	2700ohm (Typ.)	1000mA	50Vdc	10M ohm	125Vdc	0.12ohm max.	-40 to +85°C
DLW5BTM101SQ2	100ohm (Typ.)	6000mA	50Vdc	10M ohm	125Vdc	0.013ohm max.	-40 to +85°C
DLW5BTM251SQ2	250ohm (Typ.)	5000mA	50Vdc	10M ohm	125Vdc	0.020ohm max.	-40 to +85°C
DLW5BTM501SQ2	500ohm (Typ.)	4000mA	50Vdc	10M ohm	125Vdc	0.027ohm max.	-40 to +85°C
DLW5BTM102SQ2	1000ohm (Typ.)	2000mA	50Vdc	10M ohm	125Vdc	0.034ohm max.	-40 to +85°C
DLW5BTM142SQ2	1400ohm (Typ.)	1500mA	50Vdc	10M ohm	125Vdc	0.056ohm max.	-40 to +85°C

Number of Circuit: 1

Derating of Rated Current

In operating temperature exceeding +60°C, derating of current is necessary for DLW5AT series. Please apply the derating curve shown in chart according to the operating temperature.



Continued on the following page.

• This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

2



•This data sheet is applied for CHIP COMMON MODE CHOKE COIL used for General Electronics equipment for your design.

/Note:

1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.