

TF207P P-Channel -20V(D-S) MOSFET

$V_{(BR)DSS}$	$R_{DS(on)}$	I_D Max
-20V	0.017 Ω @ -4.5V	-6.0A
	0.021 Ω @ -2.5V	


FEATURE

- TrenchFET Power MOSFET
- Excellent $R_{DS(on)}$
- Low Gate Charge
- High Power and Current Handling Capability
- Surface Mount Package

APPLICATION


- Load Switch
- Power Management

SOT-23-3L




- 1.GATE
- 2.SOURCE
- 3.DRAIN

Equivalent Circuit



MARKING



Y :year code W :week code

ABSOLUTE MAXIMUM RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	-6	A
Pulsed Drain Current (note 1)	I_{DM}	-25	A
Thermal Resistance from Junction to Ambient (note 2)	$R_{\theta JA}$	100	$^\circ\text{C/W}$
Junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature	T_{STG}	-55~+150	$^\circ\text{C}$
Lead Temperature for Soldering Purposes(1/8" from case for 10 s)	T_L	260	$^\circ\text{C}$

MOSFET ELECTRICAL CHARACTERISTICS

T_a =25 °C unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
STATIC CHARACTERICTISCS						
Drain-source breakdown voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D =250μA	-20			V
Zero gate voltage drain current	I _{DSS}	V _{DS} =-18V, V _{GS} = 0V			-100	nA
Gate-body leakage current	I _{GSS}	V _{GS} =±12V, V _{DS} = 0V			±100	nA
Gate threshold voltage (note 3)	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250μA	-0.5		-1.0	V
Drain-source on-resistance (note 3)	R _{DS(on)}	V _{GS} =-4.5V, I _D =-6A	15	17	23	mΩ
		V _{GS} =-2.5V, I _D =-5A	17	21	32	mΩ
Forward tranconductance (note 3)	g _{FS}	V _{DS} =-5V, I _D =-6A		17		S
Diode forward voltage (note 3)	V _{SD}	I _S =-2.0A, V _{GS} = 0V			-1.0	V
DYNAMIC CHARACTERICTISCS (note4)						
Input Capacitance	C _{iss}	V _{DS} =-10V, V _{GS} =0V, f =1MHz		2100		pF
Output Capacitance	C _{Oss}			498		pF
Reverse Transfer Capacitance	C _{rss}			300		pF
SWITCHING CHARACTERICTISCS (note 4)						
Turn-on delay time	t _{d(on)}	V _{DD} =-10V, R _L =10Ω, V _{GS} =-4.5V, R _{GEN} =6Ω		25		ns
Turn-on rise time	t _r			30		ns
Turn-off delay time	t _{d(off)}			70		ns
Turn-off fall time	t _f			50		ns
Total Gate Charge	Q _g	V _{DS} =-10V, V _{GS} =-4.5V, I _D =-6A		17		nC
Gate-Source Charge	Q _{gs}			4.1		nC
Gate-Drain Charge	Q _{gd}			4.3		nC

Notes :

- 1.Repetitive rating: Pulse width limited by maximum junction temperature
- 2.Surface Mounted on FR4 board, t ≤10 sec.
3. Pulse test : Pulse width ≤300μs, duty cycle ≤2%.
4. Guaranteed by design, not subject to production.

Typical Electrical and Thermal Characteristics




Figure 1 Switching Test Circuit




Figure 2 Switching Waveforms




Figure 3 Power Dissipation




Figure 4 Drain Current




Figure 5 Output Characteristics










Figure 6 Drain-Source On-Resistance






Figure 13 Safe Operation Area






Figure 14 Normalized Maximum Transient Thermal Impedance

SOT-23-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

SOT-23-3L Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.