

#### NOT RECOMMENDED FOR NEW DESIGN USE <u>AP431SHA(B)N1TR-G1</u> FOR ZXRE250B(A)SA-7 USE <u>AP431SHA(B)NTR-G1</u>FOR ZXRE252B(A)SA-7



## ZXRE250 / ZXRE252

VERY LOW CATHODE CURRENT ADJUSTABLE PRECISION SHUNT REGULATOR

ZXRE250

**SOT23** 

#### Description

The ZXRE250 and ZXRE252 are three-terminal adjustable shunt regulators that offer excellent temperature stability and output current handling capability up to 100mA. The output voltage may be set to any chosen voltage between 2.5V and 36V by selection of two external divider resistors.

ZXRE250 has the same electrical specifications as the industry standard '431 except it features a very-low minimum cathode current for regulation. The typical value of  $40\mu$ A makes the parts ideal for very low-power applications.

The devices can be used as a replacement for zener diodes in many applications requiring an improvement in zener performance. The ZXRE250/2 is available in two grades with initial tolerances of 1% and 0.5% for the A and B grades respectively.

#### Features

- Minimum Cathode Current for Regulation: 40µA (typ)
- Temperature Range: -40°C to +125°C
- Reference Voltage Tolerance at +25°C ZXRE250A: 2.495V ± 1.0% ZXRE250B: 2.495V ± 0.5%
- Low Output Noise
- 0.2Ω Typical Output Impedance
- Sink Current Capability: 0.065mA to 100mA
- Adjustable Output Voltage: VREF to 36V
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

#### Applications

- Optocoupler Linearisers
- Shunt Regulators
- Improved Zener

Notes

Variable Reference

No purposely added lead, Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



**Pin Assignments** 



#### Absolute Maximum Ratings (Note 4) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter		Rating	Unit	
V <sub>KA</sub>	Cathode Voltage		40	V	
I <sub>KA</sub>	Continuous Cathode Current		150	mA	
I <sub>REF</sub>	Reference Input Current		-0.050 to +10	mA	
TJ	Operating Junction Temperature		+150	°C	
T <sub>ST</sub>	Storage Temperature		-55 to +150	°C	
D	Power Dissipation (Notes 5 & 6)	SOT23	330	mW	
PD		SOT25	500	mW	

4. Operation above the absolute maximum rating may cause device failure. Operation at the absolute maximum ratings, for extended periods, may reduce Notes: device reliability. Unless otherwise stated voltages specified are relative to the ANODE pin.

5. T<sub>J</sub>, max =  $+150^{\circ}$ C

6. Ratings apply to ambient temperature at +25°C.

## Recommended Operating Conditions (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Max	Unit
V <sub>KA</sub>	Cathode Voltage	V <sub>REF</sub>	36	V
I <sub>KA</sub>	Cathode Current	0.065	100	mA
T <sub>A</sub>	Operating Ambient Temperature	-40	+125	°C

#### Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Test C	Min	Тур	Max	Unit	
V <sub>REF</sub>	Reference Voltage	V <sub>KA</sub> = V <sub>REF</sub> ,	ZXRE250A	2.470	2.495	2.520	V
		$I_{KA} = 10 mA$	ZXRE250B	2.482	2.495	2.507	V
V <sub>DEV</sub>	Deviation of Reference Voltage Over Full Temperature Range (Note 7)	$V_{KA} = V_{REF},$	$T_A = 0$ to +70°C	_	6	16	mV
			T <sub>A</sub> = -40 to +85°C	_	14	34	mV
			T <sub>A</sub> = -40 to +125°C	-	14	34	mV
$\Delta V_{REF}$	Ratio of the Change in Reference	$l_{KA} = 10mA$	$V_{KA} = 10V$ to $V_{REF}$	_	-1.4	-2.7	mV/V
ΔV <sub>KA</sub>	Voltage to the Change in Cathode Voltage		V <sub>KA</sub> = 36V to 10V	_	-1	-2	mV/V
I <sub>REF</sub>	Reference Input Current	I <sub>KA</sub> = 10mA, R1 = 10KΩ, R2 = ∞			1	4	μA
$\Delta I_{REF}$	I <sub>REF</sub> Deviation Over Full Temperature Range (Note 7)	I <sub>KA</sub> = 10mA, R1 = 10KΩ. R2 = ∞	$T_{A} = 0$ to +70°C	_	0.8	1.2	μA
			T <sub>A</sub> = -40 to +85°C	_	0.8	2.5	μA
			T <sub>A</sub> = -40 to +125°C	—	0.8	2.5	μA
I <sub>KA(MIN)</sub>	Minimum Cathode Current for Regulation	V <sub>KA</sub> = V <sub>REF</sub>		—	40	65	μA
IKA(OFF)	Off-State Current	$V_{KA} = 36V, V_{REF} = 0V$		_	0.05	0.5	μA
Z <sub>KA</sub>	Dynamic Output Impedance (Note 8)	$V_{KA} = V_{REF}, f = 0Hz$		—	0.2	0.5	Ω
θJA	Thormal Pasistones Junction to Ambient	SOT23		_	380	_	°C/W
	Thermal Resistance Junction to Ambient	SOT25		_	250	_	°C/W

Notes:

7. Deviation of  $V_{DEV}$ , and  $\Delta I_{REF}$  are defined as the maximum variation of the values over the full temperature range. 8. Derivation of  $Z_{KA}$  on following page.



Τ2

V<sub>DEV</sub> = Vmax - Vmin

Temperature

Vmax

Vmin

#### Electrical Characteristics (continued) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

The average temperature coefficient of the reference input voltage  $\alpha V_{REF}$  is defined as:

$$\left| \alpha V_{\text{REF}} \right| = \frac{\left( \frac{V_{\text{DEV}}}{V_{\text{REF}} @ 25^{\circ} \text{C}} \right) \times 10^{6}}{T2 - T1} \text{ ppm/}^{\circ} \text{C}$$

Where:

T2 - T1 = full temperature change.

 $\alpha V_{\mathsf{REF}}$  can be positive or negative depending on whether the slope is positive or negative.

Note : 8. The dynamic output impedance, Rz, is defined as:

$$\left| Z_{KA} \right| = \frac{\Delta V_{KA}}{\Delta I_{KA}}$$

When the device is programmed with two external resistors R1 and R2, the dynamic output impedance of the overall circuit, is defined as:

$$|Z'| = \frac{\Delta V}{\Delta I} \approx |Z_{KA}| \left(1 + \frac{R1}{R2}\right)$$

## **Test Circuits**



ZXRE250 / ZXRE252 Document number: DS35228 Rev. 7 - 3

Figure 3 Test Circuit for IOFF



# **Typical Performance Characteristics**



Document number: DS35228 Rev. 7 - 3



# Typical Performance Characteristics (Continued)





# Typical Performance Characteristics (Cont.)





# Typical Performance Characteristics (Cont.)



Test Circuit for Curves B, C, D

The device is stable under all conditions with a load capacitance not exceeding 50pF. The device is stable under all conditions with a load capacitance between 5nF and 20nF. The device is stable under all conditions with a load capacitance exceeding 300nF. With a cathode current not exceeding 5mA, the device is stable with any load capacitance.



# **Application Information**





## Ordering Information





2.80

0.95

3.00

0.15

Тур

0.40

1.30

2.40

0.915

0.535

1.83

2.90

0.05

0.975

1.025

0.55

0.40

0.110

8°

## **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25





# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25





#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com