



SLIDE SHELL LOCK

SLIDE SHELL OPEN




RECOMMENDED P8 LAYOUT
TOLERANCES:±0.05

PIN NO.	PIN Assigning:
PIN1	DATA2
PIN2	CD/DAT3
PIN3	CMD
PIN4	VDD
PIN5	CLK
PIN6	VSS
PIN7	DATO
PIN8	DATI

序号	名称	材质	数量
1	外壳	SUS304	1PCS
2	胶芯主体	LCP	1PCS
3	端子	C5210	1SET=8PCS
4	固定片	C5191	2PCS
5	锁卡片	C5191	2PCS

REVISION NO.	REV. NO.	DESCRIPTION	DATE	MARK
1		ADD SPECIFICATIONS AND UPDATE DRAWING BY FOLLOWING PRODUCT	20160410	
2				
3				



台湾汉博电子科技有限公司
Taiwan Han Bo Electronic Technology Co.,Ltd.

PRODUCT NAME: 扣盖式 1.5SH
PRODUCT NO.: TF-014-H18

DRAWING NO.:
DRAWING NO.:
DRAWING NO.:

SCALE: 1:1
SCALE: 1:1
SCALE:

DATE: 2014.9
DATE:
DATE:

DATE: 2014.9
DATE:
DATE:

NOTE:
1. MATERIAL: 1.1 HOUSING: High thermoplastic, UL 94V-0
COLOR: BLACK.
1.2 SHELL: STAINLESS STEEL
1.3 TERMINAL : COPPER ALLOY
1.4 PEG : COPPER ALLOY
1.5 HINGE : COPPER ALLOY
2. FINISH:
2.1 TERMINAL:
CONTACTG AREA: SELECTIVE GOLD OVER NICKEL
SOLDER AREA: 50μ"MIN. SN OVER NICKEL
2.2 PEG AND HINGE: TIN OVER NICKEL
3. RATING:
OPERATING VOLTAGE: 30V
CURRENT RATING: 1.0A
CONTACT RESISTANCE: 50mΩ max.
INSULATION RESISTANCE: 100MΩ MIN. 100V DC
DURABILITY: 5000 CYCLES
OPERATING TEMPERATURE: -20℃~+85℃

DIMENSIONS INT:	UNLESS OTHERWISE SPECIFIABLE	TOLERANCE
X, Y, Z	±	0.38
X, X.X, ±	±	0.25
X, X.X, ±	±	0.10
ANGLE: ±	±	1°

PRODUCT NAME:	PRODUCT NO.:	DRAWING NO.:	SCALE:	DATE:
扣盖式 1.5SH	TF-014-H18		1:1	2014.9