

## **N-Channel Enhancement Mode MOSFET**

#### **Feature**

• 30V/2.0A,  $R_{DS(ON)} = 35m\Omega(MAX)$  @ $V_{GS} = 10V$ .

 $R_{DS(ON)} = 40 m\Omega(MAX)$  @ $V_{GS} = 4.5V$ .


 $R_{DS(ON)} = 55m\Omega(MAX)$  @ $V_{GS} = 2.5V$ .

- Super High dense cell design for extremely low RDS(ON).
- Reliable and Rugged.
- SC-59 for Surface Mount Package.

## **Applications**

- Power Management
- Portable Equipment and Battery Powered Systems.





# Absolute Maximum Ratings TA=25 °C Unless Otherwise noted

Parameter	Symbol	Limit	Units	
Drain-Source Voltage	$V_{DS}$	30	V	
Gate-Source Voltage	$V_{GS}$	±12	V	
Drain Current-Continuous	$I_D$	2.0	A	


### Electrical Characteristics TA=25°C Unless Otherwise noted

Parameter	Symbol	Test Conditions	Min	Typ.	Max	Units	
Off Characteristics							
Drain to Source Breakdown Voltage	BVDSS	VGS=0V, ID=250μA	30	-	-	V	
Zero-Gate Voltage Drain Current	IDSS	VDS=30V, VGS=0V	-	-	1	μΑ	
Gate Body Leakage Current, Forward	IGSSF	VGS=12V, VDS=0V	-	-	100	nA	
Gate Body Leakage Current, Reverse	IGSSR	VGS=-12V, VDS=0V	-	-	-100	nA	
On Characteristics							
Gate Threshold Voltage	VGS(th)	VGS= VDS, ID=250μA	0.6	-	1.5	V	
Static Drain-source	RDS(ON)	VGS =10V, ID =5.8A	-	30	35	$m\Omega$	
On-Resistance		VGS =4.5V, ID =5A	-	33	40	$m\Omega$	
		VGS =2.5V, ID =4A	-	45	55	$m\Omega$	
Drain-Source Diode Characteristics and Maximum Ratings							
Drain-Source Diode Forward Voltage	VSD	VGS =0V, IS=1.25A			1.2	V	

Dynamic							
Qg	Total Gate Charge	VDs=15V,VGs=10V,ID=2A		8.5	12	пC	
Qgs	Gate-Source Charge			1.1			
Qgd	Gate-Drain Charge			1.8			
ton	Turn-on Time	VDD=15V,ID=2A,VGS=10V,RG=6 $\Omega$			40	nS	
td(ON)	Turn-on Delay time			11			
tr	Turn-on Rise Time			17			
Td(off)	Turn-off Delay Time			37			
tf	Turn-off Fall Time			20			
toff	Turn-off Time				60		



# **Typical Characteristics**







Figure 1. Output Characteristics

Figure 2. Transfer Characteristics







Figure 3. Gate Threshold Variation with Temperature

Figure 4. On-Resistance Variation with Temperature






Figure 5. On-Resistance vs. Gate-to-Source Voltage Voltage

Figure 6. Source-Drain Diode Forward