



RFCPL0605 Series – RoHS Compliance

MULTILAYER CERAMIC COUPLER

Halogens Free Product

2.4 GHz / 5 GHz Dual Band RF Application

P/N: RFCPL0605030L6T

*Contents in this sheet are subject to change without prior notice

Approval sheet



FEATURES


- 1. Miniature footprint: 0.65 X 0.50 X 0.35 mm³
- 2. Low Profile Thickness
- 3. Low Insertion loss

APPLICATIONS

1. 2.4GHz / 5GHz band RF Application

CONSTRUCTION

Top view




| PIN | Connection | ction PIN Conne | |
|-----|------------|-----------------|-------|
| P1 | Coupling | P3 Output | |
| P2 | Terminate | P4 | Input |

DIMENSIONS

| Figure | Symbol | Dimension (mm) |
|----------------|--------|----------------|
| L T | L | 0.65 ± 0.10 |
| | W | 0.50 ± 0.10 |
| Top view ≥ ■ V | Т | 0.35 ± 0.05 |
| Side view | A | 0.225±0.10 |
| Side view | В | 0.20 ± 0.05 |
| | С | 0.10 ± 0.05 |
| Bottom view | D | 0.25 ± 0.05 |
| t | E | 0.025±0.025 |

ELECTRICAL CHARACTERISTICS



SOLDER LAND PATTERN

Figure Figure unit: mm Line width to be designed to match 50 Ω characteristic impedance, depending on PCB material and thickness.



Approval sheet RELIABILITY TEST

| Test item | Test condition / Test method | Specification |
|------------------------------|--|---|
| Solderability | *Solder bath temperature : $235 \pm 5^{\circ}C$ | At least 95% of a surface of each terminal |
| JIS C 0050-4.6 | *Immersion time $: 2 \pm 0.5$ sec | electrode must be covered by fresh solder. |
| JESD22-B102D | Solder:Sn3Ag0.5Cu for lead-free | |
| Leaching | *Solder bath temperature : $260 \pm 5^{\circ}C$ | Loss of metallization on the edges of each |
| (Resistance to | *Leaching immersion time \div 30 \pm 0.5 sec | electrode shall not exceed 25%. |
| dissolution of | Solder : SN63A | |
| metallization) | | |
| IEC 60068-2-58 | | |
| Resistance to soldering heat | *Preheating temperature : $120~150^{\circ}$ C, | No mechanical damage. |
| JIS C 0050-5.4 | 1 minute. | Electrical specification shall satisfy the |
| | *Solder temperature : 270±5°C | descriptions in electrical characteristics under |
| | *Immersion time : 10±1 sec | the operational temperature range within -40 $\sim 85^{\circ}$ C. |
| | Solder : Sn3Ag0.5Cu for lead-free | Loss of metallization on the edges of each |
| | Measurement to be made after keeping at | electrode shall not exceed 25%. |
| | room temperature for 24±2 hrs | |
| Drop Test | *Height : 75 cm | No mechanical damage. |
| JIS C 0044 | *Test Surface : Rigid surface of concrete or | Electrical specification shall satisfy the |
| Customer's specification. | steel. | descriptions in electrical characteristics under |
| | *Times : 6 surfaces for each units ; 2 times | the operational temperature range within -40 |
| | for each side. | ~ 85°C. |
| Vibration | *Frequency : 10Hz~55Hz~10Hz(1min) | No mechanical damage. |
| JIS C 0040 | | Electrical specification shall satisfy the |
| | *Total amplitude : 1.5mm | descriptions in electrical characteristics under |
| | *Test times : 6hrs.(Two hrs each in three | the operational temperature range within -40 |
| | mutually perpendicular directions) | ~ 85°C. |
| Adhesive Strength | *Pressurizing force : | No remarkable damage or removal of the |
| of Termination | 2N(≦0603 ; 1.6 x 0.8 mm) ; | termination. |
| JIS C 0051- 7.4.3 | 10N(>0603 ; 1.6 x 0.8 mm) | |
| | *Test time : 5±1 sec | |
| Bending test | The middle part of substrate shall be | No mechanical damage. |
| JIS C 0051- 7.4.1 | pressurized by means of the pressurizing rod | Electrical specification shall satisfy the |
| | at a rate of about 1 mm/s per second until the | descriptions in electrical characteristics under |
| | deflection becomes 1mm/s and then pressure | the operational temperature range within -40 |
| | shall be maintained for 5 ± 1 sec. | ~ 85°C. |
| | Measurement to be made after keeping at | |
| | room temperature for 24±2 hours | |



Approval sheet

| Temperature cycle | 1. 30±3 minutes at -40°C±3°C, | No mechanical damage. | |
|---------------------|--|--|--|
| JIS C 0025 | 2. 10~15 minutes at room temperature, 3. 30±3 minutes at +85°C±3°C, | Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. | |
| | 10~15 minutes at room temperature, Total 100 continuous cycles | | |
| | Measurement to be made after keeping at room temperature for 24±2 hrs | | |
| High temperature | *Temperature : 85°C±2°C | No mechanical damage. | |
| JIS C 0021 | *Test duration : 1000+24/-0 hours | Electrical specification shall satisfy the | |
| | Measurement to be made after keeping at room temperature for 24±2 hrs | descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. | |
| Humidity | *Humidity : 90% to 95% R.H. | No mechanical damage. | |
| (steady conditions) | *Temperature : 40±2°C | Electrical specification shall satisfy the | |
| JIS C 0022 | *Time:1000+24/-0 hrs. | descriptions in electrical characteristics under | |
| | Measurement to be made after keeping at room temperature for 24±2 hrs | the operational temperature range within -40 ~ 85°C. | |
| | 500hrs measuring the first data then1000hrs data | | |
| Low temperature | *Temperature : -40°C±2°C | No mechanical damage. | |
| JIS C 0020 | *Test duration : 1000+24/-0 hours | Electrical specification shall satisfy the | |
| | Measurement to be made after keeping at room temperature for 24±2 hrs | descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. | |

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

ORDERING CODE

| RF | CPL | 060503 | 0 | L | 6 | Т |
|-----------|---------|-----------------|------------|---------------------|-------------|-----------|
| Walsin | Product | Dimension | Unit of | Application | Code from | T: Taping |
| RF device | Code: | code | dimension | L: 2.4/ 5.2/ 5.8GHz | Design Code | |
| | Coupler | Per 2 digits of | 0 : 0.1 mm | Triple Band | | |
| | | Length, Width, | 1 : 1.0 mm | | | |
| | | Thickness : | | | | |
| | | e.g. : | | | | |
| | | 060503 = | | | | |
| | | Length 06, | | | | |
| | | Width 05, | | | | |
| | | Thickness 03 | | | | |

Minimum Ordering Quantity: 4000 pcs per reel. PACKAGING




Paper Tape specifications (unit :mm)

| Index | Ao | Во | ΦD | Т | W |
|----------------|---------------|---------------|---------------|---------------|---------------|
| Dimension (mm) | 0.62 ± 0.05 | 0.80 ± 0.05 | 1.55 ± 0.05 | 0.43 ± 0.05 | 8.00 ± 0.10 |
| Index | E | F | Po | P1 | P2 |
| Dimension (mm) | 1.75 ± 0.05 | 3.50 ± 0.05 | 4.00 ± 0.10 | 2.00 ± 0.05 | 2.00 ± 0.05 |

華新科技股份有限公司 Walsin Technology Corporation

Reel dimensions



Taping Quantity: 4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.
 - Temperature : +5 to +40°C
 - Humidity : 30 to 70% relative humidity
 - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
 - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
 - Products should be storage under the airtight packaged condition.