

www.txccorp.com

# SPECIFICATION FOR APPROVAL

		CN: 1612042562
CUSTOMER	:	
PRODUCT TYPE	:	SMD SEAM SEALING XTAL 5.0 × 3.2
NOMINAL FREQ.	: -	8.00000MHz
TXC P/N	:	AB08000303
REVISION	:	S1
CUSTOMER P/N	:	
PM / SALES	:	
DATE	:	
CUSTOMER CONFIRMATION	: _	
	_	

- (1) TXC requires one copy returned with signature and title of authorized individual that signifies acceptance of the attached specifications.
- (2) Orders received and accepted by TXC after return of signed copy of specification will be produced per these specifications.
- (3) Any changes to these specifications must be agreed upon by both parties and new revision of the Product Specification Sheet will be issued.
- (4) Any issuance of purchase order prior to consigning back the Approval page of "Specification Sheets" from customers will be regarded as the agreement on the contents of these specifications.

MSL:Level 1
RoHS Compliant

(for glass crystal only:Pb used in sealing glass material is exempt from EU directive)

www.txccorp.com

# PRODUCT SPECIFICATION SHEET

CN: 1612042562

PRODUCT TYPE : SMD SEAM SEALING XTAL 5.0 × 3.2

NOMINAL FREQ. : 8.000000MHz

TXC P/N : AB08000303

REVISION : S1

PE/RD	QA	MFG
Wen yuan Chang		
21-Oct-16		

#### NOTE:

(1)The green product standard set by TXC is based upon the international standards. Related information is publicly described on the TXC's Website, and updated regularly. The document is compliant with the latest green product quality system directives at the time.

(2)Revision "Sx" is for engineering samples only. PE/RD's approval required.

(3) Revision "Ax" is production ready. PE, QA and MFG's approval required

MSL:Level 1

**RoHS Compliant** 

(for glass crystal only:Pb used in sealing glass material is exempt from EU directive)



TXC CORPORATION TXC P/N: AB08000303 REVISION: S1 PAGE: 1

Rev	Revise page	Revise contents	<u>Date</u>	Ref.No.	Reviser
S1	N/A	Initial released	21-Oct-16	N/A	Xiaoyan Jiang

TXC CORPORATION TXC P/N: AB08000303 REVISION: S1 PAGE: 2

## **■ ELECTRICAL SPECIFICATIONS**

#### Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement and tests are as follow:

Ambient temperature :  $25\pm5^{\circ}$ C Relative humidity :  $40\%\sim70\%$ 

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature :  $25\pm3^{\circ}$ C Relative humidity :  $40\%\sim70\%$ 

## Measure equipment

Electrical characteristics measured by S&A 250B or equivalent.

#### **Crystal cutting type**

The crystal is using AT CUT (thickness shear mode).

#### **Unit Weight:**

0.046±0.002 g/pcs


	Darameters	Parameters SYM. Electrical Spec.					Notes
	Parameters	STIVI.	MIN	TYPE	MAX	UNITS	Notes
1	Nominal Frequency	FL	8	.000000		MHz	-
2	Oscillation Mode	-	Fur	ndamenta	al	-	-
3	Load Capacitance	CL		20		pF	-
4	Frequency Tolerance	-		±30		ppm	at 25 ℃ ± 3 ℃
5	Frequency Stability	-	±100		ppm	Over Operating Temp. Range (Reference 25℃)	
6	Operating Temperature	-	-40	~	125	$^{\circ}\mathbb{C}$	-
7	Aging	-	-5	~	5	ppm	1st Year
8	Drive Level	DL	1	50	100	μW	-
9	Effective Resistance	Rr	1	-	150	Ω	-
10	Shunt Capacitance C0	C0	7 p		pF	-	
11	Insulation Resistance	-	500	-	1	ΜΩ	at DC 100V
12	Storage Temperature Range	-	-40	~	125	$^{\circ}\mathbb{C}$	-




**TXC CORPORATION** 


TXC P/N: AB08000303 REVISION: S1 PAGE: 3

# **■ DIMENSIONS**






Suggested Layout




# **■ MARKING**



**Production location: China or Taiwan** 

## **■ SUGGESTED REFLOW PROFILE**

Total time : 200 sec. Max. Solder melting point :220  $^{\circ}\text{C}$ 




<sup>\*</sup>Coplanarity of solderable areas Camber 0.10 mm Max



TXC CORPORATION TXC P/N: AB08000303 REVISION: S1 PAGE: 4


# **■** STRUCTURE ILLUSTRATION



NO	COMPONENTS	MATERIALS	FINISH/SPECIFICATIONS
1	Lid	Kovar (Fe/Co/Ni)	-
2	Package	Ceramic (Al <sub>2</sub> O <sub>3</sub> ) + Kovar (Fe/Co/Ni)+ Ag/Cu	-
3	PAD	Au	Tungsten metalize
			+ Ni plating
			+ Au plating
4	Crystal blank	SiO <sub>2</sub>	-
5	Conductive adhesive	Ag+Silicon	-
6	Electrode	Noble Metal	-


TXC CORPORATION TXC P/N: AB08000303 REVISION: S1 PAGE: 5

## **■ PACKING**



DIMENSIONS	Α	В	С	D	Е	F	G	Н	
DIVIENSIONS	1.65±0.10	5.40±0.10	3.50±0.10	8.00±0.10	12.00±0.30	4.00±0.10	1.55±0.10	1.75±0.10	(UNIT : mm)

## REMARK:



DIMENSIONS	┙	L1	W	W1	pcs / Reel (UNIT : mm)
DIVILIVSIONS	180±1.00	13±0.50	16.5±0.20	12±0.10	Standard Reel Quantity is 1,000 pcs per reel

TXC CORPORATION TXC P/N: AB08000303 REVISION: S1 PAGE: 6

# ■ RELIABILITY SPECIFICATIONS (AEC-Q200 Compliant)

# 1.Mechanical Endurance

No.	Test Item	Test Met	thods	REF.DOC	
1.1	Drop Test	120 cm height, 20 times on Stainless	JIS C 6701		
1 2	Mechanical Shock	Device are shocked to half sine wave	e ( 5000 G ) three mutually	MIL-STD-202	
1.2	Mechanical Shock	perpendicular axes each 3 times. 0.3	m sec. duration time	Method 213	
		Frequency range	10 ~ 2000 Hz~10 Hz		
		Amplitude	1.52 mm/20G	MIL CTD 202	
1.3	Vibration	Sweep time	20 minute	MIL-STD-202 Method 204	
		Perpendicular axes each test time	4 Hrs	Wictiou 204	
			(Total test time 12 Hrs)		
		Temperature	245 °C ± 5°C		
		Immersing depth	1.25 mm		
1.4	Solderability	Immersion time	5 ± 1 seconds	J-STD-002	
		Flux	Rosin resin methyl alcohol		
			solvent (1:4)		
1.5	Terminal Strength	Mount on PCB board and shear stren	AEC-Q200-006		
1.6	Board Flex	Duration Time: 60 sec, Deviation: 3m	AEC-Q200-005		

## 2. Environmental Endurance

No.	Test Item	Test Methods	REF. DOC
2.1	Resistance To Soldering Heat	Pre-heat temperature $125 ^{\circ}\text{C}$ Pre-heat time $60 ^{\circ}$ 120 sec.Test temperature $260 \pm 5 ^{\circ}\text{C}$ Test time $10 \pm 1 \text{sec.}$	MIL-STD 202 Method 210
2.2	High Temp. Storage	+ 125 °C ± 3 °C for all 1000 Hrs.	MIL-STD-202 Method 108
2.3	Low Temp. Storage	- 40 °C ± 3 °C for all 1000 Hrs.	JIS C 6701
2.4	Thermal Shock	Total 1000 cycles of the following Thermal Shock : $\begin{array}{c c} 1 & \text{cycle} \\ \hline 125 \pm 3^{\circ}\text{C} \\ \hline 25^{\circ}\text{C} \\ \hline -55 \pm 3^{\circ}\text{C} \\ \hline \end{array}$	MIL-STD-202 Method 107
2.5	Temperature Cycle	Total 1000 cycles of the following temperature cycle : $-40^{\circ}$ C ± 3 to 125°C ± 3 , Dwell time:15min.	JESD 22 Method JA-104
2.6	Biased Humidity	+ 85°C ± 3°C , RH 85% , 1000 Hrs.	MIL-STD-202 Method 103
2.7	Moisture Resistance	20 cycles ( +25°C ~65°C , 80%~100% RH) , 24hrs/cycle.	MIL-STD 202 Method 106
2.8	Operational Life	+ 125 °C ± 3 °C for 1000 Hrs.	MIL-STD-202 Method 108