

● FEATURES

Power dissipation


Plastic-Encapsulate Transistors(NPN)

● MAXIMUM RATINGS ($T_A=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	40	V
V_{CEO}	Collector-Emitter Voltage	30	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current -Continuous	3	A
P_c	Collector Power Dissipation	2.5	W
T_J	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature	-55-150	$^\circ\text{C}$

SOT-89

1. BASE



2. COLLECTOR

3. Emitter

● ELECTRICAL CHARACTERISTICS(Tamb=25°C unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = 100\mu\text{A}, I_E=0$	40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = 10\text{mA}, I_B=0$	30			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E= 100\mu\text{A}, I_C=0$	6			V
Collector cut-off current	I_{CBO}	$V_{CB}= 40\text{V}, I_E=0$			1	μA
Collector cut-off current	I_{CEO}	$V_{CE}= 30\text{V}, I_B=0$			10	μA
Emitter cut-off current	I_{EBO}	$V_{EB}= 6\text{V}, I_C=0$			1	μA
DC current gain	$h_{FE(1)}$	$V_{CE}=2\text{V}, I_C= 1\text{A}$	60		400	
	$h_{FE(2)}$	$V_{CE}=2\text{V}, I_C= 100\text{mA}$	32			
Collector-emitter saturation voltage	$V_{CE(\text{sat})}$	$I_C= 2\text{A}, I_B= 0.2 \text{ A}$			0.5	V
Base-emitter saturation voltage	$V_{BE(\text{sat})}$	$I_C= 2\text{A}, I_B= 0.2 \text{ A}$			1.5	V
Transition frequency	f_T	$V_{CE}= 5\text{V} , I_C=0.1\text{A}$ $f = 10\text{MHz}$	50			MHz

● h_{FE} Classification

Marking	DG			
Rank	R	S	T	U
h_{FE}	100~200	140~280	200~400	280~560

Typical characteristics




Figure 1. Static Characteristic




Figure 2. DC current Gain




Figure 3. Base-Emitter Saturation Voltage
Collector-Emitter Saturation Voltage




Figure 4. Current Gain Bandwidth Product




Figure 5. Collector Output Capacitance