

SPTECH Silicon NPN Power Transistor

2SC4237

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{CEQ(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C=10\text{mA}$; $I_B=0$	800			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=5\text{A}$; $I_B=1\text{A}$			1.0	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C=5\text{A}$; $I_B=1\text{A}$			1.5	V
I_{CBO}	Collector Cutoff Current	At rated Voltage			100	μA
I_{CEO}	Collector Cutoff Current	At rated Voltage			100	μA
I_{EBO}	Emitter Cutoff Current	At rated Voltage			100	μA
h_{FE-1}	DC Current Gain	$I_C=5\text{A}$; $V_{CE}=5\text{V}$	18		28	
h_{FE-2}	DC Current Gain	$I_C=1\text{mA}$; $V_{CE}=5\text{V}$	5			
f_T	Current-Gain—Bandwidth Product	$I_C=1\text{A}$; $V_{CE}=10\text{V}$		8		MHz

Switching times

t_{on}	Turn-on Time	$I_C=5\text{A}$, $I_{B1}=1\text{A}$; $I_{B2}=-2\text{A}$ $R_L=50\Omega$; $V_{BB2}=4\text{V}$			0.5	μs
t_{stg}	Storage Time				3.5	μs
t_f	Fall Time				0.3	μs