



SCHOTTKY BARRIER DIODES

FEATURES


- Guard ring protection
- Low forward voltage drop
- For use in low voltage, high frequency inverters
- Surface mount device type

MECHANICAL DATA

- Case: SOD-323
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 5.48mg / 0.00019oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Parameter	Symbols	RB551V-40	Units
Maximum recurrent peak reverse voltage	V_{RM}	40	V
Continuous forward current	I_O	500	mA
Reverse Leakage Current	I_R	0.1 @ $V_R=40V$	mA
Peak Forward Surge Current, 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	I_{FSM}	25	A
Maximum Forward Voltage	V_F	0.47 @ $I_F=0.5A$	V
Total power dissipation	P_D	200	mW
Thermal Resistance, Junction to Ambient Air	$R_{\theta JA}$	400	°C/W
Junction Temperature	T_j	125	°C
Storage Temperature	T_{stg}	-55 ~ +150	°C



Fig.1 Power Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 TYPICAL FORWARD VOLTAGE




Fig.4 Typical Junction Capacitance





Fig.5 Maximum Non-Repetitive Peak Forward Surge Current






PACKAGE OUTLINE

Plastic surface mounted package; 2 leads


SOD-323



SOD-323 mechanical data

UNIT		A	C	D	E	E ₁	b	L ₁	A ₁	∠
mm	max	1.1	0.15	1.4	1.8	2.75	0.4	0.45	0.2	9°
	min	0.8	0.08	1.2	1.4	2.55	0.25	0.2	—	
mil	max	43	5.9	55	70	108	16	16	8	
	min	32	3.1	47	63	100	9.8	7.9	—	

The recommended mounting pad size



Marking

Type number	Marking code
RB551V-40	D4