



SURFACE MOUNT ULTRAFAST RECOVERY RECTIFIER

Reverse Voltage - 50 to 1000 V

Forward Current - 1 A

FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- High efficiency
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg/0.00053oz

PINNING

| PIN | DESCRIPTION |
|-----|-------------|
| 1 | Cathode |
| 2 | Anode |



Top View
Marking Code: US1AW-US1DW: USL
US1GW: USM
US1JW-US1MW: USH
Simplified outline SOD-123FL and symbol

Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.







Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

| Parameter | Symbols | US1AW | US1BW | US1DW | US1GW | US1JW | US1KW | US1MW | Units | | | | | |
|--|-----------------------------------|------------|-------|-------|-------|-------|-------|-------|-------|--|--|--|--|--|
| Maximum Repetitive Peak Reverse Voltage | V _{RRM} | 50 | 100 | 200 | 400 | 600 | 800 | 1000 | V | | | | | |
| Maximum RMS voltage | V _{RMS} | 35 | 70 | 140 | 280 | 420 | 560 | 700 | V | | | | | |
| Maximum DC Blocking Voltage | V _{DC} | 50 | 100 | 200 | 400 | 600 | 800 | 1000 | V | | | | | |
| Maximum Average Forward Rectified Current at T _c = 125 °C | I _{F(AV)} | 1 | | | | | | | A | | | | | |
| Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load | I _{FSM} | 30 | | | | | | | A | | | | | |
| Maximum Instantaneous Forward Voltage at 1 A | V _F | 1.0 | | 1.3 | | 1.65 | | V | | | | | | |
| Maximum DC Reverse Current T _a = 25 °C at Rated DC Blocking Voltage T _a = 125 °C | I _R | 5 100 | | | | | | | µA | | | | | |
| Maximum Reverse Recovery Time ⁽¹⁾ | t _{rr} | 50 | | | 75 | | | ns | | | | | | |
| Typical Junction Capacitance ⁽²⁾ | C _j | 15 | | | | | | | pF | | | | | |
| Typical Thermal Resistance ⁽³⁾ | R _{θJA} | 85 | | | | | | | °C/W | | | | | |
| Operating and Storage Temperature Range | T _j , T _{stg} | -55 ~ +150 | | | | | | | °C | | | | | |

(1) Measured with I_F = 0.5 A, I_R = 1 A, I_{rr} = 0.25 A.

(2) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(3) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.







PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-123FL



The recommended mounting pad size



Marking

| Type number | Marking code |
|-------------|--------------|
| US1AW | USL |
| US1BW | |
| US1DW | |
| US1GW | USM |
| US1JW | USH |
| US1KW | |
| US1MW | |