SOT-89 Plastic-Encapsulate Voltage Regulators

78L12 Three-terminal positive voltage regulator

SOT-89-3L



FEATURES

- Maximum output current
  I_{OM}: 0.1A
- Output voltage
  V_O: 12V
- Continuous total dissipation
  P_D: 0.6 W (T_a= 25 ℃)

ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)

Parameter	Symbol	Value	Unit
Input Voltage	V_i	30	V
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	166.7	℃/W
Operating Junction Temperature Range	T_{OPR}	-40~+125	℃
Storage Temperature Range	T_{STG}	-65~+150	℃

ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE (Vi=19V,Io=40mA,Ci=0.33uF,,Co=0.1uF, unless otherwise specified)

Parameter	Symbol	Test conditions		Min	Typ	Max	Unit
Output voltage	Vo		25℃	11.5	12	12.5	V
		14V≤V_I≤27V, Io=1mA-40mA	0-125℃	11.4	12	12.6	V
		Io=1mA-70mA		11.4	12	12.6	V
Load Regulation	△Vo	Io=1mA-100mA	25℃		22	100	mV
		Io=1mA-40mA	25℃		13	50	mV
Line regulation	△Vo	14.5V≤V_I≤27V	25℃		55	250	mV
		16V≤V_I≤27V	25℃		49	200	mV
Quiescent Current	Iq		25℃		4.3	6.5	mA
Quiescent Current Change	△Iq	16V≤V_I≤27V	0-125℃			1.5	mA
	△Iq	1mA≤I_O≤40mA	0-125℃			0.1	mA
Output Noise Voltage	V_N	10Hz≤f≤100KHz	25℃		70		μV/Vo
Ripple Rejection	RR	15V≤V_I≤25V,f=120Hz	0-125℃	37	42		dB
Dropout Voltage	Vd		25℃		1.7		V

* Pulse test.

TYPICAL APPLICATION



Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as

Typical Characteristics

Output Characteristics



Dropout Characteristics



Quiescent Current



Current Cut-off Grid Voltage



Output Voltage vs Junction Temperature



Power Derating Curve



Outlitne Drawing

SOT-89-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

SOT-89-3L Suggested Pad Layout



Note:
1.Controlling dimension:in/millimeters.
2.General tolerance: ±0.05mm.
3.The pad layout is for reference purposes only.

PACKAGE SPECIFICATIONS

Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (pcs)	Box Size (mm)	QTY/Box (pcs)	Carton Size (mm)	G.W.(Kg)
SOT-89-3L	7'	330	1000	203×203×195	40000	438×438×220	180000

Important Notice and Disclaimer

Microdiode Electronics (Jiangsu) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design,purchase or use.

Microdiode Electronics (Jiangsu) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does Microdiode Electronics (Jiangsu) assume any liability for application assistance or customer product design. Microdiode Electronics (Jiangsu) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Jiangsu).

Microdiode Electronics (Jiangsu) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Jiangsu).