

Single Output Hall Effect Latch

Features


- 3.3V to 26V DC operation voltage
- Temperature compensation
- Wide operating voltage range
- Open-Drain pre-driver
- 25mA maximum sinking output current.
- -40°C to 85°C operating temperature
- Low Profile SOT-23 Package(Green and PB Free)

Description

GR178 is an integrated Hall effect latched sensor designed for electronic commutation of brush-less DC motor applications. The device using HV BCD process includes an on-chip Hall voltage generator for magnetic sensing, a comparator that amplifies the Hall voltage, and a Schmitt trigger to provide switching hysteresis for noise rejection, and open-collector output. An internal band-gap regulator is used to provide temperature compensated supply voltage for internal circuits and allows a wide operating supply range.


If a magnetic flux density larger than threshold Bop, OUT is turned on(low). The output state is held until a magnetic flux density reversal falls below Brp causing OUT to be turned off (high).

Ordering and Marking Information



greenergy OPTO Inc. reserves the right to make changes to improve reliability or manufacture ability without notice, and advise customers to obtain the latest version of relevant information to verify before placing orders.

Pin Configuration




Pin Description

Pin No.	Name	Function
1	OUT	Output
2	VDD	Power Supply Pin
3	GND	Ground Pin


Absolute Maximum Ratings

Supply Voltage VCC, VCC	-----	28V
Reverse VCC Polarity Voltage, VRCC	-----	-28V
Magnetic Flux Density, B	-----	Unlimited Gauss
Output Current(Continuous), IO	-----	25mA
Power Dissipation, PD	-----	550mW
Storage Temperature Range, TSTG	-----	-65°C ~ 150 °C
Thermal Resistance from Junction to case, θ_{JC}	-----	49°C/W
Thermal Resistance from Junction to ambient, θ_{JA}	-----	227°C/W
Ambient Temperature, TA	-----	-40°C~85°C

Function Block



Application Circuit



Electrical Characteristics (VCC = 12.0V & TA = +25°C, unless otherwise noted.)

Parameter	Min.	Typ.	Max.	Unit
-----------	------	------	------	------


SUPPLY VOLTAGE


Supply Voltage, VDD(Operating)	3.3	-	26	V
Startup Current, IDD (Operating)	-	3.0	4.5	uA
Output Leakage Current, IOFF(VOUT =12V)	-	<0.1	10	uA
Output Saturation Voltage, Vds (sat)(IOUT =20mA)	-	0.3	-	V
Magnetic (1mT=10 Gauss)				
Operate Point, BOP	5	35	60	Gauss
Release Point, BRP	-60	-35	-5	Gauss
Hysteresis, BHYS	-	70	-	Gauss

Driver output vs. magnetic pole

Characteristics	Test Conditions	DO
North pole	B < Brp	High
South pole	B > Bop	Low

Note: The magnetic pole is applied facing the branded side of the package




Package Information
SOT-23


SYMBOL	SOT-23			
	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A		1.45		0.057
A1	0.00	0.15	0.000	0.006
A2	0.90	1.30	0.035	0.051
b	0.30	0.50	0.012	0.020
c	0.08	0.22	0.003	0.009
D	2.70	3.10	0.106	0.122
E	2.60	3.00	0.102	0.118
E1	1.40	1.80	0.055	0.071
e	0.95 BSC		0.037 BSC	
e1	1.90 BSC		0.075 BSC	
L	0.30	0.60	0.012	0.024
θ	0°	8°	0°	8°

Note: 1. Dimension D and E1 do not include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 10 mil per side

Tape and Specification Reel

SOT-23



Greenergy OPTO, Inc. reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.