


Fast Recovery Rectifier

FR101 ~ FR107

■ Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- Fast switching for high efficiency
- Low reverse leakage
- Built-in strain relief, ideal for automated placement
- High forward surge current capability
- High temperature soldering guaranteed:
250°C/10 seconds at terminals



■ Absolute Maximum Ratings Ta = 25°C unless otherwise specified

Parameter	Symbol	FR 101	FR 102	FR 103	FR 104	FR 105	FR 106	FR 107	Unit
Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Surge Peak Reverse Voltage	V _{RSM}	35	70	140	280	420	560	700	
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	
Instantaneous Forward Voltage at I _F =1A	V _F				1.3				
Averaged Forward Current at T _L =75°C	I _{FAV}				1				
Peak forward surge current	I _{FSM}				30				A
Maximum DC Reverse Current T _A =25°C at rated DC blocking voltage T _A =100°C	I _R				5				μA
					50				
Reverse Recovery Time *1	t _{rr}			150		250	500		ns
Typical Junction Capacitance *2	C _j			15					pF
Typical thermal resistance *3	R _{thJA}			50					°C/W
Junction Temperature	T _j			150					°C
Storage Temperature	T _{stg}			-55 to 150					

* 1 Reverse recovery condition I_F = 0.5 A, I_R = 1 A, I_{rr} = 0.25 A

* 2 Measured at 1MHz and applied reverse voltage of 4V D.C

* 3 P.C.B. mounted with 0.2×0.2" (5×5mm) copper pad areas

■ Marking

NO.	FR101	FR102	FR103	FR104	FR105	FR106	FR107
Marking	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	RS1M

Fast Recovery Rectifier

FR101 ~ FR107

■ Typical Characteristics

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instantaneous Forward Characteristics




Fig.4 Typical Junction Capacitance





Fig.5 Maximum Non-Repetitive Peak Forward Surge Current




Fast Recovery Rectifier

FR101 ~ FR107

■ Package Outline Dimensions

Plastic surface mounted package; 2 leads

SMA



UNIT		A	D	E	H _E	c	e	g	a
mm	max	2.2	4.5	2.7	5.2	0.31	1.6	1.5	0.3
	min	1.9	4.0	2.3	4.7	0.15	1.3	0.9	
mil	max	87	181	106	205	12	63	59	12
	min	75	157	91	185	6	51	35	

■ The recommended mounting pad size

