

DESCRIPTION

The PT5607 is a high speed high voltage (600V) driver to control power devices like MOS-transistors or IGBTs in half bridge systems with dependent high and low side referenced output channels. The logic input is compatible with standard CMOS or LSTTL output, down to 3.3V logic. The device includes an undervoltage detection unit with hysteresis characteristic and prevents power devices against large amount of conduction loss, when voltage margin of gate is not high enough. The output drivers feature a high pulse current buffer stage designed for minimum driver cross-conduction. The floating channel can be used to drive an N-channel power MOSFET or IGBT, in the high side configuration which operates up to 600 volts. It is pin and input polarity compatible to IR2101.

APPLICATIONS

- Appliance motor drives air conditioners, washing machines, refrigerator, dish washer, Fans
- General purpose inverters
- Electric bike, Electric tools
- Lighting, switching power supply

FEATURES

- Drives two IGBT/MOSFET power devices
- high side channel fully operate up to +600V
- Gate drive supplies from 10V to 20 V per channel
- Under-voltage lockout
- Advanced input filter
- Built-in dead-time protection: 0.5us
- IO+/-: 290/620mA, large sourcing current to bypass miller effect
- Shoot-through (cross-conduction) protection
- 3.3V/5V/15V input logic compatible
- Matched propagation delays for all channels
- Matched dead time
- High side output in phase with HIN input
- Low side output in phase with LIN input
- Tolerant to negative transient voltage, immunity of dv/dt up to 50V/ns
- Low di/dt gate drive for better noised immunity
- -40°C to 125°C operating range
- SOP8L package available
- Lead-free



8-Lead SOIC



BLOCK DIAGRAM



TYPICAL APPLICATION





ORDER INFORMATION

Valid Part Number	Package Type	Top Code	
PT5607	8-Pin, SOP, 150 MIL	PT5607-S	

PIN CONFIGURATION



PIN DESCRIPTION

Pin Name	Description	Pin No.
VCC	Low-side supply voltage	1
HIN	Logic input for high-side gate driver output(HO), in phase	2
LIN	Logic input for low-side gate driver output(LO), in phase	3
СОМ	Low-side gate drive return	4
LO	Low-side driver output	5
VS	High voltage floating supply return	6
HO	High-side driver output	7
VB	High-side gate drive floating supply	8



FUNCTION DESCRIPTION

LOW SIDE POWER SUPPLY

VCC is the low side supply and it provides power both to input logic and to low side output power stage. The built-in under-voltage lockout circuit enables the device to operate at sufficient power on when a typical VCC supply voltage higher than V_{CCUV+} =8.6 is present, shown as Figure1. The IC shuts down the gate drivers outputs, when the VCC supply voltage is below V_{CCUV-} =8.1 V, shown as Figure1. This prevents the external power devices from extremely low gate voltage levels during on-state and therefore from excessive power dissipation.



Figure.1: VCC Supply UVLO Operating Area

HIGH SIDE POWER SUPPLY

VB to VS is the high side supply voltage. The totally high side circuitry can float with respect to COM following the external high side power device emitter/source voltage. Due to the internally low power consumption, the whole high side circuitry can be supplied by bootstrap topology connected to VCC, and it can be powered with small bootstrap capacitor tied between PIN VB and PIN VS.

The device operating area as a function of the supply voltage is given in Figure 2.



Figure.2: VBS supply UVLO operating area



LOW SIDE AND HIGH CONTROL INPUT LOGIC

The Schmitt trigger threshold level of each input is compatible to LSTTL and CMOS down to 3.3 V. Input Schmitt trigger and advanced noise filter provide beneficial noise rejection to short input pulses.

DEAD TIME



INPUT/OUTPUT TIMING DIAGRAM





PT5607

SWITCHING TIME WAVEFORM DEFINITIONS





ABSOLUTE MAXIMUM RATINGS

Stresses exceeding the absolute maximum ratings may damage the device or make the function abnormal. All the voltage parameters are absolute voltages referenced to COM unless otherwise stated in the table.

Parameter	Symbol	Min.	Max.	Unit
High-side floating supply voltage	VB	-0.3	625	
High-side offset voltage	Vs	V _B -25	V _B +0.3	
High-side gate driver output voltage	Vно	Vs-0.3	Vs +0.3	
Low-side gate driver output voltage	V _{LO}	COM-0.3	V _{CC} +0.3	V
Logic input voltage(HIN,LIN)	V _{HIN} V _{LIN}	-0.3	25	
Low-side supply voltage	Vcc	-0.3	25	
Allowable offset voltage slew rate	dV/dT	-	50	V/ _{ns}
Package power dissipation @ T _A ≤+25°C	PD	-	0.625	W
Thermal resistance, junction to ambient	Rth _{JA}		200	°C/W
Junction temperature	TJ	-50	+150	
Storage temperature	Ts	-40	+150	°C
Lead temperature (soldering, 10 seconds)	ΤL	-	300	

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Min.	Тур.	Max.	Unit
Low-side supply voltage	Vcc	10	-	20	
High-side Floating Supply Offset Voltage *1	Vs	-6	-	600	
High-side Floating Supply Voltage	VB	Vs+10	-	Vs+20	
High-side gate driver output voltage	V _{HO}	Vs	-	VB	V
Low-side gate driver output voltage	VLO	COM	-	Vcc	
Logic input voltage	Vhin V _{LIN}	0	-	5	
IC operating junction temperature	TJ	-40	-	+125	°C

*1: For normal logic operation, it is recommended to keep the VS above -6V referenced to COM.



STATIC ELECTRICAL CHARACTERISTICS

 $(V_{CC}-COM) = (V_B-V_S) = 15V$. $T_{AMB}=25^{\circ}C$ unless otherwise specified; The V_{IN} , V_{TH} and I_{IN} parameters are referenced to COM. The V_0 and I_0 parameters are referenced to COM and are applicable to the respective output leads: HO or LO.

Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit
Low Side Power Supply Characteristics						
VCC quiescent current	I _{QVCC}	V _{HIN} =0, V _{LIN} =0	-	180	250	μA
VCC supply under-voltage positive going threshold	Vccuv+		7.7	8.6	9.5	
VCC supply under-voltage negative going threshold	V _{ccuv-}		7.2	8.1	9	V
Vcc supply under-voltage lockout hysteresis	VCCHYS		-	0.5	-	
High Side Floating Power Supply Characteristic	s					
High side VBS supply under-voltage positive going threshold	VBSUV+		6.6	7.8	9	
High side VBS supply under-voltage negative going threshold	V _{BSUV-}		6	7.2	8.4	V
High side VBS supply under-voltage lockout hysteresis	V _{BSUVHYS}		-	0.6	-	
High side VBS quiescent current	IQBS	V _{BS} =15V	-	50	85	
Offset supply leakage current	I _{LK}	V _B =V _S =600V V _{CC} =0V	-	-	10	μA
Gate Driver Output Section						
Output high short-circuit pulse current	I ₀₊	V _{HO} =V _S =0, V _{HO} =V _B =15V, PW<10µs	-	290	-	
Output low short-circuit pulse current	lo-	V _{LO} =COM=0, V _{LO} =V _{CC} =15V, PW<10µs	-	620	-	mA
High level output voltage drop, V _{CC} -V _{LO} ,V _{BS} -V _{HO}	ΔVон	IO+= 20 mA	-	0.4	1	V
Low level output voltage drop	ΔV_{OL}	IO-= 20 mA	-	0.15	0.3	V
Allowable negative VS pin voltage for COM	Vsn	Fixed V _{BS} =15V	-6	-	-	V
Logic Input Section				•	•	
Logic"1" Input voltage HIN and LIN	VIH		2.5	-	-	
Logic"0" Input voltage HIN and LIN	VIL		-	-	0.8	v
Input positive going threshold	V _{IN,TH+}		-	1.9	-	v
Input negative going threshold	Vin,th-		-	1.4	-	
Logic "1" Input bias current	I _{HIN+}	V _{IN} =5V	-	50	70	
Logic "0" Input bias current	I _{HIN} -	V _{IN} =0V	-	0	1	
Logic "1" Input bias current	I LIN+	V _{IN} =5V	-	50	70	μA
Logic "0" Input bias current	I LIN-	V _{IN} =0V	-	0	1	



DYNAMIC ELECTRICAL CHARACTERISTICS

 $(V_{CC}-COM) = (V_B-V_S)=15V$, $V_S=COM$, and $C_{HO}=C_{LO}=1nF$ unless otherwise specified, $T_{AMB}=25^{\circ}C$.

Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit
VCC supply current	IVCCOP	f _{LIN} =20KHz, f _{HIN} =20KHz,	-	1	1.5	mA
Turn-On propagation delay	ton		300	500	700	
Turn-Off propagation delay	toff	See switching time waveform	300	500	700	
Turn-On rise time	t _R	definitions	-	70	-	
Turn-Off fall time	t _F		-	32	-	
Input filter	t _{flt}	V _{IN} =0 or 5V	100	250	400	ns
Dead time	DT	HIN and LIN inputs without external dead time	300	500	700	110
Delay matching(ton, toff)	MT	HIN and LIN inputs with external dead time >2µs	-	-	50	
Output pulse-width matching	PM	PW _{IN} =10µs, PM=PW _{OUT} -PW _{IN}	-	-	50	



PT5607

PACKAGE INFORMATION

8 PINS, SOP, 150MIL







Symbol	Dimension (mm)					
	Min.	Nom.	Max.			
А	-	-	1.75			
A1	0.10	-	0.25			
A2	1.25	-	-			
b	0.31	-	0.51			
С	0.10	-	0.25			
D	4.90 BSC					
E		6.00 BSC				
E1	3.90 BSC					
е	1.27 BSC					
L	0.40	-	1.27			
θ	0°	-	8 °			

Notes:

1. Refer to JEDEC MS-012 AA



IMPORTANT NOTICE

Princeton Technology Corporation (PTC) reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its products and to discontinue any product without notice at any time. PTC cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a PTC product. No circuit patent licenses are implied.

Princeton Technology Corp. 2F, 233-1, Baociao Road, Sindian Dist., New Taipei City 23145, Taiwan Tel : 886-2-66296288 Fax: 886-2-29174598 http://www.princeton.com.tw