ISO9001: 2000	ISO14001: 2004

Title. TACT SWITCH

Product Model. TS-1003T

Customer's Part NO.

Customer's Model:

Customer's Approval Requested.

Please return this copy as a certification of yourapproval.

Checked by: Date:

Approved by: Date:


APPROVE	REVIEW	POLT
王凱	李成功	許志明


XUNPU ELECTRONICS CO.,LTD




CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		TS-1003T	TACT SWITCH	


产品符合ROHS






PCB Layout(Pattern side)







General tolerance: ±0.2mm

NO.	NAME	MATERIAL	NATIONALITY	QTY.	FINISHING
1	Terminal	Brass		4	Plating silver
2	Contact	SUS		1	
3	Cover	SPCC		1	PLAting nickel
4	Base	Nylon		1	Black
5	Keystoke	Nylon		1	BlacK

APPROVE BY	王凯12.05.21	CHECKED BY	李成功12.05.21	PRPARE BY	许志明12.05.21
------------	------------	------------	-------------	-----------	-------------



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		TS-1003T	TACT SWITCH	

A.Specification & meanings

The name of the tact switch is composed by type and specification, the particular meaning of the type, specification and code is as follows.



1. Operating force: An English letter expresses it, unite: Newton (N),as chart 1 shows:

Operating			
force Code Spec		Press force(N)	Return force
Code	Spec		
16	1.6	1.6±0.5	0.4min
26	2.6	2.6±0.5	0.4min

Examples: "TS-1003T-16" denotes the tacts witch with 12 \times 12 base, the height is 7.3 mm, the stem is black, the operating force is 1.6 N.

and positioning to the control of th						
APPROVE BY	王凱12.05.21	CHECKED BY	李成功12.05.21	PRPARE BY	許志明12.05.21	



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		TS-1003T	TACT SWITCH	А

1、 概述

GENERAL

1.2 适用范围

APPLICATION

此规格书适用于机械式轻触开关的相关要求

This specification is applied to the requirements for TACTILE SWITCH (MECHANICAL CONTACT)

1.3 工作温度范围

Operating Temperature Range

- -20℃~70℃(在标准大气压、标准湿度条件下)
- -20°C ~70°C (Normal humidity, normal air pressure)
- 1.4 贮藏温度范围

Storage Temperature Range

- -30℃~80℃(在标准大气压、标准湿度条件下)
- -30° C \sim 80 $^{\circ}$ C (Normal humidity, normal air pressure)
- 1.5 测试条件

Test Conditions

在没有其它特定的条件下,应该在以下的条件下进行测试和测量:

Unless otherwise specified, tests and measurement shall be made in the following standard conditions:

常温.....5℃~35℃

Normal temperature.......5℃~35℃ 标准湿度......相对湿度 25%~85%

Normal humidity.....relative humidity 25%~85%

Normal numidity.....relative numidity 25%~标准大气压......86KPa~106Kpa

Normal air pressure......86Kpa~106Kpa

在制造过程中,测试和测量应该在以下的条件下进行:

If any doubt arise from the judgment, tests shall be conducted at the following conditions:

环境气压......86KPa~106Kpa Airpressure......86KPa~106Kpa

APPROVE BY	王凱12.05.21	CHECKED BY	李成功12.05.21	PRPARE BY	許志明12.05.21
------------	------------	------------	-------------	-----------	-------------



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		TS-1003T	TACT SWITCH	

2、 详细说明

Detailed specification

2.1 外观:应无影响、降低产品性能的缺陷;

Appearance: There should be no defects that affect the serviceability of product.

2.2 结构尺寸和安装尺寸:应符合装配图要求;

Style and dimension: shall conform to the assemble drawings.

2.3 操作形式:有触觉反应的操作

Type of actuating: Tactile feedback.

2.4 开关结构: 单回路单输出(具体的触点结构在装配图中已绘出);

Contact arrangement: 1 pole, 1 throw

(Details of contact arrangement are given in the assembly drawings.)

2.5 开关工作额定值: DC 12V, 50mA (有效值)

Ratings: 12V DC, 50mA (effective value)

3. 电气性能:

ELECTRICAL SPECIFICATION

伍	项 目 试 验 条 件				要求
ITI	EM		EST CONDITIONS		REQUIREMENTS
		在以 5V 10mA 的] 的电路中,以一个等于	直流电源或不低于1KI 一2倍按力的静负荷施		
1	接触电阻	Applying a static	load of 2 times ope	erating force to	≤100mΩ
	Contact Resistance	the center of the stem, measurements shall be made by			
		5V DC 10mA or m	ore than 1KHZ AC	small-current	
		contact resistance me	ter.		
2	绝缘电阻 Insulation Resistance	在端子之间施加 DC 100V /1min 的条件下,测量端子之间底座、盖板的电阻值 Measurement shall be made following application of 100V DC potential, across terminals, and across terminals and cover, for one minute.			≥100MΩ
	介质耐压	在端子之间施加 2	250V AC(50HZ 或 60	OHZ)/1min	无击穿、无飞弧
3	Dielectric	250V AC (50HZ c	or 60HZ) shall be app	olied across	There should be
voltage		terminals, for one minute.			no breakdown and
	ronago			flashover	
APPROVE	APPROVE BY 王凱12.05.21 CHECKED BY 李成功12.05.21 PRPARE E		PRPARE B	Y 許志明12.05.21	



CUSTOMER		CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
			TS-1003T	TACT SWITCH	
	项目		试验条件		要求
	ITEM	1	TEST CONDITIONS		REQUIREMENTS
	械性能: IANICAL SPECI				
1	按力 Operating Force	量开关导通所需的最大力 Placing the switch suc vertical and then grad	ch that the direction of dually increasing the le e maximum load require	switch operation is pad applied to the	refer to chart 3
2	最大行程 Full Travel	开关驱动件顶端中心,没 Placing the switch suc vertical and then apply	ch that the direction of ring static load of 2time the travel distance for	switch operation is soperating force to	0.25±0.1mm
APP	ROVE BY	王凱12.05.21 CHE	CKED BY 李成功12.	05.21 PRPARE E	許志明12.05.21



	ALTINOVAL OF LOTTONO							
CUSTOMER		CUSTOMER'S	P/N GYE	E'S P/N	PRODI	UCT	REVISION	
			TS-	-1003T	TACT S	WITCH		
	项目		试验》	条 件	I		要求	
	ITEM		TEST CON	DITIONS			REQUIREMENTS	
3	回弹力 Return Forc	后,测量顶端向自 The sample swi operation is veri to the whole trav free position sha		更。 uch that the epressing the force of the s	switch center to its			
4	停止强度 Stop Streng	荷持续1min。 Placing the swit vertical, and the direction of stem	方向放置,从操作 ch such that the en a static load operation for a p	ion is n the Th	S 无机械和电气损坏			
5	手柄拔出强度 Stem Strength	柄的行程范围。 Placing the swit vertical, and the	方向放置, 反方 ch such that the n the maximum f lirection of stem o	orce to withs	switch operat tand a pull ap	ion is	20N.min.	
6	可焊性 Solderabilit	(1) 焊接温度:245 Solder temp ty (2) 浸入时间:2s± Immersion t 对于其它步	shall be made folks $5\pm5^{\circ}\!$	5.6—86》试验	90 Ex coa min	除边缘外涂层应均匀覆盖 90%以上 Except for the edge, the coating should cover a minimum 90%		
APP	ROVE BY	王凱12.05.21	CHECKED BY	李成功12.	05.21 P	RPARE E	許志明12.05.21	



CUSTOMER			CUSTOMER	'S P/N	GYE'	S P/N	PR	ODUCT		REVISION
				TO A	1002T	TAC	T CIVITOI	_		
	75.0				TS-1003T TACT SWITC		SWITCE			
	项目			试验条件					要求	
	ITEM				TEST CON	IDITIONS			RE	QUIREMENTS
	5、极限电气性能: ENVIRONMENTAL SPECIFICATION									
1	低温测试 Resistance low temperat	to ture	(4) 温度 20.0°C							阻: ≤200mΩ t resistance: Ω I.1,4.2,4.3 4.1,4.2,4.3
2	高温测试 Heat resista	nce	标准湿度的 forth below humidity co (1) 温度 tem (2) 时间	temperature:80±2℃						狙: ≤200mΩ t resistance: Ω ł.1,4.2,4.3 4.1,4.2,4.3
3	温度周期性》 Change temperatu	of	样品应放在 试期间样品 After 5 cy allowed to conditions	根据下面的测试要求进行 5 次循环的温度周期性测试,实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试。测试期间样品应保持干燥. After 5 cycles of following conditions, the sample shall be allowed to stand under normal temperature and humidity conditions for 1 h. and measurements shall be made. During the test water drops shall be removed. Temperature Time Conta						
APP	APPROVE BY 王凱1			СН	ECKED BY	李成功12	.05.21	PRPARE	BY	許志明12.05.21



CUSTOMER		CUSTOMER'S P/N		S P/N	PRODUCT		REVISION	
			TS-1	1003T	TACT SWITC	H		
				条件			要求	
	ITEM		TEST CON			R	EQUIREMENTS	
4	湿温测试 Moisture resistance	标准湿度的环境 forth below the s humidity condition (1) 温度: 60 temperatu (2) 相对湿度:	实验条件进行测 中 1 小时后做性 rample shall be rs for 1 h before ±2℃ re: 60±2℃ 90%~95% rmidity:90% to	则试,实验后 生能测试: F : left in norm	F样品应放在常温及 ollowing the test se nal temperature and ents are made:	接触电 Conta ≤200n 项目3	且阻:≤200mΩ ct resistance:	
5	硫化试验 Sulfuration resistance	标准湿度的环境 forth below the s humidity condition (1) H2S气体 H ₂ S gas c (2) 时间: 72 Time: 72h (3) 温度: 40s	H ₂ S gas concentration:					
6	盐雾试验 Salt Mist	The switch sha (1) 温度: 35℃ temperatu (2) 盐溶液浓度 salt solutio (3) 时间: 8h±′ Time: 8h±1 实验后的盐沉积物	在以下设定条件下进行测量: The switch shall be checked after followingtest: (1) 温度: 35℃±2℃ temperature: 35℃±2℃ (2) 盐溶液浓度: 5±1% (质量百分比) salt solution: 5±1%(solids by mass) (3) 时间: 8h±1h Time: 8h±1 hour 实验后的盐沉积物后水冲掉 After test, salt deposit shall be removed by running water.				井上没有腐蚀斑点 No remarkable sion shall be nized in metal part.	
APP	ROVE BY	王凱12.05.21 CH	HECKED BY	李成功12.	05.21 PRPAR	E BY	許志明12.05.21	



CUSTOMER CUSTOMER'S P/N GYE'S P/N PROD TS-1003T TACT S 6、极限机械性能: ENDURANCE SPECIFICATION 项目 试验条件 ITEM TEST CONDITIONS	BUCT REVISION SWITCH 要求 REQUIREMENTS
6、极限机械性能: ENDURANCE SPECIFICATION 项目 试验条件	要求
ENDURANCE SPECIFICATION 项目 试验条件	
项目 试验条件	
ITEM TEST CONDITIONS	REQUIREMENTS
112111 1201 001101110110	
根据下面的测试要求进行测试:	
Measurement shall be made following the test set forth be (1) DC 12V, 50mA带负载 DC 12V, 50 mA resistive load (2) 按动速率: 1次/秒 Rate of operation: 1times/s (3) 按力: 按力的1.5 倍 Operating Force: OperatingForce1.5double (4) 平均无故障寿命: Average fault-freelife 16 1.6 100000次 25 2.5 100000次	接触电阻≤200mΩContact resistance≤200mΩ 触点弹力≤10ms Contact bounce≤10ms 按力: 初值的±30% Operating Force: initial value±30% 项目3,4.1,4.2,4.3 Item 3,4.1,4.2,4.3
根据以下给定条件进行测试: Measurement shall be made following the test set forth be (1) 振动频率范围: 10~55~10Hz Vibration frequency range: 10 to 55 to 10Hz (2) 振幅(峰一峰): 1.5mm Amplitude: 1.5mm Amplitude: 1.5mm 版动万回: 包括手枘行桯万回在内旳二个相互垂直向 Direction of vibration:Three mutually perpendicted direction including the direction of stem travel 例试时间:每次2hours. Duration: Each 2hours.	项目3,4.1,4.2,4.3 Item 3,4.1,4.2,4.3
7. 焊接条件:	
SOLDERING CONDITIONS:	
请按以下条件进行焊接: (1) 焊锡温度: ≤350℃ 手工焊接 (2) 连续焊接时间: ≤3 s Please practice according to below conditions: (1) Soldering temperature: 350℃ Max. (2) Continuous soldering time: 3 sMax.	
APPROVE BY 王凱12.05.21 CHECKED BY 李成功12.05.21 F	PRPARE BY 許志明12.05.21



CUSTOMER		CUSTOMER'S P/N	GYE'S P/N		PRODUCT	REVISION	
			TS-1003T		TACT SWITCH		
	自动浸焊	自动浸焊 项目Items		条件 Condition			
	Conditions for	助焊剂附着量		不附着于零部件贴装面的程度			
	Auto-dip	Flux built-up	Flux built-up		Mounting surface should not be coated with flax		
	,	预热温度	预热温度		印刷电路板焊接面的周围温度100℃ max.		
		Preheating temperature		Ambient temperature of the soldered surface of PC board. 100 ℃ max.			
7.2		预热温度时间 Preheating tim	ie	60s max.			
		焊接温度		260℃ max.			
		Soldering temperature					
	焊接浸渍时间 Continuous dipping time		g time	5s max.			
		焊接次数			2次以下		
	Number of soldering 焊接说明:			2times max.			

1、开关浸焊后,注意不要用溶剂清洗。

After switches were soldered, please be careful not to clean switches with solvent.

1.1 在使用烙铁的情况下,焊锡温度应在350℃以下、3 秒以内。

In the case of using solding iron, solding conditions shall be 350 ℃ max and 3 sec.max.

1.2 浸焊后,注意不要在顶部施加负荷。

Right after switches were soidered; please be careful not to load to on the knobs of switches.

- 2、设计中应注意的事项(Design instructions)
- 2.1 印刷基板的安装孔尺寸参见产品图。

Follow recommended P.W.B. piercing plan in outside drawing page.

- 3、注意点(Note):
- 3.1 注意不要施加超负荷的压力或晃动开关。

Please be cautions not to give excessive static load or shock to swiches.

3.2 开关浸焊后,印刷基板注意不要叠放。

Please be careful not to pile up P.W.B.after switches were soldered.

3.3 保管时尤其应注意避开高湿高温和有腐蚀性气体的环境。如需要长时间保存,请不要 打开包装箱。

Preservation under high temperature and high humidity or corrosive gas should be avoided Especially. When you need to preserve for a long period, do not open the carton.

APPROVE BY	王凱12.05.21	CHECKED BY	李成功12.05.21	PRPARE BY	許志明12.05.21