## **SMT Power Inductors**

Power Beads - PA3784.XXXHL Series





😷 Current Rating: Over 94 Apk

• Inductance Range: 120nH to 180nH

Height: 8.0 mm Max

😎 **Footprint:** 10.0mm x 8.0mm Max

Halogen Free

Electrical Specifications @ 25°C — Operating Temperature - 40°C to +130°C <sup>7</sup>								
Part Number	Inductance <sup>1</sup> @ OA <sub>DC</sub> (nH +/- 10%)	Inductance <sup>2</sup> @Irated (nH TYP)	Irated <sup>3</sup> (ADC)	<b>DCR</b> <sup>4</sup> (mΩ nominal)	Saturation Current <sup>5</sup> (A TYP)		Heating Current <sup>6</sup>	
					25°C	100°C	(A TYP)	
PA3784.121HL	120	120	84	0.18 +/- 5%	94	84	70	
PA3784.151HL	150	150	67		83	67		
PA3784.181HL	180	165	55		67	55		


#### NOTES:


- 1. Inductance measured at 100kHz, 100mVrms.
- 2. Inductance at Irated is the value of the inductance at 25°C at the listed rated current.
- The rated current as listed is either the saturation current (25°C or 100°C) or the heating current depending on which value is lower
- 4. The nominal DCR is measured from point (a) to point (b), as shown below on the mechanical drawing.
- 5. The saturation current is the typical current which causes the inductance to drop by 20% at the stated ambient temperatures (25°C, 100°C and 125°C). This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effects) to the component.
- 6. The heating current is the DC current which causes the part temperature to increase by approximately  $40^{\circ}\text{C}$  when used in a typical application.


- 7. In high volt\*time applications, additional heating in the component can occur due to core losses in the inductor which may necessitate derating the current in order to limit the temperature rise of the component. To determine the approximate total losses (or temperature rise) for a given application, the coreloss and temperature rise curves can be used.
- Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PA3784.121HL becomes PA3784.121HLT).
- Pulse complies to industry standard tape and reel specification EIA481. The tape and reel for this product has a width (W=24mm), pitch (Po=16.0mm) and depth (Ko=8.2mm).
- The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range

Mechanical Schematics

#### PA3784.XXXHL








SUGGESTED LAND PATTERN

8.0 MAX (4.88) b (2x (2.50)



Weight . . . . . . . . . . . . . 2.75 grams

**Dimensions:** mm Unless otherwise specified, all tolerances are ± 0,25

pulseelectronics.com P725.B (9/14)


## **SMT Power Inductors**

Power Beads - PA3784.XXXHL Series


2








## ◆-.121HL\_25C →-.151HL\_25C →-.181HL\_25C




pulseelectronics.com P725.B (9/14)



### PA3784.XXXHL CoreLoss (W)



# PA3784.XXXHL Temp Rise vs Power Dissipation



Total Power Dissipation (W) = CopperLoss + CoreLoss CopperLoss = Irms^2 \* Rdc(mOhms) / 1000 CoreLoss = (from table)

For More	information				
Pulse Worldwide	Pulse Europe				

3

Headquarters Zeppelinstrasse 15
12220 World Trade Drive San Diego, CA 92128 Germany
U.S.A.

Tel: 858 674 8100

Fax: 858 674 8262

Tel: 49 7032 7806 0 Fax: 49 7032 7806 12 Pulse China Headquarters B402, Shenzhen Academy of Aerospace Technology Bldg. 10th Kejinan Road High-Tech Zone

Nanshan District Shenzhen, PR China 518057 Tel: 86 755 33966678 Fax: 86 755 33966700 Pulse North China Room 2704/2705

Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China

Tel: 86 21 62787060 Fax: 86 2162786973 **Pulse South Asia** 

135 Joo Seng Road #03-02 PM Industrial Bldg. Singapore 368363

Singapore 368363

Tel: 65 6287 8998 Fax: 65 6287 8998 Pulse North Asia

3F, No. 198 Zhongyuan Road Zhongli City Taoyuan County 320 Taiwan R. O. C. Tel: 886 3 4356768 Fax: 886 3 4356823 (Pulse) Fax: 886 3 4356820 (FRE)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2014. Pulse Electronics, Inc. All rights reserved.

pulseelectronics.com P725.B (9/14)