


P.C.B EDGE

RECOMMENDED P.C.B LAYOUT
TOLERANCE: + / - 0.05mm



Customer drawing


REVISIONS			
S/N	ECN	DESCRIPTION	DATE
1	HK--	First Release Drawing	20/Aug/13
			APPROVED

D-SUB TECHNICAL DATA

- SHELL : SPCC, 100u" min tin over 50u" min nickel over 50u" copper
BODY : PBT, UL 94V-0, Color:Black.
CONTACTS : Copper Alloy
Gold flash plated over 50u" nickel on mating area
100u" tin plated over 50u" nickel on solder area
BRACKET : Zinc Alloy ,Nickel plated
BOARDLOCK: Copper Alloy,Tin plated
ELECTRICAL : Voltage rating 250V AC(RMS)
Current rating 3A
Withstanding Voltage >1000 V AC(RMS)
Insulation resistance >1000 M Ohms
Contact resistance 25 mOhms max.

PRODUCT CODE

L17H3DD0130



UNLESS OTHERWISE SPECIFIED			
TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	DATE
.X + / -	0.50	CHECKED	20/Aug/13
.XX + / -	0.30	Yong/Tong	20/Aug/13
.XXX + / -	0.20		
FRACTIONS + / -			
ANGLES + / -	5°		
SEE NOTES FOR MATERIALS AND FINISHES			
REMOVE SHARP EDGES			
DIMENSIONS		ANGLE OF PROJECTION	
0-68	TINNES		
100-90	UL		
TITLE		SIZE DRAWING NO.	
Amphenol		A4	
Amphenol East Asia Limited		C L17H3DD0130	
Dual ports D-SUB L17H Series		SCALE	
		NONE	
		SHEET 1 OF 1	
		REV.	
		1	