


## SOT-23 Plastic-Encapsulate MOSFETS

### 30V P-Channel Advanced Power MOSFET

$V_{(BR)DSS}$	$R_{DS(on)}\text{Typ}$	$I_D \text{ Max}$
-30V	43mΩ@ -10V	- 4.1A
	66mΩ@ -4.5V	


### SOT-23



### FEATURE

- Low  $R_{DS(on)}$  @  $V_{GS} = -10V$
- -5V Logic Level Control


### MARKING



### APPLICATION

- Load Switch
- Switching circuits
- High-speed line driver
- Power Management Functions

### Equivalent circuit



### PACKAGE SPECIFICATIONS

Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (pcs)	Box Size (mm)	QTY/Box (pcs)	Carton Size (mm)	Q'TY/Carton (pcs)
SOT-23	7'	178	3000	203×203×195	45000	438×438×220	180000

Maximum Ratings and Thermal Characteristics (TA = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	$V_{DS}$	-30	V
Gate-Source Voltage		$\pm 20$	
Continuous Drain Current	$I_D$	-4.1	A
		-3.2	
Pulsed Drain Current <sup>1)</sup>	$I_{DM}$	-16.4	A
Maximum Power Dissipation <sup>1),2)</sup>	$P_D$	1.2	W
		0.9	
Junction Temperature	$T_J$	150	°C
Storage Temperature	$T_{stg}$	-50 to 150	°C
Thermal Resistance from Junction-to-Ambient ( $t \leq 5s$ )	$R_{\theta JA}$	80	°C/W

#### Notes

1) Pulse width limited by maximum junction temperature.

2) Surface Mounted on FR4 Board,  $t \leq 5$  sec.

The above data are for reference only.



## MOSFET ELECTRICAL CHARACTERISTICS


T<sub>a</sub>=25°C unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
<b>Static</b>						
Drain-source breakdown voltage	V <sub>(BR)DSS</sub>	V <sub>GS</sub> = 0V, I <sub>D</sub> = -250μA	-30			V
Gate-body leakage	I <sub>GSS</sub>	V <sub>GS</sub> = ±20V, V <sub>DS</sub> = 0V			±100	nA
Zero gate voltage drain current	I <sub>DSS</sub>	V <sub>DS</sub> = -30V, V <sub>GS</sub> = 0V			-1	μA
		V <sub>DS</sub> = -24V, V <sub>GS</sub> = 0V			-100	μA
Gate-threshold voltage (note 1)	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = -250μA	-1.2	-1.6	-2.5	V
Drain-source on-resistance (note 1)	R <sub>DS(on)</sub>	V <sub>GS</sub> = -10V, I <sub>D</sub> = -4A		43	55	mΩ
		V <sub>GS</sub> = -4.5V, I <sub>D</sub> = -3A		66	80	
Forward transconductance (note 1)	g <sub>FS</sub>	V <sub>DS</sub> = -5V, I <sub>D</sub> = -4A	5.5			S
<b>Dynamic characteristics (note 2)</b>						
Total Gate C charge	Q <sub>g</sub>	V <sub>DS</sub> = -15V, I <sub>D</sub> = -4A, V <sub>GS</sub> = -10V		8.2		nC
Gate-Source Charge	Q <sub>gs</sub>			0.8		
Gate-Drain Charge	Q <sub>gd</sub>			2.7		
Input capacitance	C <sub>iss</sub>	V <sub>DS</sub> = -15V, V <sub>GS</sub> = 0V, f = 1MHz		493		pF
Output capacitance	C <sub>oss</sub>			65		
Reverse transfer capacitance	C <sub>rss</sub>			44		
<b>Switching characteristics</b>						
Turn-on delay time (note 2)	t <sub>d(on)</sub>	V <sub>DD</sub> = -15V, V <sub>GS</sub> = -10V, I <sub>D</sub> = -1A, R <sub>G</sub> = 3.3Ω		7.2		ns
Rise time (note 2)	t <sub>r</sub>			4.8		
Turn-off delay time (note 2)	t <sub>d(off)</sub>			25		
Fall time (note 2)	t <sub>f</sub>			8.5		
<b>Drain-source body diode characteristics</b>						
Source drain current(Body Diode)	I <sub>SD</sub>				-2	A
Body diode forward voltage (note 1)	V <sub>SD</sub>	I <sub>SD</sub> = -4A, V <sub>GS</sub> = 0V		-0.88	-1.2	V


**Notes :**

1. Pulse Test : Pulse Width ≤ 300μs, Duty Cycle 2 %.
2. These parameters have no way to verify.


### Typical Characteristics




**Fig1.** Typical Output Characteristics




**Fig2.** Normalized Threshold Voltage Vs. Temperature




**Fig3.** Typical Transfer Characteristics



**Fig4.** On-Resistance vs. Drain Current and Gate



**Fig5.** Typical Source-Drain Diode Forward Voltage



**Fig6.** Maximum Safe Operating Area

### Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance





Fig10. Switching Time Test Circuit and waveforms


## Outline Drawing

SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		
	Min	Typ	Max
A	1.00		1.40
A1			0.10
b	0.35		0.50
c	0.10		0.20
D	2.70	2.90	3.10
E	1.40		1.60
E1	2.4		2.80
e		1.90	
L	0.10		0.30
L1	0.4		
θ	0°		10°

## Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance:  $\pm 0.05\text{mm}$ .
3. The pad layout is for reference purposes only.

## **Important Notice and Disclaimer**

Microdiode Electronics (Jiangsu) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Jiangsu) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Jiangsu) assume any liability for application assistance or customer product design. Microdiode Electronics (Jiangsu) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Jiangsu).

Microdiode Electronics (Jiangsu) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Jiangsu).