


Three-terminal Positive Voltage Regulator 78M12

■ Features

- Maximum Output current $I_{o\max}$: 0.5 A
- Output voltage V_o : 12V
- Continuous total dissipation P_D : 1.25W



■ Absolute Maximum Ratings $T_a = 25^\circ C$

Parameter	Symbol	Rating	Unit
Input Voltage	V_i	35	V
Operating Junction Temperature Range	T_{OPR}	0 to +125	°C
Storage Temperature Range	T_{STG}	-65 to +150	°C

■ Electrical Characteristics ($V_{IN}=19V, I_o=350mA, 0^\circ C < T_j < 125^\circ C, C_i=0.33 \mu F, C_o=0.1 \mu F$, unless otherwise specified)

Parameter	Symbol	Testconditions	Min	Typ	Max	Unit
Output voltage	V_o	$T_j=25^\circ C$	11.5	12	12.5	V
		$14.5 \leq V_i \leq 27V, I_o=5mA \sim 350mA, P_o \leq 15W$	11.4	12	12.6	V
Load regulation	ΔV_o	$I_o=5mA \sim 500mA, T_j=25^\circ C$		25	240	mV
		$I_o=5mA \sim 200mA, T_j=25^\circ C$		10	120	mV
Line regulation	ΔV_o	$14.5 \leq V_i \leq 30V, I_o=200mA, T_j=25^\circ C$	10	100	100	mV
		$16 \leq V_i \leq 30V, I_o=200mA, T_j=25^\circ C$	3	50	50	mV
Quiescent current	I_q	$T_j=25^\circ C$	4.6	6.0	6.0	mA
Quiescent current change	ΔI_q	$14.5 \leq V_i \leq 30V, I_o=200mA$		0.8	0.8	mA
		$5mA \leq I_o \leq 350mA$		0.5	0.5	mA
Output noise voltage	V_N	$10Hz \leq f \leq 100KHz, T_j=25^\circ C$	75			μV
Ripple rejection	RR	$15V \leq V_i \leq 25V, f=120Hz, I_{o\max}=300mA$	55	80		dB
Dropout Voltage	V_d	$I_o=350mA, T_j=25^\circ C$		2.0		V
Short Circuit Current	I_{SC}	$V_i=19V, T_j=25^\circ C$		240		mA
Peak Output Current	I_{pk}	$T_j=25^\circ C$		0.7		A

■ Typical Application

