



# SPECIFICATION OF PRODUCT 承认书

| CUSTOMER:      |              |  |
|----------------|--------------|--|
| DESCRIPTION: _ | Piezo Buzzer |  |
| FUSHENG P/N:   | FSR-1325-5V  |  |
| CUSTOMER P/N:  |              |  |
| DATE:          |              |  |

| CUSTOMER | APPROVER   | CHECKER  |
|----------|------------|----------|
|          | Yunqing Wu | Bing Yan |

## 泰州福声电子科技有限公司

地址:江苏省泰州市海陵区凤凰西路98号

电话: 0086-523-86219066 传真: 0086-523-81601108

邮箱: sales@electronic-tech.cn

网址: <u>www.tzfsdz.com</u>

## 1.SPECIFICATION 规格

| No. | ltem                   | Unit | Specification    | Condition                |
|-----|------------------------|------|------------------|--------------------------|
| 1   | Oscillation Frequency  | Hz   | $4000\!\pm\!500$ | square wave              |
| 2   | Operating Voltage      | Vp-р | 3 ~ 30           |                          |
| 3   | Rated Voltage          | Vp-р | 5                |                          |
| 4   | Current Consumption    | mA   | MAX. 8           | at Rated Voltage         |
| 5   | Sound Pressure Level   | dB   | MIN. 75          | at 10cm at Rated Voltage |
| 6   | Electrostatic Capacity | pF   | 25000±30%        | at 100Hz 1V              |
| 7   | Operating Temperature  | °C   | -20 ~ +70        |                          |
| 8   | Storage Temperature    | °C   | -30 ~ +80        |                          |
| 9   | Dimension              | mm   | 13 x H 2.5       | See appearance drawing   |
| 10  | Weight (MAX)           | gram | 2.5              |                          |
| 11  | Housing Material       |      | PBT              |                          |

## 2. APPEARANCE DRAWING 尺寸图



Tol :  $\pm$  0.5 Unit: mm

## 3.TESTING METHOD 测量方式

#### **Standard Measurement conditions**

Temperature:25±2°C Humidity:45-65%

#### Acoustic Characteristics:

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments

shown below.



#### In the measuring test, buzzer is placed as follows:





## 5. Soldering Condition

(1) Recommendable reflow soldering condition is as follows

(Reflow soldering is twice)

Note: It is requested that reflow soldering should be executed

after heat of product goes down to normal.



## 6. RELIABILITY TEST

|   | ITEM   | TEST CONDITION AND REQUIREMENT  |  |  |
|---|--|---|--|--|
| 1 | High Temperature<br>Test (Storage)   | After being placed in a chamber with 802°C for 96 hours and thenbeing placed in normal condition for 2 hours.Allowable variation of SPL after test:10dB.  |  |  |
| 2 | Low Temperature<br>Test (Storage)  | After being Placed in a chamber with -302°C for 96 hours and thenbeing placed in normal condition for 2 hours.Allowable variation of SPL after test:10dB.   |  |  |
| 3 | Humidity Test  | After being Placed in a chamber with 90-95% R.H. at 40 2°C for 96<br>hours and then being placed in normal condition for 2 hours.<br>Allowable variation of SPL after test: 10dB.   |  |  |
| 4 | Temperature Cycle<br>Test  | The part shall be subjected to 5 cycles. One cycle shall be consist of:<br>$+70^{\circ}C$ $+25^{\circ}C$ $+25^{\circ}C$ $-20^{\circ}C$ $0.5hr$ $0.5 + 0.5$ $0.5 + 0.5$ $0.5 + 0.5$ $0.5 + 0.5$ $0.5 + 0.5$ Allowable variation of SPL after test: 10dB. |  |  |
| 5 | Drop Test  | Drop on a hard wood board of 4cm thick, any directions, 6 times,<br>at the height of 75cm.<br>Allowable variation of SPL after test: 10dB.  |  |  |
| 6 | Vibration Test   | After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz         band of vibration frequency to each of 3 perpendicular directions for         2 hours .         Allowable variation of SPLafter test:         10dB.                        |  |  |
| 7 | Solderability       Lead terminals are immersed in rosin for 5 seconds and then         immersed in solder bath of +300       5°C for 3       1 seconds .         90% min. lead terminals shall be wet with solder       (Except the edge of terminals). |   |  |  |
|   | Terminal Strength  | The force of 9.8N(1.0kg) is applied to each terminal in axial direction for<br>10 seconds.<br>No visible damage and cutting off.  |  |  |