




PDFNK 6 5×6-8L Plastic-Encapsulate MOSFETS

CJAC110N03 N-Channel Power MOSFET

V _{(BR)DSS}	R _{DS(on)} TYP	I _D
30V	1.8mΩ@10V	110A
	3.5mΩ@4.5V	



DESCRIPTION

V_{GS} OFF, V_{DS} = 30V, I_D = 110A, R_{DS(on)} = 1.8mΩ @ 10V, 3.5mΩ @ 4.5V


FEATURES

- V_{GS} OFF, V_{DS} = 30V, I_D = 110A, R_{DS(on)} = 1.8mΩ @ 10V, 3.5mΩ @ 4.5V
- P_{tot} = 120W (T_a = 25°C)
- R_{θJA} = 62.5°C/W
- R_{θJC} = 1.04°C/W
- V_{GS} OFF, V_{DS} = 30V, I_D = 110A, R_{DS(on)} = 1.8mΩ @ 10V, 3.5mΩ @ 4.5V

APPLICATIONS


- Switching power supply
- Motor drive

MARKING



CJAC 110N03 XX
 Pin 1 indicator
 XX = Code

EQUIVALENT CIRCUIT



MAXIMUM RATINGS (T_a=25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V _{DS}	30	V
Gate-Source Voltage	V _{GS}	±20	V
Continuous Drain Current	I _D ^①	110	A
Pulsed Drain Current	I _{DM} ^②	440	A
Single Pulsed Avalanche Energy	E _{AS} ^③	800	mJ
Thermal Resistance from Junction to Ambient	R _{θJA} ^⑥	62.5	°C/W
Thermal Resistance from Junction to Case	R _{θJC} ^①	1.04	°C/W
Power Dissipation	P _D ^①	120	W
Junction Temperature	T _J	150	°C
Storage Temperature Range	T _{stg}	-55 ~ +150	°C
Lead Temperature for Soldering Purposes(1/8" from case for 10s)	T _L	260	°C

MOSFET ELECTRICAL CHARACTERISTICS







$T_a=25\text{ }^\circ\text{C}$ unless otherwise specified

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Off characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	30			V
Zero gate voltage drain current	I_{DSS}	$V_{DS} = 24V, V_{GS} = 0V$			1	μA
Gate-body leakage current	I_{GSS}	$V_{DS} = 0V, V_{GS} = \pm 20V$			± 100	nA
On characteristics ^④						
Gate-threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	1.0	1.7	2.5	V
Static drain-source on-state resistance	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 30A$		1.8	2.4	m Ω
		$V_{GS} = 4.5V, I_D = 20A$		3.5	4.3	m Ω
Forward transconductance	g_{FS}	$V_{DS} = 10V, I_D = 2A$		17		S
Dynamic characteristics ^{④ ⑤}						
Input capacitance	C_{iss}	$V_{DS} = 15V, V_{GS} = 0V,$ $f = 1MHz$		4830		pF
Output capacitance	C_{oss}			677		
Reverse transfer capacitance	C_{rss}			639		
Gate resistance	R_g	$f = 1MHz$		0.6		Ω
Switching characteristics ^{④ ⑤}						
Total gate charge	Q_g	$V_{GS} = 4.5V, V_{DS} = 15V,$ $I_D = 24A$		42.5		nC
Gate-source charge	Q_{gs}			12.9		
Gate-drain charge	Q_{gd}			23.4		
Turn-on delay time	$t_{d(on)}$	$V_{DS} = 15V, R_L = 0.75\Omega,$ $V_{GS} = 10V, R_G = 3\Omega$		10		ns
Turn-on rise time	t_r			6.5		
Turn-off delay time	$t_{d(off)}$			75		
Turn-off fall time	t_f			18		
Drain-Source Diode Characteristics						
Drain-source diode forward voltage	V_{SD} ^④	$V_{GS} = 0V, I_S = 10A$			1.0	V
Continuous drain-source diode forward current	I_S ^①				110	A
Pulsed drain-source diode forward current	I_{SM} ^②				440	A

Notes:


1. $T_C=25\text{ }^\circ\text{C}$ Limited only by maximum temperature allowed.
2. $P_W \leq 10\mu s$, Duty cycle $\leq 1\%$.
3. EAS condition: $V_{DD} = 15V, V_{GS} = 10V, L = 0.5mH, R_g = 25\Omega$ Starting $T_J = 25\text{ }^\circ\text{C}$.
4. Pulse Test : Pulse Width $\leq 300\mu s$, duty cycle $\leq 2\%$.
5. Guaranteed by design, not subject to production.
6. The value of $R_{\theta JA}$ is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper, in a still air environment with $T_a = 25\text{ }^\circ\text{C}$.

Typical Characteristics




Typical Characteristics


Capacitances




Gate Charge




Maximum Forward Biased Safe Operating Area




PDFNWB5x6-8L Package Outline Dimensions



Top View
[顶视图]




Bottom View
[背视图]



Side View
[侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.000	0.035	0.039
A3	0.254REF.		0.010REF.	
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
e	1.270TYP.		0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
H	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°

PDFNWB5x6-8L Suggested Pad Layout



Note:


1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.

PDFNWB5×6 Tape and Reel


PDFNWB5×6-8L Embossed Carrier Tape




Packaging Description:
PDFNWB5×6-8L parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 5,000 units per 13" or 33.0 cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
PDFNWB5×6-8L	6.30	5.30	1.10	Ø1.50	1.75	5.50	4.00	8.00	2.00	12.00

PDFNWB5×6-8L Tape Leader and Trailer



PDFNWB5×6-8L Reel



Dimensions are in millimeter						
Reel Option	D	D1	D2	G	W1	W2
13"Dia	Ø330.00	100.00	13.00	1.90	17.60	12.40

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
5,000 pcs	13 inch	5,000 pcs	340×336×29	50,000 pcs	353×346×365