



300V 15A 2.5mm² 28-12AWG
 Poles: 2-12P
 Pitch: 5.0mm(.197"), 5.08mm(.200")

Materials

Housing: PA66 (UL 94V-0)
 Contact: Phosphor Bronze, Nickel Plated.
 Wire Cage: Brass (Nickel Plated) or
 Steel (Zn Plated)
 Screw: M2.5, Steel, A3 Zinc Plated.

序号/revwvo.	更改记录/revision note	签名/signature	日期/date
------------	--------------------	--------------	---------

设计/Designed by	绘图/Drawing by	审核/checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 X': ±2° .X ±0.1 .X' ±1° .XX ±0.05 .XX' ±0.5° .XXX ±0.01
XINLAIYA ELECTRONIC CO., LTD		图名/Title	文件编号/File No.	
新莱亚电子		XY2500F-AS		
		XY2500F-BS	页序/Sheet	
备注/Remark				单位/Units: mm