

承认书 Specifications型 名 TypeGCRH129GLE 部品型号 GLE Part NO.GCRH129 系列接受 Accepted by客户部品型号 Customer's Part No.


外形寸法 Physical dimensions

单位 Unit: mm

RoHS Comp.







备注: 黑色印字 使用材料 Materials

NO.	构成部品 Components	材质 Materials	原产国 Country of origin
1	磁性材料	镍锌铁氧体磁粉	中国
	Magnetic powder	Nickel zinc ferrite magnetic powder	China
2	铜线	改良聚胺脂涂布铜线	德国
	Wire	Polyurethane-system coated copper wire	Germany
3	胶水	环氧树脂	中国
	epoxy	Phenolic epoxy resin	China
4	电极	铜镀锡	中国
	Electrode	Tinned copper	China

2019.10.21			
日期 Date	页 Page	变 更 内 容 Contents of revision	确 认 Check
	日期	日期页	



TEL: 0755-27815501-5503 / 29305001-5003 FAX: 0755-27815500 / 29305500

承认者	审查者	担当者
Approved by	Checked by	Made by
张立华	张顺钧	

GCRH129 Type 一般规格 General Specifications (1/3)				
	项目 Item	规格 Specification	条件 Condition	
1	弯曲测试 Bending test	Change from an initial value L: within±10%	试件焊接在基板上,按箭头方向以大约 0.5mm/秒的速度加压,直到基板变形幅度到 3mm 保持 30 秒。 Apply pressure gradually in the direction of the arrow at a rate of about 0.5mm/s until bent depth reaches 3mm and hold for 30±5s. Pressing device □ 加压治具 R340 ■ 基板 Board: 40X100mm □ Thickness: 1.0mm	
2	固着强度 Adhesion strength	Change from an initial value L: within±10%	按箭头方向用 R0.5 的加压棒在试件中施加一定的静力并保持 60±5 秒. A static load using a R0.5 pressing tool shall be applied the arrow and to the body of the specimen in the direction of the arrow and shall be hold for 60±5s.Measure after removing pressure.	
3	耐振性 Vibration	Change from an initial value L: within±10%	振动频率 $10\sim55\sim10$ Hz,振幅 1.5 mm,分 X,Y,Z 方向各振动 1 小时(共 3 小时)。 The specimen shall be subjected to a vibration of 1.5 mm amplitude, sweep frequency $10\sim55$ Hz (10 Hz to 55 Hz to 10 Hz in a period of one minute) for 1 h in each of $3(X,Y,Z)$ axes.	
4	耐冲击性 Mechanical shock	Change from an initial value L: within±10%	利用橡胶块式落下冲击试验机,分别在 3 个互相垂直的方向以 981 m/S² 的冲击加速度落下。 Peak acceleration: 981 m/S² Duration of pulse: 6ms 3 times in each of 3(X,Y,Z)axes. The specimen must be fixed on test board. Three successive shock shall be applied in the perpendicular direction of each surface of the specimen.	
5	自然落下试验 Free fall test	Change from an initial value L: within±10%	试件安装在基板上,并固定在重 500 克的盒中,由 1 米高自由落体, 3 个互相垂直的方向各 3 次。 The specimen must be fixed on test board. It must be equipped with instruments of which weight is 500g. Then it shall be fallen freely from 1m height to rigid wood 3 times in each of three axes.	
6	焊锡付着性 Solder ability	90%以上的面积要被 覆盖。 New solder shall cover 90% minimum of the surface immersed.	试验品的电极深布松香后,在 $5\sim10$ 秒内焊锡,焊锡槽温度 245 ± 5 °C,时间: 3 ± 0.5 秒。 Terminals shall be immersed for 5 to 10 seconds in flux at room temperature. Dip sample into solder bath containing molten solder at 245 ± 5 °C for 3 ± 0.5 seconds.	
7	焊锡耐热性 Resistance to soldering heat	Change from an initial value L: within ± 10%	试验方法 Test method 热风炉焊接 Reflow soldering method 预热 Preheat 150~180℃ 90±30s 峰值温度 Peak temp 260℃ (230℃min,30±10s) 试验板的厚度 0.8mm 上按上面条件通过两次热风炉。 The specimen shall be subjected to the reflow process under the above condition 2 times. Test board shall be 0.8mm thick. Base material shall be glass epoxy resin. 测定 Measurement 常温常湿中放置于 1 小时以上测试。 The specimen shall be stored at standard atmospheric conditions for 1 h in prior to the measurement.	

GC	GCRH129 Type 一般规格 General Specifications (2/3)				
	项目 Item	规格 Specification	条件 Condition		
8	耐电压 Dielectric strength	没有损害。 Without damage.	在电极与磁材之间加入直流电压 100V 通电时间 1 分钟。 100V DC shall be applied for 60s between the terminal and the core.		
9	绝缘抵抗 Insulation resistance	100MΩ 以上 100MΩ or more.	在电极与磁材之间加入直流电压 100V。 100V DC shall be applied between the terminal and the core.		
10	耐寒性 Low temperature	Change from an initial value L: within ± 10%	在温度-40±3℃中放置 500±12 小时后,常温常湿中放置 1 小时以上 2 小时以内测试。 After stored at a temperature of -40 \pm 3℃ for 500 \pm 12h. The specimen should be measured,then it should be measured under normal temperature and humidity in 1h~ 2h hours.		
11	耐热性 Dry heat	Change from an initial value L: within ± 10%	在温度 85±2℃中放置 500±12 小时后,常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be stored at a temperature of 85±2℃ for 500±12h. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~2h.		
12	耐湿性 Dump heat	Change from an initial value L: within±10%	在温度 60±2℃,湿度 90~95%中放置 500±12 小时后,常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be stored at a temperature of 60±2℃with relative humidity of 90 ~ 95% for 500 ± 12h. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~2h.		
13	温度循环 Temperature cycle	Change from an initial value L : within±10%	以温度-40℃中放置 30 分钟,在 85℃放置 30 分钟,中间转换时间不超过 2 分钟为一个循环。完成 500 个循环后,常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be measured afcer to 500 continuous cycles of temperature change of -40℃ for 30 min and 85℃ for 30 min with the transit period of 2min or less. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~ 2h.		
14	温度特性 Temperature drift	Inductance temperature coefficient 2000 ppm/℃ or less	在温度-25~+ 85℃之间测试。 To be measured in the range of -25℃ to 85℃.		
15	使用温度范围 Operating temperature range	-40 ~ + 125℃	包括制品的发热温度。 Products heating tempratne.		
16	保存温度范围 Storage temperature range	-40 ~ + 85°C *(-40 ~ + 60°C)	在包装的状态下。 In packing state.		

标准状态 Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions in making measurements and test as follows;


Ambient temperature : 5° C to 35° C, Relative humidity: 45% to 85%, Air pressure: 86kPa to 106kPa If more strict measurement is required, measurement shall be made within following limits;

Ambient temperature : $20\pm2^{\circ}$ C, Relative humidity: $65\pm5\%$, Air pressure: 86kPa to 106kPa


GCRH129 Type 一般规格 General Specifications (3/3)

条件 Reflow soldering condition

- 回数:2回
- Reflow times: 2times max
- We recommend infrared ray as heat source of reflow bath.
- However halogen lamp shall be used, side heat will be beyond range of resistance heat, so we can't recommend it.



推荐焊盘寸法 Recommended PCB pattern




单位 Unit: mm

客户部品型号 Customer`s Part No.	GLE 部品型号 GLE Part NO.	中心 InductanceLo (uH)	测定频率 Test Frequency (Hz/v)	直流阻抗 DC Resistance (mΩ) max.	饱和电流 Isat (A) Max. △L/L≧-35%
	GCRH129-101MC	100	1KHz/0.25v	140	2.20
	GCRH129-221MC	220	1KHz/0.25v	300	1.50
	GCRH129-331MC	330	1KHz/0.25v	450	1.20
	GCRH129-471MC	470	1KHz/0.25v	600	1.00
Note: 午容公差 Inductar	nce Tolerance : (特性以实物为准)			
	□ K =±10%				.00/

GCRH129 捆包规格 Packing Specifications


Unit: mm

1. 寸法 Tape Dimensions




А	24.0
В	11.50
С	1.75
D	16.0
E	4.00
F	2.00
G	Ø1.50
Н	0.40

2. 方法 Taping method 冷封 (The direction shall be seen from the top cover tape side.)




3. 卷盘寸法图 Reel dimensions



Α	330.0
В	Ø13.0
С	21.0
D	30.4
E	100
F	26.4

4. 捆包箱 Packing box



- 捆包箱材质 Packing case material 纸 Kraft paper
- 收纳数 Real quantity per packing box 2reel / 1box
- 数量/ 卷 Quantity: 300PCS / reel
- 表示 Marking 客户部品型号,数量,Lot No. Customer's part number, Quantity, Lot number.

禁用物质 Prohibited Subtances

1. RoHS 规制的六种物质

1) 铅及其化合物 Lead and its compounds

2)水银及其化合物 Mercury and its inorganic compounds

3) 镉及其化合物 Cadmium and its compounds

4) 六价铬化合物 Hexavalent chromium compounds

5) 多溴联苯 **PBB**

6) 多溴二苯醚 PBDE

2. 破坏臭氧层的化学物质使用限制

PROHIBITION TO USE OZONE DEPLETING SUBSTANCES (ODS)

限制性物质 Prohibited substances

1) 氟氯化碳 CFCS

2) 氟哌丁苯 Halon

3) 四氯化碳 Carbon tetrachloride

4) 三氯乙烯(三氯乙烷) Trichloroethane (Methy1 chloroform)

我公司保证我司的产品和生产过程符合"RoHS 规则", 所有产品中使用的材料均是化学物质生产规则中登记的材料。

We confirm that our products and our production process accord with "rule of RoHS". All materials used in this product are registered material under Regulation of Manufacture of Chemical Substances.