


ROHS COMPLIANT

REV.	DESCRIPTION	DATE	ECN NO.
01	NEW DESIGN	2018/06/07	-



No. of Contact	A ±0.25 ±.010	B ±0.13 ±.005	C ±0.38 ±.015	D ±0.25 ±.010
09	16.90	25.00	30.80	19.28

REMARKS:

1. MATERIALS AND FINISH
SHELL : STEEL MATERIAL, FRONT NICKEL FINISHED
BACK SHELL, TIN FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS FIBER
CONTACT MATERIAL : BRASS
CONTACT FINISH : FULL GOLD FLASH

2. ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING : 5.0 AMPS
CONTACT PRESSURE : 30 MILLIOWS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGOHMS MIN.
TEMPERATURE RATING : -55°C - +105°C

DRAWN:	JEFF ZHOU	2018.06.07	东莞市赢海电子有限公司 东莞市赢海电子有限公司 D-SUB Male Solder Type
CHECKED:	KEYIN JIN	2018.06.07	
APPROVED:	JINGUO YANG	2018.06.07	
Dimensions in mm(inches) 		Code 000	TITLE:
TOLERANCE UNLESS SPECIFIED: XX ± 0.13		Scale 1:1	REV. 01
		Angles: ±2°	Part No: GDR09M-180°