

NPN-General use transistor

1W 、 1.5A、 30V


Applications:

Can be used for switching and amplifying in various electrical and electronic equipments

MAX RATINGS

parameters	symbol	rating	unit
collector-emitter voltage ($I_B=0$)	V_{CEO}	30	V
collector-base voltage ($I_E=0$)	V_{CBO}	40	V
emitter - base voltage ($I_C=0$)	V_{EBO}	6	V
Collector current	I_C	1.5	A
Total power dissipation ($T_A=25^\circ C$) [*]	P_{tot}	1	W
Max junction temperature	T_{jm}	150	°C
Storage temperature	T_{stg}	-55~150	°C

* mounted on printed circuit board.



1: Base 2: Collector 3: Emitter


ELECTRONIC CHARACTERISTIC (Unless otherwise specified $T_A=25^\circ C$)

parameters	symbol	Test condition	min	typ	max	unit
collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=2mA, I_B=0$	30	—	—	V
collector- base breakdown voltage	$V_{(BR)CBO}$	$I_C=100\mu A, I_E=0$	40	—	—	V
emitter - base breakdown voltage	$V_{(BR)EBO}$	$I_E=100\mu A, I_C=0$	6	—	—	V
Forward current transfer ratio ¹⁾	2SC2883O	$V_{CE}=1V; I_C=100mA$	120		200	—
	2SC2883Y		160	—	320	
collector-base cutoff current	I_{CBO}	$V_{CB}=35V, I_E=0$	—	—	100	nA
emitter-base cutoff current	I_{EBO}	$V_{EB}=6V, I_C=0$	—	—	100	nA
collector-emitter saturation voltage ¹⁾	$V_{CE(sat)}$	$I_C=800mA, I_B=80mA$	—	—	0.5	V
Transition frequency	f_T	$I_C=50mA, V_{CE}=10V, f=100MHz$	—	100	—	MHz

¹⁾ pulse method: $t_w:300\mu s$, duty ratio≤2%.

Outline dimensions (see fig.1)

unit: mm



dimensions symbols	SOT-89		
	min	typ	max
A	1.4		1.6
b	0.35		0.55
b1	0.4		0.65
b2		1.6	
c	0.35		0.45
D	4.4		4.6
E	2.35		2.55
e		1.5	
e1		3	
H _E		4.15	
L		2.7	
L _E		1.0	
α		50	

Fig.1 Outline dimensions