SHG Series

Aluminum Electrolytic Capacitors

Item Name	Rating	Case size	KNSCHA Lifetime
01EC5994	SHG160V22 µ F	Φ 8*12L	10000 hours

1. Operating Temp. Range

-25°C ~ + 105°C

2. Electrical Characteristics See Table 1.

[Table 1]

	-						
Rated Voltage VDC	Surge Voltage VDC	Nominal Static Capacitance (µ F)	Tolerance on Capacitance(%) 20°C 120Hz	Dissipation Factor (tan δ)max 20°C 120Hz			Impedance(Ω) 100KHZ 20℃
160	200	22	-20 ~ +20	0.20	85.4	240	3.5

3. Dimensions



4. Marking

The following items are printed in white on the brown sleeve



① Rated voltage & Nominal Capacitance

- 2 Polarity (negative)
- ③ Trade Mark
- (4) series
- (5) Symbol of Capacitance Tolerance (M)
- 6 Max Operating Temp.

5.MULTIPLIEF	FOR RIPPLE	CURRENT
~		

U.	Frequency Coefficient	
	Freq.(Hz) 40 (FO)	

	Cap(μ F)	60 (50)	120	1K	10K	100K
	0.1-47	0.75	0.80	0.85	0.90	1.00
	68-680	0.80	0.85	0.90	0.95	1.00
	1000-22000	0.85	0.87	0.89	0.92	1.00
(2).	Temperature Coe	efficient				
	Ambient	40	60	70	85	105
	Temperature(°C)		00	10		
	Coefficient	2.40	2.10	1.78	1.65	1.00

6. Characteristics

No.	Item	Performance	Test Method	
1	Leakage Current	I= 85.4 μA (I=0.02CV+15 μ A) I= Max Leakage Current C=Ctatic Capacitor: V=Rated Voltage	Protection Resistor : $1000\pm10\Omega$ Applied Volt : Rated Voltage Mesauring time : 5minutes	
2	Static Capacitance	17.6 \sim 26.4 μ F	Measured Frequency : 120Hz±20% Measured Voltage ≤ 0.5Vrms, 1.5 ~ 2.0VDC	
3	Dissiption Factor (tanδ)	0.20 and Under	Same as condition of Capacitors	
4	High Temp. Load Charac- teristics	Leakage Current \leq the value specified in Table 1Cap. Change $\leq \pm 20\%$ of initial valueDissipation Factor $\leq 200\%$ of value specified in TableAppearanceNo remarkable abnormality	Test Temp. : 105±2°C Applied voltage: Rated voltage Test Time :10,000 hours +72, -0 hours	
5	High Temp. no load Charac- teristics	Leakage Current \leq the value specified in Table 1Cap. Change $\leq \pm 20\%$ of initial valueDissipation Factor $\leq 200\%$ of value specified in TableAppearanceNo remarkable abnormality	Test Temp. : 105±2°C No voltage applied Test Time :1000 hours +24, -0 hurs	
6	Terminal Strength	Tensile Strength45N {4.5kg}Bending Strength25N {2.5kg}	Keeping time Tensile 1~5sec Bending 30±5sec	
7	Impedance Ratio	W V 160 Z-25°C/Z+20°C 3 Z-40°C/Z+20°C 4		
8	Temperature Charac - teristics	StageItemPerformanceStageTest Temp(°C)2,3Impedance Ratioless than the value mentioned in 5-7,1 20 ± 2 5Cap, Change $\leq \pm 25\%$ against value in stage 42 $-25\pm 3;$ 3 $-25\pm 3;$ 4 20 ± 2 After the capacitor is held at tempereture of each stage and reaches temperature stability, measure performance.5 105 ± 2		
9	Surge Voltage	Item Perforemance Leakage Current ≤ the initial specified value Cap, Change ≤ ±15% against value be Dissipation Factor ≤ the initial specified value Appearance No remakable abnormalit Test Temp. 15~35°C Test volt. Surge Volt.S Voltage apply. 1,000times of chage for 30±5sec, und and discharge for 5min30sec. 1	fore test ue y Specified in 2	

No,KNS-20200415001 (2/5)

6-2. Characteristics

No.	Item	Performance	Test Method
10	Vibration Resistance	CapacitanceStability requiredCap. Change≤±5% of the initial specifiAppearanceNo remarkable abnormaliFrequency : 10~55Hz/1min. Width of vibrationalityY and Z directions, each for 2 hours (Total	ty tion, 1.5mm Direction and duration X,
11	Solderbility	3/4 area of surrounding directions of surface should be covered with new solder.	Solder: Sn-Ag, Sn-Cu Type Soldering Temp : 240±5°C Dipping degree : 2~2.5mm Flux : Ethanol solution (JIS K8101) or Isopropylalchol (JIS K8839) solution of Rosin (JIS K5902)
12	Resistance to Soldering	Leakage Current \leq Initial specified valueCap. Change $\leq \pm 10\%$ of initial valueDissipation Factor \leq Initial specified in valueAppearanceNo remarkable abnormality	Soldering Temp. 280±5°C Soldering Time . 10±1sec.
13	Resistance to Humidity	Leakage Current \leq Initial specified valueCap. Change $\leq \pm 15\%$ of initial valueDissipation Factor \leq Initial spesified valueAppearanceNo remarkable abnormality	Test Temp. : $40\pm2^{\circ}C$ Humidity 90~95% Test Time : 500 \pm 8 hours After the above condition,restored to normal temp, and then measured.
14	Perssure valve moment charact- erstics	There must not be thing ignition, scattering the resolution that that case works safely	Dcmethod: impress the reverse voltage and of 1A, I cancel an electric current.

7 Packing method

Packaging shape, size, quantity



Component	Quanity
size	per
8*12	24000pcs.

- Related Standards JIS C 5141 8
- Marking on packing box 9
 - 1 Item name
 - 2 Series name

 - 3 Rated Voltage
 4 Nominal Static Capacitance
 5 Case size

 - 6 Lot No.
 - Quantity

10 Leakage

current <Condition>

Connecting the capacitor with a protective resistor $(1k\Omega \pm 10\Omega)$ in series for

2 minutes, and then, measure leakage current

<Criteria

I : Leakage current (μA) I (μA) \leq 0.02CV+15 (μA) whichever is greater, measurement circuit refer to right drawing. C: Capacitance (μF)



11 Soldeing

11-1 Soldering by soldering iron

I emperature of iron top : $270 \sim 350^{\circ}$ C Operating time : within 3 sec.

11-2 Flow soldering.

Preheat : PCB surface temperature $120^{\circ}C\pm5^{\circ}C$ Solder Temp : $260^{\circ}C\pm5^{\circ}C$ Solder Dipping Temp. : $2\sim4$ sec.

12 Cleaning of PC boad after soldering

Using follwing solvents is possible but make sure followingcondition Solvent

Solvent

IPA or Alcoholic agent like Pinealpha ST-100S, Cleanthrough 750H, 750L, 710M, 750K, or Technocare FRW-14 ${\sim}17$

- ① Cleaning should be made by ultrasonic within 5min, at the temperature less then 60°C.
- (2) Control of pollution is necessary (conductivity,pH, specific gravity, water volume)
- ③ Please do not keep near cleaning agent. Please do not store in air-tight container. Please let it dry by hot air at the temperature less than maximum operating temp.

13 The situation of using

- Please do not use a condenser in the next use environment.
- 1 One circumference environment (weatherability) condition.
- (a) Direct water, salt water and environment oil works or become a dew condensation state.
- (b) Environment full of harmful gas (a hydrogen chloride, sulfurous acid.

nitrous acid hydrochloric acid, ammonia).

- (c) Ozone, infrared rays and the environment where radioactive rays are done collation of
- ② Vibration shock condition is extreme environment more than rule ranges of delivery specifications.
- 14 A country of origin

15

A country of origin of an KNSCHA SHG series alminum electrolysis condenser of specifications:

- China
- Effective life for storage

Storage conditions:

- ① Temperature range must be between 5-35°C
- 2 Relative humidity must be less than 75%
- ③ Must be stored indoor
- ④ Must be free from water, oil or salt water
- 5 Must be free from toxic gasses (hydrogen sulfide, sulfurous acid, chlorine, ammonium, etc.)
- 6 Must be free from ozone, ultraviolet rays or any other radiation
- ⑦ Must be kept in capacitor original package

No,KNS-20200415001 (4/5)

Aluminum Electrolytic Capacitor SHG Series Structure



Controls of ozone layer destructive chemical materials

Regulated materials : CFCs, Halon, Carbon Tetrachloride, 1.1.1-Trichloroethane The products and parts do not include the above materials The products and parts are not used the above materials on process.

The products and parts are not used PBBOs (Poly Bromo Bi-phenyl Oxides).

All materials are mentioned as existing chemical material in the "Law of examine and control of Production of Chemical Material"

The products are not listed in Appendix 1 of Export Trade Rule and Regulation

A condenser of this series supports RoHS regulation.