N-Channel 20 V (D-S) MOSFET

PRODUCT SUMMARY	
V_{DS} (V)	20
$R_{DS(on)}$ max. (Ω) at V_{GS} = 4.5V	0.020
$R_{DS(on)}$ max. (Ω) at V_{GS} = 2.5V	0.025
Q_g typ. (nC	4.0
I_D (A) [a, e]	7
Configuration	Single

FEATURES

- TrenchFET® power MOSFET
- Low on-resistance
- 100 % R_g tested
- Material categorization: for definitions of compliance please see

Pb-free
RoHS COMPLIANT

SOT-23





N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)				
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-source voltage		V_{DS}	20	V
Gate-source voltage		V_{GS}	± 12	
Continuous drain current (T_J = 150 °C)	T_C = 25 °C	I_D	7 [e]	A
	T_C = 70 °C		5[e]	
	T_A = 25 °C		5.0 [b, c]	
	T_A = 70 °C		4.4 [b, c]	
Pulsed drain current (t = 300 µs)		I_{DM}	26	
Continuous source-drain diode current	T_C = 25 °C	I_S	2.1	
	T_A = 25 °C		1.1 [b, c]	
Maximum power dissipation	T_C = 25 °C	P_D	2.8	W
	T_C = 70 °C		1.6	
	T_A = 25 °C		1.3 [b, c]	
	T_A = 70 °C		0.8 [b, c]	
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +150	°C
Soldering recommendations (peak temperature)			260	

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT
Maximum junction-to-ambient [b, d]	t ≤ 5 s	R_{thJA}	75	100	°C/W
Maximum junction-to-foot (drain)	Steady state	Rt_{hJF}	40	50	

Notes

a. Based on T_C = 25 °C
b. Surface mounted on 1" x 1" FR4 board
c. t = 5 s
d. Maximum under steady state conditions is 166 °C/W
e. Package limited

SPECIFICATIONS (T_J = 25 °C, unless otherwise noted)						
PARAMETER	**SYMBOL**	**TEST CONDITIONS**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
Static						
Drain-source breakdown voltage	V_{DS}	V_{GS} = 0 V, I_D = 250 µA	20	-	-	V
V_{DS} temperature coefficient	$\Delta V_{DS}/T_J$	I_D = 250 µA	-	30	-	mV/°C
$V_{GS(th)}$ temperature coefficient	$\Delta V_{GS(th)}/T_J$		-	-4.8	-	
Gate-source threshold voltage	$V_{GS(th)}$	V_{DS} = V_{GS} , I_D = 250 µA	0.5	-	1.5	V
Gate-source leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 20 V	-	-	± 100	nA
Zero gate voltage drain current	I_{DSS}	V_{DS} = 20V, V_{GS} = 0 V	-	-	1	µA
		V_{DS} = 20V, V_{GS} = 0 V, T_J = 70 °C	-	-	10	
On-state drain current [a]	$I_{D(on)}$	$V_{DS} \leq$ 5 V, V_{GS} = 10 V	20	-	-	A
Drain-source on-state resistance [a]	$R_{DS(on)}$	V_{GS} = 4.5V, I_D = 5.5 A	-	0.020	-	Ω
		V_{GS} = 2.5 V, I_D = 5 A	-	0.025	-	
Forward transconductance [a]	g_{fs}	V_{DS} = 15 V, I_D = 5.5 A	-	24	-	S
Dynamic [b]						
Input capacitance	C_{iss}	V_{DS} = 10 V, V_{GS} = 0 V, f = 1 MHz	-	424	-	pF
Output capacitance	C_{oss}		-	100	-	
Reverse transfer capacitance	C_{rss}		-	42	-	
Total gate charge	Q_g	V_{DS} = 10 V, V_{GS} = 10 V, I_D = 5.5 A	-	8.2	13	nC
		V_{DS} = 10 V, V_{GS} = 4.5 V, I_D = 5.5 A	-	4.2	7	
Gate-source charge	Q_{gs}		-	1.4	-	
Gate-drain charge	Q_{gd}		-	1.4	-	
Gate resistance	R_g	f = 1 MHz	2.5	12.6	25.2	Ω
Turn-on delay time	$t_{d(on)}$	V_{DD} = 10 V, R_L = 3.4 Ω $I_D \cong$ 4.4 A, V_{GEN} = 4.5 V, R_g = 1 Ω	-	6	12	ns
Rise time	t_r		-	20	30	
Turn-off delay time	$t_{d(off)}$		-	14	21	
Fall time	t_f		-	10	20	
Turn-on delay time	$t_{d(on)}$	V_{DD} = 10 V, R_L = 3.4 Ω $I_D \cong$ 4.4 A, V_{GEN} = 10 V, R_g = 1 Ω	-	3	6	
Rise time	t_r		-	11	20	
Turn-off delay time	$t_{d(off)}$		-	20	30	
Fall time	t_f		-	7	14	
Drain-Source Body Diode Characteristics						
Continuous source-drain diode current	I_S	T_C = 25 °C	-	7	-	A
Pulse diode forward current	I_{SM}		-	-	25	
Body diode voltage	V_{SD}	I_S = 4.4 A, V_{GS} = 0 V	-	0.82	1.2	V
Body diode reverse recovery time	t_{rr}	I_F = 4.4 A, di/dt = 100 A/µs, T_J = 25 °C	-	13	20	ns
Body diode reverse recovery charge	Q_{rr}		-	6	12	nC
Reverse recovery fall time	t_a		-	8	-	ns
Reverse recovery rise Time	t_b		-	5	-	

Notes

a. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %

b. Guaranteed by design, not subject to production testing

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Output Characteristics



Transfer Characteristics



On-Resistance vs. Drain Current and Gate Voltage



Capacitance



Gate Charge



On-Resistance vs. Junction Temperature

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Source-Drain Diode Forward Voltage



On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage



Single Pulse Power (Junction-to-Ambient)



* V_{GS} > minimum V_{GS} at which $R_{DS(on)}$ is specified

Safe Operating Area, Junction-to-Ambient

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating [a]



Power Derating, Junction-to-Foot



Power Derating, Junction-to-Ambient

Note

a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Foot

SOT-23 (TO-236): 3-LEAD



Dim	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	0.89	1.12	0.035	0.044
A_1	0.01	0.10	0.0004	0.004
A_2	0.88	1.02	0.0346	0.040
b	0.35	0.50	0.014	0.020
c	0.085	0.18	0.003	0.007
D	2.80	3.04	0.110	0.120
E	2.10	2.64	0.083	0.104
E_1	1.20	1.40	0.047	0.055
e	0.95 BSC		0.0374 Ref	
e_1	1.90 BSC		0.0748 Ref	
L	0.40	0.60	0.016	0.024
L_1	0.64 Ref		0.025 Ref	
S	0.50 Ref		0.020 Ref	
q	3°	8°	3°	8°
ECN: S-03946-Rev. K, 09-Jul-01 DWG: 5479				

RECOMMENDED MINIMUM PADS FOR SOT-23



Recommended Minimum Pads
Dimensions in Inches/(mm)

Return to Index

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be oHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.