

規 格 承 認 書

PECIFICATION FOR APPROVAL

客 戶

CUSTOMER : 立创

項 目

ITEM : 贴片式电磁无源蜂鸣器（外部驱动）

型 號

TYPE : GSC9032RB-16R2700

描述

DESCRIPTION : $\phi 9.0 \times 3.2$ MM 2700Hz 16Ω ≥ 85 DB 侧发音 LCP 材质

客戶料號

CUSTOMER NO. :

規 格 書 號

SPECIFICATION NO.:

版 本

EDITION NO. : V1.0

日 期

DATE : 2019-12-26

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查 TESTED BY	審核 CHECKED BY	承認 APPROVED BY

東莞市贏海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作 ISSUED BY	審查 CHECKED BY	確認 APPROVED BY
周明		

地址：廣東省東莞市長安鎮厦边元灶头工业区 16-6 號

電話 / TEL: 0769-83060958 傳真 / FAX: 0769-81608993

網址：HTTP://WWW.INGHAI.COM


A. SCOPE

This specification applies magnetic buzzer, GSC9032RB-16R2700


B. SPECIFICATION

No.	Item	Unit	Specification	Condition
1	Oscillation Frequency	Hz	2700	Vo-p=1/2duty , square wave
2	Operating Voltage	Vo-p	2 ~ 4	
3	Rated Voltage	Vo-p	3.6	
4	Current Consumption	mA	MAX. 80	at Rated Voltage
5	Sound Pressure Level	dB	Min.85	at 10cm at Rated Voltage
6	Coil Resistance	Ω	16±3	
7	Operating Temperature	°C	-20 ~ +80	
8	Storage Temperature	°C	-30 ~ +85	
9	Dimension	mm	9.0 x H3.2	See appearance drawing
10	Environmental Protection Regulation		RoHS	


C. APPEARANCE DRAWING Tol : ± 0.3 Unit: mm



D:TEST METHOD:




Test Circuit




Test Equipps

E:FREQUENCY RESPONSE:




F:RELIABILITY TEST

NO.	ITEM	TESTING CONDITION	VARIANCE AFTER TEST
1	<i>High temp. storage life</i>	The part shall be capable of withstanding a storage temperature is +80°C for 120 hours	
2	<i>Low temp. storage life</i>	The part shall be capable of withstanding a storage temperature is -30°C for 120 hours	
3	Temp. Cycle	Total 5 cycles, 1 cycle consisting of $-30 \pm 2^\circ\text{C}$, 30 minutes $20 \pm 5^\circ\text{C}$ 15 minutes $80 \pm 2^\circ\text{C}$, 30 minutes $20 \pm 5^\circ\text{C}$ 15 minutes	
4	Humidity Test	$40 \pm 2^\circ\text{C}$, 90~95% RH, 120 hours	<i>After the test the part shall meet specifications without any degradation in appearance and performance except SPL shall be initial value $\pm 10\text{dB}$ or more.</i>
5	Vibration Test	The part shall be subjected to a vibration cycle is 10Hz in a period of 1 minute. Total peak amplitude shall be .52mm(9.3g). The vibration test shall consist of 2 hours per plane in each three mutually perpendicular planes for a total time of 6 hours.	
6	Shock	Sounder shall be measured after being applied shock (980m/s^2) for each three mutually perpendicular directions to each of 3 times by half sine wave.	
7	Drop Test	Dropped naturally from 700mm height onto the surface of 10mm thick wooden board. 2 directions-upper and side of the part are to be applied.	
8	Lead pull	The part shall be pushed with a force of 9.8N for 10 ± 1 seconds behind the part. 	After the test part shall meet specifications without any degradation in appearance and performance.
9	Recommended temp. Profile for Reflow Oven	Shown in Fig.1	



Warranty:For a period of one year from date of manufacture under normal operations.

G: Recommended Temp. Profile for Reflow Oven (Fig.1)




Profile Feature	Pb-Free Assembly
Average ramp-up rate(T_L to T_p)	3°C/second max.
Preheat	
-Temperature Min.($T_{S\min}$)	150°C
-Temperature Min.($T_{S\max}$)	200°C
-Temperature Min.(ts)	60~180 seconds
$T_{S\max}$ to T_L	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
- Temperature(T_L)	217°C
-Time(T_L)	60~150 seconds
Peak temperature(T_p)	250°C+0/-5°C
Time within 5°C of actual Peak temperature (tp)	6 seconds max.
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

H: PACKING:



PACKING:



NOTES:

1. 1800 PCS per box
2. Total 10 boxes per carton
3. Total 8000 PCS carton