

General Description

The WSF15N10G uses advanced SGT MOS technology to provide low $R_{DS(ON)}$, low gate charge, fast switching and excellent avalanche characteristics. This device is specially designed to get better ruggedness and suitable to use in Synchronous rectification applications

Features

- advanced SGT MOS technology
- Low gate charge
- Low $R_{DS(ON)}$


Product Summary

BVDSS	$R_{DS(ON)}$	I_D
100V	75m Ω	15A

Applications

- Fast Switching
- DC-DC Power System
- Load Switch

TO-252 Pin Configuration



Absolute Maximum Ratings at $T_j=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current ¹⁾	15	A
$I_{D, pulse}$	Pulsed Drain Current ²⁾	45	A
E_{AS}	Single Pulse Avalanche Energy ⁴⁾	5.5	mJ
P_D	Total Power Dissipation ³⁾	36	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ⁵⁾	---	62	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case	---	3.5	$^\circ\text{C/W}$

Electrical Characteristics (T_J=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	100	---	---	V
ΔBV _{DSS} /ΔT _J	BVDSS Temperature Coefficient	Reference to 25°C, I _D =1mA	---	0.098	---	V/°C
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =10V, I _D =5A	---	50	75	mΩ
		V _{GS} =4.5V, I _D =2A	---	60	90	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	1.2	2.0	2.7	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =80V, V _{GS} =0V, T _J =25°C	---	---	1	uA
		V _{DS} =80V, V _{GS} =0V, T _J =55°C	---	---	5	
I _{GSS}	Gate-Source Leakage Current	V _{GS} =±20V, V _{DS} =0V	---	---	±100	nA
R _g	Gate Resistance	V _{DS} =0V, V _{GS} =0V, f=1MHz	---	28.8	---	Ω
Q _g	Total Gate Charge (10V)	V _{GS} =10V, V _{DS} =50V, I _D =5A	---	6.5	---	nC
Q _{gs}	Gate-Source Charge		---	1.4	---	
Q _{gd}	Gate-Drain Charge		---	1.4	---	
T _{d(on)}	Turn-On Delay Time	V _{GS} =10V, V _{DS} =50V, R _G =2Ω, I _D =5A	---	14	---	ns
T _r	Rise Time	---	3.2	---		
T _{d(off)}	Turn-Off Delay Time	---	36	---		
T _f	Fall Time	---	14	---		
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =25V, f=100KHz	---	410	---	pF
C _{oss}	Output Capacitance	---	---	80	---	
C _{rss}	Reverse Transfer Capacitance	---	---	50	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous diode current ¹⁾	V _G =V _D =0V, Force Current	---	---	15	A
I _{SP}	Pulsed diode current ²⁾		---	---	45	A
V _{SD}	Diode Forward Voltage ²⁾	V _{GS} =0V, I _S =5A, T _J =25°C	---	---	1.3	V
t _{rr}	Reverse Recovery Time	I _F =5A, dI/dt=100A/μs, T _J =25°C	---	36	---	nS
Q _{rr}	Reverse Recovery Charge		---	37	---	nC

- 1) Calculated continuous current based on maximum allowable junction temperature.
- 2) Repetitive rating; pulse width limited by max. junction temperature.
- 3) Pd is based on max. junction temperature, using junction-case thermal resistance.
- 4) V_{DD}=50V, R_G=25Ω, L=0.3mH, starting T_J=25°C.
- 5) The value of R_{θJA} is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper, in a still air environment with T_a=25°C.

Typical Characteristics




Figure 1, Typ. output characteristics

Figure 2, Typ. transfer characteristics




Figure 3, Typ. capacitances

Figure 4, Typ. gate charge




Figure 5, Drain-source breakdown voltage

Figure 6, Drain-source on-state resistance




Figure 7, Threshold voltage




Figure 8, Forward characteristic of body diode




Figure 9, Drain-source on-state resistance




Figure 10, Drain current




Figure 11, Safe operation area $T_C=25\text{ }^\circ\text{C}$





Figure 12, Max. transient thermal impedance



SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.38
A1	0	-	0.10
A2	0.9	1.01	0.10
b	0.72	-	0.85
b1	0.71	0.76	0.81
b2	0.72	-	0.90
b3	5.13	5.33	5.46
c	0.47	-	0.60
c1	0.46	0.51	0.56
c2	0.47	-	0.60
D	6.00	6.10	6.20
D1	5.25	-	-
E	6.50	6.60	6.70
E1	4.70	-	-
e	2.186	2.286	2.386
H	9.80	10.10	10.40
L	1.40	1.50	1.70
L1	2.90 REF		
L2	0.508 BSC		
L3	0.90	-	1.25
L4	0.60	0.80	1.00
L5	0.15	-	0.75
L6	1.80 REF		
θ	0°	-	8°
θ1	5°	7°	9°
θ2	5°	7°	9°



Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5, In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you intend to use.
- 9, this catalog provides information as of Sep. 2014. Specifications and information herein are subject to change without notice.