




7	压柄	SUS	
6	触点	银合金	
5	端子	C2680	镀银
4	弹片	C5210	
3	按钮	PBT	白色
2	上盖	PBT	黑色
1	底座	PBT	白色
序号	名称	材料	备注



Rating	DC30V 100mA	Electrical Life	1000,000 cycles
Contact Resistance	500mΩ Max	Mechanical Life	1000,000 cycles
Insulation Resistance	>100MΩ DC500V	Ambient Temper. Used	-25℃ to +85℃
Withstand Voltage	AC500V 1min.	Ambient Humidity Used	≤85% at +40℃
Soldering Temper.	235±5℃ 5s	Operating Force	20±15gf max

ΔX		ANGULAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE: MICRO SWITCH
ΔX		L ≤ 4	±0.2	DWN	DATE	VIEW:	PART NO.:
ΔX		4 < L ≤ 16	±0.3	CHKD	DATE	UNIT: mm	DWG NO.: DM1-135P-1-16
ΔX		16 < L ≤ 63	±0.4	APPD	DATE	SIZE: A4	WEIGHT: 1.0g
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO., LIMITED	
		REVISIONS					SHEET 1/1
		www.xk-dg.cn	www.helloxkb.com	www.helloxkb.cn			REVISION A0