


# P-CHANNEL ENHANCEMENT MODE VERTICAL DMOS FET

ISSUE 2 – MARCH 94

**ZVP0545A**

## FEATURES

- \* 450 Volt  $V_{DS}$
- \*  $R_{DS(on)}=150\Omega$



## ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Drain-Source Voltage	$V_{DS}$	-450	V
Continuous Drain Current at $T_{amb}=25^\circ C$	$I_D$	-45	mA
Pulsed Drain Current	$I_{DM}$	-400	mA
Gate Source Voltage	$V_{GS}$	$\pm 20$	V
Power Dissipation at $T_{amb}=25^\circ C$	$P_{tot}$	700	mW
Operating and Storage Temperature Range	$T_j:T_{stg}$	-55 to +150	°C

## ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^\circ C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS.
Drain-Source Breakdown Voltage	$BV_{DSS}$	-450		V	$I_D=-1mA, V_{GS}=0V$
Gate-Source Threshold Voltage	$V_{GS(th)}$	-1.5	-4.5	V	$I_D=-1mA, V_{DS}=V_{GS}$
Gate-Body Leakage	$I_{GSS}$		20	nA	$V_{GS}=\pm 20V, V_{DS}=0V$
Zero Gate Voltage Drain Current	$I_{DSS}$		-20 -2	$\mu A$ mA	$V_{DS}=-450 V, V_{GS}=0$ $V_{DS}=-360 V, V_{GS}=0V,$ $T=125^\circ C(2)$
On-State Drain Current(1)	$I_{D(on)}$	-100		mA	$V_{DS}=-25 V, V_{GS}=-10V$
Static Drain-Source On-State Resistance (1)	$R_{DS(on)}$		150	Ω	$V_{GS}=-10V, I_D=-50mA$
Forward Transconductance (1)(2)	$g_{fs}$	40		mS	$V_{DS}=-25V, I_D=-50mA$
Input Capacitance (2)	$C_{iss}$		120	pF	$V_{DS}=-25 V, V_{GS}=0V, f=1MHz$
Common Source Output Capacitance (2)	$C_{oss}$		20	pF	
Reverse Transfer Capacitance (2)	$C_{rss}$		5	pF	
Turn-On Delay Time (2)(3)	$t_{d(on)}$		10	ns	$V_{DD}\approx-25V, I_D=-50mA$
Rise Time (2)(3)	$t_r$		15	ns	
Turn-Off Delay Time (2)(3)	$t_{d(off)}$		15	ns	
Fall Time (2)(3)	$t_f$		20	ns	

(1) Measured under pulsed conditions. Width=300μs. Duty cycle ≤2%

(2) Sample test.