


- Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 20\text{m}\Omega$
- After environmental testing: $\leq 40\text{m}\Omega$

X1511 W R S-XX HF-LP SW XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Series No.

② Category: W-wafer

③ Welding Board Angle: R- Right Angle 90°

④ Welding Way: S-SMT




⑤ Row No.-Pin No.: XX-02P~15P

⑥ Plug the Pin & Special No.: HF-Halogen Free

⑦ Material: LP -LCP 94V-0

⑧ **Planting Category:** SW- Matte Tin Plating

⑨ Color: Blank-Natural Color



SECTION A-A
SCALE 1:1

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	1.50	4.30	3.40	09	12.00	14.80	13.90
03	3.00	5.80	4.90	10	13.50	16.30	15.40
04	4.50	7.30	6.40	11	15.00	17.80	16.90
05	6.00	8.80	7.90	12	16.50	19.30	18.40
06	7.50	10.30	9.40	13	18.00	20.80	19.90
07	9.00	11.80	10.90	14	19.50	22.30	21.40
08	10.50	13.30	12.40	15	21.00	23.80	22.90

△	X1511WRS-XXHF-LPSW	LCP UL 94V-0 Halogen Free	Brass	Matte Tin Plating	X1511H
	X1511WRS-XX-LPSW	LCP UL 94V-0			
	PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

Recommended P.C.B Layout
General Tolerance±0.05

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

XKB INDUSTRIAL PRECISION CO., LIMITED 香港星坤工業精密有限公司						ANGULAR	± 5°	DWN	DATE	VIEW: 	XJST1WR3-XXHP-LPSW				
△ X						L ≤ 4	± 0.2	CHKD	DATE	UNIT: mm	PART NO.:				
△ X						4 < L ≤ 16	± 0.3				1.50mm Crimp Style Connectors				
△ X						16 < L ≤ 63	± 0.4				DWG NO.:				
MARK	DESCRIPTION				DATE	REVISED	APPROVED	APPD	DATE	SIZE: A4					
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
Authorized Signature(s)													1.0a	1/1	A0