


# DFN1006-3L Plastic-Encapsulate MOSFETs

## CJBA7002K N-Channel MOSFET

$V_{(BR)DSS}$	$R_{DS(on)MAX}$	$I_D$
60V	1.5Ω@10V	0.41A
	1.8Ω@4.5V	




### FEATURE

- Low On-Resistance
- Low Threshold Voltage
- Fast Switching Speed
- ESD Protected Gate

### APPLICATION


- Load Switch
- Portable Applications
- Power Management Functions

### MARKING:



Top View  
Bar Denotes Gate  
and Source Side

### Equivalent Circuit



### ABSOLUTE MAXIMUM RATINGS ( $T_a=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	60	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current	$I_D$	0.41	A
		0.30	
Pulsed Drain Current	$I_{DM}$	1.2	A
Power Dissipation	$P_D$	0.1	W
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	1250	$^\circ\text{C}/\text{W}$
Storage Temperature	$T_{STG}$	-55~+150	$^\circ\text{C}$

# MOSFET ELECTRICAL CHARACTERISTICS

MOSFET ELECTRICAL CHARACTERISTICS( $T_a=25^\circ\text{C}$  unless otherwise noted)







Parameter	Symbol	Test Condition	Min	Type	Max	Unit
<b>Static Characteristics</b>						
Drain-source breakdown voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$	60			V
Zero gate voltage drain current	$I_{\text{DSS}}$	$V_{\text{DS}} = 60\text{V}, V_{\text{GS}} = 0\text{V}$			100	nA
Gate-body leakage current	$I_{\text{GSS}}$	$V_{\text{GS}} = \pm 20\text{V}, V_{\text{DS}} = 0\text{V}$			$\pm 10$	$\mu\text{A}$
		$V_{\text{GS}} = \pm 5\text{V}, V_{\text{DS}} = 0\text{V}$			$\pm 1$	
Gate threshold voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}} = V_{\text{GS}}, I_D = 250\mu\text{A}$	1.3	1.4	2.3	V
Drain-source on-resistance <sup>a</sup>	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = 10\text{V}, I_D = 40\text{mA}$		1.2	1.5	$\Omega$
		$V_{\text{GS}} = 4.5\text{V}, I_D = 35\text{mA}$		1.3	1.8	
Forward transconductance <sup>a</sup>	$g_{\text{fs}}$	$V_{\text{DS}} = 5\text{V}, I_D = 40\text{mA}$	100			mS
Diode forward voltage	$V_{\text{SD}}$	$V_{\text{DS}} = 0\text{V}, I_S = 300\text{mA}$		0.84	1.1	V
<b>Dynamic characteristics</b>						
Input Capacitance <sup>b</sup>	$C_{\text{iss}}$	$V_{\text{DS}} = 40\text{V}, V_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$		41	80	pF
Output Capacitance <sup>b</sup>	$C_{\text{oss}}$			3.6	7	
Reverse Transfer Capacitance <sup>b</sup>	$C_{\text{rss}}$			2.9	5.6	
Gate resistance	$R_g$	$V_{\text{DS}} = 0\text{V}, V_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$		81	200	$\Omega$
Total Gate Charge	$Q_g$	$V_{\text{GS}} = 4.5\text{V}$ $V_{\text{GS}} = 10\text{V}$ $V_{\text{DS}} = 50\text{V}, I_D = 1\text{A}$		0.72	1.5	nC
Gate-Source Charge	$Q_{\text{gs}}$			1.41	2.8	
Gate-Drain Charge	$Q_{\text{gd}}$			0.24	0.4	
Turn-on delay time <sup>b</sup>	$t_{\text{d}(\text{on})}$			0.24	0.5	
Turn-on rise time <sup>b</sup>	$t_r$	$V_{\text{DS}} = 50\text{V}, I_D = 1\text{A}$ $V_{\text{GS}} = 10\text{V}, R_G = 6\Omega$		3.98	10	ns
Turn-off delay time <sup>b</sup>	$t_{\text{d}(\text{off})}$			4.95	10	
Turn-off fall time <sup>b</sup>	$t_f$			18.52	40	
				11.94	25	

**Notes:**


a. Pulse Test : Pulse width  $\leq 300\mu\text{s}$ , duty cycle  $\leq 2\%$ .

b. These parameters have no way to verify.

## Typical Characteristics



## DFN1006-3L Package Outline Dimensions



X1-DFN1006-3			
Dim	Min	Max	Typ
<b>A</b>	0.47	0.53	0.50
<b>A1</b>	0	0.05	0.03
<b>b1</b>	0.10	0.20	0.15
<b>b2</b>	0.45	0.55	0.50
<b>D</b>	0.95	1.075	1.00
<b>E</b>	0.55	0.675	0.60
<b>e</b>	—	—	0.35
<b>L1</b>	0.20	0.30	0.25
<b>L2</b>	0.20	0.30	0.25
<b>L3</b>	—	—	0.40


All Dimensions in mm

### NOTICE

JSCJ reserves the right to make modifications,enhancements,improvements,corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.


## DFN1006-3L Tape and Reel

### DFN1006-3L Embossed Carrier Tape




Dimensions are in millimeter										
Pkg type	a	B	C	d	E	F	P0	P	P1	W
DFN1006-3L	0.66	1.15	0.66	Ø1.50	1.75	3.50	4.00	2.00	2.00	8.00

### DFN1006-3L Tape Leader and Trailer



### DFN1006-3L Reel



Dimensions are in millimeter								
Reel Option	D	D1	D2	G	H	I	W1	W2
7" Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
10000 pcs	7 inch	100,000 pcs	203×203×195	400,000 pcs	438×438×220	