


Fast switching in thick and thin-film circuits diode


 Marking Code: **A7**  
 SOT-23 Plastic Package

**Absolute Maximum Ratings ( $T_a = 25^\circ\text{C}$ )**

Parameter	Symbol	Value	Unit
Repetitive Peak Reverse Voltage	$V_{RRM}$	85	V
Continuous Reverse Voltage	$V_R$	75	V
Continuous Forward Current (Double Diode Loaded)	$I_F$	125	mA
Continuous Forward Current (Single Diode Loaded)	$I_F$	215	mA
Repetitive Peak Forward Current	$I_{FRM}$	450	mA
Non-repetitive Peak Forward Surge Current at $t = 1 \text{ s}$ at $t = 1 \text{ ms}$ at $t = 1 \mu\text{s}$	$I_{FSM}$	0.5 1 4.5	A
Power Dissipation	$P_{tot}$	350	mW
Junction Temperature	$T_j$	150	$^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	- 65 to + 150	$^\circ\text{C}$

**Characteristics at  $T_a = 25^\circ\text{C}$** 

Parameter	Symbol	Max.	Unit
Forward Voltage at $I_F = 1 \text{ mA}$ at $I_F = 10 \text{ mA}$ at $I_F = 50 \text{ mA}$ at $I_F = 150 \text{ mA}$	$V_F$	0.715 0.855 1 1.25	V
Reverse Current at $V_R = 25 \text{ V}$ at $V_R = 75 \text{ V}$ at $V_R = 25 \text{ V}, T_j = 150^\circ\text{C}$ at $V_R = 75 \text{ V}, T_j = 150^\circ\text{C}$	$I_R$	30 1 30 50	nA $\mu\text{A}$ $\mu\text{A}$ $\mu\text{A}$
Diode Capacitance at $V_R = 0, f = 1 \text{ MHz}$	$C_d$	1.5	pF
Reverse Recovery Time at $I_F = I_R = 10 \text{ mA}, I_R = 1 \text{ mA}, R_L = 100 \Omega$	$t_{rr}$	4	ns




Fig. 1 Forward Characteristics




Fig. 2 Typical Leakage Current vs Reverse Voltage




Fig. 3 Typical Total Capacitance vs Reverse Voltage