

FEATURES

- $R_{DS(ON)} < 4.4\Omega$ @ $V_{GS} = 10V, I_D = 1A$
- Fast switching capability
- Lead free in compliance with EU RoHS directive.
- Improved dv/dt capability, high ruggedness

MECHANICAL DATA


- Case: TO-220, ITO-220, TO-251, TO-252, TO-262, TO-263 Package

Ordering Information

Part No.	Package	Packing
2N65-TU	TO-220	50pcs / Tube
2N65F-TU	ITO-220	50pcs / Tube
2N65E-TU	TO-262	50pcs / Tube
2N65D-TU	TO-263	50pcs / Tube
2N65D-TR	TO-263	800pcs / 13"Reel
2N65N-TU	TO-251	75pcs / Tube
2N65M-TU	TO-252	75pcs / Tube
2N65M-TR	TO-252	2.5Kpcs / 13"Reel


PRODUCT SUMMARY

V_{DS} (V)	$R_{DS(on)}$ (Ω)	I_D (A)
650	4.4 @ $V_{GS} = 10V$	2



Block Diagram

Pin Definition:
 1. Gate
 2. Drain
 3. Source



ABSOLUTE MAXIMUM RATINGS

($T_C = 25^\circ C$, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V_{DSS}	650	V
Gate-Source Voltage		V_{GSS}	3.0	V
Continuous Drain Current		I_D	2.0	A
Pulsed Drain Current (Note 2)		I_{DM}	8.0	A
Avalanche Energy		E_{AS}	115	mJ
Power Dissipation	TO-220/TO-263/TO-262	P_D	44	W
	ITO-220		23	
	TO-251/TO-252		34	
Junction Temperature		T_J	+150	C
Storage Temperature		T_{STG}	-55 ~ +150	C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by maximum junction temperature

3. $L=30mH$, $I_{AS}=2.7A$, $V_{DD}=50V$, $R_G=25\Omega$, Starting $T_J=25^\circ C$

2N65

650V N-Channel Power MOSFET

THERMAL DATA

PARAMETER		SYMBOL	RATING	UNIT
Junction to Ambient	TO-220/ITO-220	θ_{JA}	62.5	C/W
	TO-262/TO-263		110	
	TO-251/TO-252			
Junction to Case	TO-220/TO-263/TO-262	θ_{JC}	2.35	C/W
	ITO-220		5.5	
	TO-251/TO-252		2.9	

ELECTRICAL CHARACTERISTICS (T_C=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	V_{DSS}	$V_{GS}=0V, I_D=250\mu A$	650			V
Drain-Source Leakage Current	I_{DS}	$V_{DS}=650V, V_{GS}=0V$		10		μA
Gate-Source Leakage Current	Forward	$V_G=30V, V_{DS}=0V$		100		nA
	Reverse	$V_{GS}=-30V, V_{DS}=0V$		-100		nA
ON CHARACTERISTICS						
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	2.0		4.0	V
Static Drain-Source On-State Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=1.0A$		4	4.4	Ω
DYNAMIC CHARACTERISTICS						
Input Capacitance	C_{ISS}	$V_{DS}=25V, V_{GS}=0V, f=1MHz$		300		pF
Output Capacitance	C_{OSS}			45		pF
Reverse Transfer Capacitance	C_{RSS}			2		pF
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{D(ON)}$	$V_{DD}=300V, I_D=2A, R_G=25\Omega$ (Note 1, 2)		10		ns
Turn-On Rise Time	t_R			25		ns
Turn-Off Delay Time	$t_{D(OFF)}$			20		ns
Turn-Off Fall Time	t_F			25		ns
Total Gate Charge	Q_G	$V_{DS}=480V, I_D=2.4A, V_{GS}=10V$ (Note 1, 2)		5.7		nC
Gate-Source Charge	Q_{GS}			1.8		nC
Gate-Drain Charge	Q_{GD}			2		nC
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=2.0A$			1.4	V
Maximum Continuous Drain-Source Diode Forward Current	I_S				2.0	A
Maximum Pulsed Drain-Source Diode Forward Current	I_{SM}				8.0	A
Reverse Recovery Time	t_{rr}	$V_{GS}=0V, I_S=2A$ $dI/dt=100A/\mu s$ (Note 1)		357		ns
Reverse Recovery Charge	Q_{RR}			2		μC


Notes: 1. Pulse Test: Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.

2. Essentially independent of operating temperature.


2N65

650V N-Channel Power MOSFET

TEST CIRCUITS AND WAVEFORMS



Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms


2N65

650V N-Channel Power MOSFET


TEST CIRCUITS AND WAVEFORMS(Cont.)




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform



Unclamped Inductive Switching Test Circuit







Unclamped Inductive Switching Waveforms

2N65

650V N-Channel Power MOSFET


TYPICAL CHARACTERISTICS




2N65

650V N-Channel Power MOSFET


TO-220AB



ITO-220AB



TO-263




Dimensions in inches and (millimeters)

2N65

650V N-Channel Power MOSFET


TO-252

(DPAK)




Dimensions in inches and (millimeters)

TO-251



Dimensions in inches and (millimeters)

TO-262



Dimensions in inches and (millimeters)